


Measuring leads

SML 100/1



Product	SML 100/1
description	Silicone measuring lead, 4mm plug with caged spring on both sides. Nickel-plated copper-beryllium contact spring. Highly flexible, double insulated stranded lead, resistant against soldering iron, grip and lead shatter-proof. Built in color indicator for easy identification of insulation damages.
operating instruction	BA401
article-no. / *colour	9733881xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green
drawing	
technical data	
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	16 A
material socket	contact pin: brass contact spring: copper - beryllium
housing material	PVC-P
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
cable length	100 cm
conductor size	1 mm ²

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges

⁽²⁾without rated measurement category, for other circuits that are not directly connected to mains

stand : November 13, 2025 5:59 PM