


Sockets

PB 4



Product	PB 4
description	4 mm diameter test socket for measuring and testing printed boards during operation. The test socket may also be mounted on the printed board using a BZ 2.2 DIN7971 pan-head, self-tapping screw. Tin-plated brass through-hole 4 mm diameter socket.
operating instruction	BA406
article-no. / *colour	● 00 black ● 01 red
drawing	
	 Technical drawing showing two views of the PB 4 test socket. The side view (left) shows a total height of 10.5 mm, a mounting hole diameter of $\varnothing 1.9$ mm, a mounting hole pitch of 17.8 mm, and a total width of 21 mm. The top view (right) shows a total width of 7.5 mm, a mounting hole diameter of 4 mm, a mounting hole pitch of 7 mm, and a total height of 5.2 mm. A 1.2 mm dimension is also indicated for the mounting hole offset.
technical data	
connection	solder connection
rated voltage	30 VAC / 60 VDC
rated current (consider derating curve)	16 A
material socket	brass, tin plated
housing material	PC
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +85 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges
 stand : November 13, 2025 6:00 PM