


# Standard Inductive Sensors

PS8-18GI70-E2\_CE



## Dimensions(Unit:mm)



## Technical Features

| Signaling                          |                                            |
|------------------------------------|--------------------------------------------|
| Signalling                         | Back led                                   |
| Data Output                        |                                            |
| Electrical connection              | DC - PNP                                   |
| Contact Type                       | NO                                         |
| Max. switching current             | 200 mA                                     |
| Output protection                  | Short circuit and reverse                  |
| Sensor voltage drop (load powered) | <2 V                                       |
| Max. switching frequency           | 200 Hz                                     |
| Electrical Characteristics         |                                            |
| Supply voltage                     | 10 to 30Vdc                                |
| Ripple                             | ±10 %                                      |
| Current consumption                | <10 mA                                     |
| Electrical Connection              |                                            |
| Electrical connection              | Cable                                      |
| Cable length                       | 2 m PVC                                    |
| Cable length options               | PVC 6 m PVC 10 m PVC 15 m PVC 20m PVC 25 m |
| Number of wires                    | 3 wires                                    |

| Housing                       |                                                                |
|-------------------------------|----------------------------------------------------------------|
| Enclosure                     | threaded; brass with nickel plating                            |
| Tube length options           | 50 mm (standard)                                               |
| Operating temperature         | - 25 °C to + 70 °C                                             |
| Protection class              | IP67, IP69K                                                    |
| Housing options               | GX (stainless steel), GT (PTFE), GP (plastic)                  |
| Tube length                   | 70 mm                                                          |
| Recommended tightening torque | 3 Nm                                                           |
| Mechanical Characteristics    |                                                                |
| Diameter                      | M18                                                            |
| Sensing distance Sn           | 08 mm                                                          |
| Mouting                       | Not flushed                                                    |
| Hysteresis                    | ±5 %                                                           |
| Repeatability                 | <0.01 mm                                                       |
| Operational distance          | 6.48 mm                                                        |
| Standard object               | 24x24 mm                                                       |
| Cable options                 | PU                                                             |
| Weight                        | 150 g                                                          |
| Thread type                   | M18 x 1 mm                                                     |
| Application                   | Common industrial areas ou Atmosferas com poeiras combustíveis |

## ORDERING DETAILS

| Description      | TE Part Number       |
|------------------|----------------------|
| PS8-18GI70-E2_CE | <b>6000005914-SE</b> |

### Accessory: Controls - KMV Line

| Part Number        | Model               | No channels    | Application                 | Supply voltage   | Power consumption                     |
|--------------------|---------------------|----------------|-----------------------------|------------------|---------------------------------------|
| <b>52920552-SE</b> | KMV-100/110-220 Vac | Single channel | Source with relay to sensor | 110Vac or 220Vac | 1 VA at 110 Vca and 1.7 VA at 220 Vca |

### Accessory: Bracket - Bracket for Tubular Sensors

| Part Number          | Model | Application                     | Material            | Fixation                     |
|----------------------|-------|---------------------------------|---------------------|------------------------------|
| <b>5000010248-SE</b> | MS-18 | assembly of M18 tubular sensors | 304 stainless steel | through included M5x1 screws |

## te.com

©2026 TE Connectivity plc. family of companies. All Rights Reserved.

TE Connectivity, TE, TE connectivity (logo), and EVERY CONNECTION COUNTS, Schaffner and Schaffner MORE POWER TO YOU are trademarks owned or licensed by TE Connectivity plc. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

03/26 ED