

Product: [MPS-8U-RST 5L-2RKT 5L](#) 








M12 Power | h-splitter | Male → 2 x Female, 4-pin L-coded, 63 V / 16 A

Product Description

M12 Power | h-splitter | input: 1 x Male, output: 2 x Female, 4-pin L-coded, 63 V / 16 A

Technical Drawing





Technical Specifications

Product Description

Product Family:	Power Connector
Brand:	Lumberg Automation
Connector Type:	Molded Splitter
Shielding Type:	Unshielded
Voltage Rating:	63 V
Rated Voltage (UL):	63 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	60 V AC/DC
Current Rating:	16 A

Technical Data Side 1

Side 1 Product Sub Family:	M12 Power
Side 1 Type of Contact/Gender:	Pin Contact / Male
Connector Design:	Input M12 Male h shape
Attachment Type:	Coupling Screw
Number of Pins:	5 (4+FE)
Coding, Side 1:	L
Insulation Resistance:	> 10 ⁸ Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	-30 °C to +90 °C, notice derating
Protection Degree / IP Rating**:	IP65, IP67
Side 1 Design Standard:	IEC 61076-2-111
Side 1 Pollution Degree:	3 acc. to IEC 60664-1
Clearance / Creepage Distance:	IEC 60664-1 (2020-05)
Overvoltage Category:	III acc. to IEC 60664-1
Contact Base Material:	Copper Alloy (CuZn)
Side 1 Contact Plating:	Gold over Copper (Cu/Au)
Contact Bearer Material:	Polyamide (PA)
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Thermoplastic Polyurethane (TPU)
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Copper Alloy (CuZn)
Attachment Plating:	Nickel (Ni)
O-Ring Material:	Fluoroelastomer (FPM/FKM)
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight
Note:	1. Do not connect or disconnect under load.

Technical Data Side 2

Side 2 Product Sub Family:	M12 Power
Side 2 Type of Contact/Gender:	Socket Contact / Female
Connector Design, Side 2:	Output 2 x M12 Female
Attachment Type, Side 2:	Coupling Nut
Number of Pins, Side 2:	5 (4+FE)
Coding, Side 2:	L
Mating Cycles, Side 2:	≤ 100
Protection Degree / IP Rating, Side 2**:	IP65, IP67
Clearance / Creepage Distance, Side 2:	IEC 60664-1 (2020-05)
Overvoltage Category, Side 2:	III acc. to IEC 60664-1
Contact Base Material, Side 2:	Copper Alloy (CuZn)
Contact Plating, Side 2:	Gold over Copper (Cu/Au)
Contact Bearer Material, Side 2:	Polyamide (PA)
Contact Bearer Color, Side 2:	Black
Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Copper Alloy (CuZn)
Attachment Plating, Side 2:	Nickel (Ni)
Fastening Torque (Attachment), Side 2:	M 12x1: (50-60) Ncm, hand-tight

Technical Data Side 3

Attachment Material, Side 3:	Copper Alloy (CuZn)
Coding, Side 3:	L
Contact Base Material, Side 3:	Copper Alloy (CuZn)
Contact Bearer Color, Side 3:	Black
Contact Bearer Material, Side 3:	Polyamide (PA)
Contact Plating, Side 3:	Gold over Copper (Cu/Au)
Number of Pins, Side 3:	5 (4+FE)
Protection Degree / IP Rating (IEC 60529), Side 3:	IP65, IP67, IP68
Rated Current*, Side 3:	16 A
Rated Voltage, Side 3:	63 V
Type of Contact / Gender, Side 3:	Socket Contact / Female

Technical Data Side 4

Product Sub Family, Side 4:	M12 Power
Protection Degree / IP Rating (IEC 60529), Side 4:	IP65, IP67, IP68
Rated Current*, Side 4:	16 A

Approvals

UL-File:	E497237
UL:	UL 2237; cULus

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
Note Derating:	* Notice derating

Variants

Item #	Item Description
26383	MPS-8U-RST 5L-2RKT 5L

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.