


## Measuring leads

### MAL S GG-B 100/2,5



| Product                                                                        | MAL S GG-B 100/2,5                                                                                                                                                                                                                                                                 |
|--------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| description                                                                    | Safety adapter test lead according to IEC 61010 with 4 mm safety plug straight outlet and 4 mm safety socket on the other end. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve. Built in color indicator for easy identification of insulation damages. |
| operating instruction                                                          | BA453                                                                                                                                                                                                                                                                              |
| article-no. /<br>*colour                                                       | 9340461xx<br>                                                                                                                                                                                   |
| drawing                                                                        |                                                                                                                                                                                                |
| technical data                                                                 |                                                                                                                                                                                                                                                                                    |
| rated voltage                                                                  | AC/DC 1000 V                                                                                                                                                                                                                                                                       |
| measurement cat. acc. to IEC 61010                                             | CAT III                                                                                                                                                                                                                                                                            |
| rated current<br>(consider derating curve)                                     | 32 A                                                                                                                                                                                                                                                                               |
| material plug                                                                  | brass, nickel plated                                                                                                                                                                                                                                                               |
| material socket                                                                | brass, nickel plated                                                                                                                                                                                                                                                               |
| housing material                                                               | PA                                                                                                                                                                                                                                                                                 |
| temperature range acc. To IEC61010 <sup>(1)</sup>                              | -15 °C to +70 °C                                                                                                                                                                                                                                                                   |
| flammability class acc. to UL 94<br>(only valid for basic material of housing) | V-2                                                                                                                                                                                                                                                                                |
| cable length                                                                   | 100 cm                                                                                                                                                                                                                                                                             |
| conductor size                                                                 | 2,5 mm <sup>2</sup>                                                                                                                                                                                                                                                                |

<sup>(1)</sup>contact the manufacturer for applications at deviating temperature ranges  
 stand : November 13, 2025 5:59 PM