



PRODUCT SPEC SHEET

SKU 104836

Model:VT-61012CCT

EAN:3800170256828

VT-61012CCT 12W BACKLIT RECESSED PANEL CREE CHIP 3IN1 SQ 6YRS WTY



IP20
STANDARD



- Strong and sturdy Plastic body Backlit Mini Panels
- High quality power driver ensures reliable lifetime
- Choose and switch to your preferred color temperature at any time using the CCT switch
- Designed with high efficiency LED SMD-CREE Chip chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-61012CCT
Cutting Size:	150x150mm
On/Off Cycles:	>15000
Installation Type:	Recessed
CRI:	>80
Watts:	12
Lumens:	1320
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	Plastic
Dimension:	189x170.8x28.8mm
Operation Temperature:	-20°C to +45°C

LISTING DETAILS

SKU:	104836
Model:	VT-61012CCT
EAN:	3800170256828
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	0.19
Unit CBM:	0.001563
Dimension:	189x170.8x28.8mm

MASTER BOX PACKAGING

Box Qty:	60
Qty Per Pallet:	1200
Length (Box) mm:	192

Shape:	Square
LED Chip Type:	SMD-CREE Chip
Beam Angle:	120°
Energy Rating Label:	E (2021)
IP Rating:	IP20
Energy Saving:	85 Energy
Long Life:	30,000 Hours

Width (Box) mm:	39
Height (Box) mm:	175