


Varistors for High Voltage



AMCV-SH01206

Request Samples



Check Inventory



3.2 x 1.6 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- SMD type, small size suitable for high density mounting
- Excellent clamping ratio and strong capability of voltage surge suppression
- Excellent solderability (Ni, Sn plating)
- Green, meet RoHS requirements.

Applications

- AC Mains surge protection for 120V/ 230V
- AC-DC Switch Mode Power Supplies (SMPS)
- Commercial and industrial LED lighting
- Home and Commercial appliances
- Industrial Control panels for AC distribution
- Uninterruptible Power Supplies (UPS).
- Level 1 and Level 2 EV Charging equipment
- Solar Inverters /Grid connected equipment

Electrical Specifications

Part Number	Max. Working Voltage		Varistor Voltage	Max. Clamping Volts/Amps		Rated Single Pulse Transient	
Test Condition	<30μA		@1mA DC	8/20μs		Energy 10/1000μs	Peak Current 8/20μs
	DC	AC RMS					
Units	Volts	Volts	Volts	Volts	Amps	Joules	Amps
Symbol	VDC	VAC	VB	VC	IC	ET	IP
AMCV-SH1206-151-301	200	150	240[216-264]	360	5.0	0.9	300
AMCV-SH1206-151-201	200	150	240[216-264]	360	5.0	0.9	200
AMCV-SH1206-171-301	225	175	270[243-297]	410	5.0	1.0	300
AMCV-SH1206-171-201	225	175	270[243-297]	410	5.0	1.0	200
AMCV-SH1206-191-201	250	195	300[270-330]	450	5.0	1.0	200
AMCV-SH1206-231-201	300	230	360[324-396]	540	5.0	0.9	200
AMCV-SH1206-251-101	320	250	390[351-429]	590	5.0	0.9	100
AMCV-SH1206-271-101	350	275	430[387-473]	650	5.0	1.0	100
AMCV-SH1206-301-101	385	300	470[423-517]	710	5.0	1.0	100
AMCV-SH1206-321-600	410	320	510[459-561]	880	5.0	0.5	60

Operating Temperature: -55°C to +125°C

Storage: Temperature 10°C to +50°C, RH<60%, Max. Humidity <85% RH

Items	Test Methods and Remarks
Varistor Voltage at 1mA DC (VB)	Measuring current: 1mA DC, Duration: 0.2 to 2 sec
Capacitance (C)	Measure source: 1.0 VRMS, Test frequency: 1kHz.
Clamping Voltage (VC)	Measuring source: 8/20us waveform

Unless otherwise specified, the standard atmospheric conditions for measurement/test as:

- Ambient Temperature: 20±15°C
- Relative Humidity: 65±20%
- Air Pressure: 86 kPa to 106 kPa




12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/13/2026

ABRACON IS
ISO9001-2015
CERTIFIED

Varistors for High Voltage



AMCV-SH01206

Request Samples




Check Inventory



3.2 x 1.6 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Number Identification



*Tolerance refers to varistor voltage.

Part Marking

No Marking




12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/13/2026

ABRACON IS
ISO9001-2015
CERTIFIED

Varistors for High Voltage



AMCV-SH01206

Request Samples





Check Inventory



3.2 x 1.6 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications





Recommended PCB Layout


Series	A	B	C	D	L (ref)	G (ref)	H (ref)
AMCV-SH1206	3.2+0.6/-0.2	1.6+0.4/-0.2	2.0	0.25 – 0.75	3.8 - 5.5	1.8 – 2.5	1.6 – 2.2

Dimensions: mm

Materials



	Part Name	Material
1	Base Material	ZnO
2	Internal Conductor	Ag-Pd
3	Terminal Electrode	Ag (Inner layer) Ni-Sn (Outer layer)



AMCV-SH01206

Request Samples




Check Inventory



3.2 x 1.6 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile




Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C	60 ~ 120 sec.
2	Reflow	T_L ≥217°C	60 ~ 90 sec.
3	Peak heat	T_P 260°C Max.	10 sec. MAX

Ref Paste: Sn/3.0Ag/0.5Cu (Lead-Free)

Max ramp up rate:3°C/Sec

Max ramp down rate:6°C/Sec

Varistors for High Voltage



AMCV-SH01206

Request Samples




Check Inventory




3.2 x 1.6 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

Tape & Reel: 2K pcs/reel



a	b	P	D	W	K	T
2.1	3.90	4.0	3.50	8.0	2.2	0.30



A	C	W1
178	58	$8.4 \pm 1.5 / -0.0$

Dimensions: mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200
 Bee Cave, TX 78738
 Phone: 512-371-6159 Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
7/13/2026

ABRACON IS
 ISO9001-2015
 CERTIFIED