


4-Port USB Type-C PCIe Card, USB 3.2 10Gbps, USB-C PCI Express Expansion Card, 4x Independent USB Controllers, Windows/Linux/macOS, TAA-Compliant

Product ID: P10Q4C-USB-CARD



Expand the USB connectivity of a desktop computer or server by adding four external USB Type-C 10Gbps ports with this internal PCI Express 3.0 expansion card.

Traditional single-controller USB cards share bandwidth across all ports. With its four independent USB controllers, this USB-C expansion card enables each port to achieve up to 10Gbps, reducing bottlenecks and increasing data throughput.

The high bandwidth makes the card ideal for transferring large files, real-time editing of high-resolution photos and videos on external storage, off-loading media from mobile devices, using high-resolution video capture devices, tethered photography equipment, or high-speed USB network adapters like 10G Ethernet copper or fiber adapter.

This USB PCI Express card can provide up to 5V 3A (15W) per USB-C port, enabling sync and charge of portable devices. If the motherboard can't supply enough power, a built-in SATA power connector can supply additional power to the card.

The PCI Express USB card is plug-and-play in most major operating systems, including Windows, macOS, and Linux. The card is compatible with PCI Express 3.0 and x4, x8, and x16 slots. The USB expansion card also ships with a pre-installed standard profile bracket and includes a low-profile bracket for maximum compatibility.

Certifications, Reports and Compatibility





Applications

Features

- **HIGH-PERFORMANCE USB CARD:** Enhance a desktop computer or server by upgrading or expanding its USB connectivity with this four-port USB Type-C card; Features individual USB controllers for up to 10Gbps per port (data only); PCI Express 3.0; TAA-compliant
- **DEDICATED 10GBPS PER PORT:** Features 4x USB controllers ensuring up to 10Gbps of bandwidth per port; High data throughput is ideal for large file transfers on external storage, simultaneous use of multiple USB-C devices, or using 10GbE USB network adapters
- **COMPATIBILITY:** Windows/Linux/macOS compatible; Add-on card ships with standard-profile bracket installed (low-profile included); PCIe 3.0 x4 (or larger) slot required; Plug-and-play drivers; Supported speeds: 10Gbps, 5Gbps, 480Mbps, 12Mbps, and 1.1Mbps
- **AUXILIARY SATA POWER:** If the motherboard doesn't provide enough power, the built-in SATA power connection can be used to supply additional power to the USB ports; Internal USB-C PCIe expansion card can supply up to 5V 3A (15W) per port
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB 3.2 Gen 2 PCI Express Type-C card is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030911436
Warranty	2 Years

Power

Power Source	Bus Powered
Power Delivery	15W

Physical & Environmental

Color	Red
Product Length	5.5 in [14 cm]
Product Width	2.2 in [56.2 mm]
Product Height	4.7 in [12.0 cm]

Weight of Product	3.3 oz [94 g]
Operating Temperature	0C to 85C (32F to 185F)
Storage Temperature	-25C to -13C (14F to 185F)
Humidity	20% ~ 80% RH (non-condensing)

Performance

Total USB Power Output	15W max per port
Maximum Data Transfer Rate	10Gbps
Type and Rate	USB 10Gbps
UASP Support	Yes

Hardware

Number of Ports	4
Interface	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	PCI Express 3.0
Chipset ID	ASMedia - ASM3142
	ASMedia - ASM1543
	ASMedia - ASM2812X

Packaging & In-the-Box

Included in Package	1 - PCIe USB Card (Standard Bracket Installed)
	1 - Low-Profile Bracket
	1 - Quick-Start Guide
Package Width	6.7 in [17 cm]
Package Depth	5.6 in [14.2 cm]
Package Height	1.2 in [30 mm]

Shipping (Package)
Weight 5.6 oz [160 g]

Connector(s)

Host Connector 1 (Quantity)	1
Host Connector 1	PCI Express x4
Connector 1 (Quantity)	4
Connector 1	USB-C (10Gbps, 15W)
Connector 2 (Quantity)	1
Connector 2	SATA (15-Pin)

****Product appearance and specifications are subject to change without notice.***