

## 5 Port Unmanaged Industrial Gigabit Ethernet Switch - DIN Rail / Wall-Mountable - TAA

**Product ID:** IES51000



The IES51000 5-Port Industrial Ethernet Switch offers 5 Gigabit Ethernet ports in a compact, IP30-rated metal enclosure, making it the ideal network solution for harsh industrial environments such as factory floors, warehouses or large junction boxes.

Quickly connect your network devices with little to no configuration. This unmanaged industrial network switch supports 10/100/1000 Mbps transfer speeds, full/half-duplex auto-negotiation, jumbo frames and auto MDI/MDIX, which helps to eliminate the hassle of troubleshooting mis-matched speed and duplex settings.

Providing seamless operation in the event of power dips or failures, the switch features redundant 12-58V DC terminal block power inputs to help prevent unnecessary downtime. When used with two power sources, the switch also supports alarm relay contacts that you can wire to your existing alarm circuit to notify you instantly when a power disruption occurs.

For easy installation and dependable performance in harsh environments, the switch can be DINRail or wall mounted and features a compact, IP30-rated enclosure with an extended operating temperature range (-40C to 75C).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Ideal for industrial applications such as warehouses and junction boxes without temperature control
- Suitable for adding Gigabit Ethernet on factory / manufacturing floors
- Great for adding small workgroups to an existing network

## Features

- 5 10/100/1000 Mbps unmanaged RJ45 Ethernet ports
- IP30-rated DIN rail and wall-mountable metal enclosure
- Wide-range redundant power via two 12-58V DC terminal block inputs, with alarm relay
- Overcurrent and reverse polarity protection
- Extended operating temperature range (-40C to 75C)

---

### General

|                  |              |
|------------------|--------------|
| UPC              | 065030859318 |
| Package Quantity | 1            |
| Warranty         | 2 Years      |

---

### Power

|                   |                |
|-------------------|----------------|
| Power Source      | Terminal Block |
| Input Voltage     | 12 ~ 58 DC     |
| Power Consumption | 3.63W Max.     |

---

### Physical & Environmental

|                       |                            |
|-----------------------|----------------------------|
| Color                 | Black                      |
| Material              | Steel                      |
| Product Length        | 4.4 in [11.1 cm]           |
| Product Width         | 3.5 in [89.0 mm]           |
| Product Height        | 1.1 in [28.0 mm]           |
| Weight of Product     | 11.6 oz [328.0 g]          |
| Operating Temperature | -40C to 75C (-40F to 167F) |

|                     |                            |
|---------------------|----------------------------|
| Storage Temperature | -40C to 85C (-40F to 185F) |
| Humidity            | 5-95% RH (Non-Condensing)  |

## Performance

|                            |                                                      |
|----------------------------|------------------------------------------------------|
| Maximum Data Transfer Rate | 2 Gbps (Full-Duplex)                                 |
| Maximum Cable Length       | 328.1 ft [100 m]                                     |
| Buffer Size                | 128 KB                                               |
| Flow Control               | Half-duplex back-pressure and IEEE802.3x full-duplex |
| Compatible Networks        | 10/100/1000 Mbps                                     |
| Auto MDIX                  | Yes                                                  |
| Full Duplex Support        | Yes                                                  |
| Jumbo Frame Support        | 9K max.                                              |
| Switching Architecture     | Store-and-Forward                                    |

## Hardware

|                    |                                                                                                                                                                                             |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of Ports    | 5                                                                                                                                                                                           |
| Interface          | RJ45 (Gigabit Ethernet)                                                                                                                                                                     |
| Industry Standards | IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-TX<br><br>IEEE 802.1p QoS, IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3ad Link Aggregation<br><br>IP30 (Enclosure) |
| LED Indicators     | 1 - P1 (Power) indicator<br><br>1 - P2 (Power) indicator<br><br>1 - ALM (Alarm) indicator<br><br>5 - Link / Act<br><br>5 - Speed indicator                                                  |

## Packaging & In-the-Box

|                           |                                |
|---------------------------|--------------------------------|
| Included in Package       | 1 - Industrial Ethernet Switch |
|                           | 2 - Wall-Mount Brackets        |
|                           | 1 - DIN-Rail Clip              |
|                           | 4 - Screws                     |
|                           | 1 - Terminal Block             |
|                           | 1 - Instruction Manual         |
| Package Width             | 7.0 in [17.8 cm]               |
| Package Depth             | 5.5 in [13.9 cm]               |
| Package Height            | 3.3 in [83 mm]                 |
| Shipping (Package) Weight | 18.3 oz [518 g]                |

---

#### Connector(s)

|                        |                         |
|------------------------|-------------------------|
| Connector 1 (Quantity) | 5                       |
| Connector 1            | RJ-45                   |
| Connector 2 (Quantity) | 1                       |
| Connector 2            | Terminal Block (6 Wire) |

---

***\*Product appearance and specifications are subject to change without notice.***