

ECN/PCN No.: 5245

For Manufacturer						
Product Description: AUTOMOTIVE & INDUSTRIAL GRADE CMOS-COMPATIBLE SMD CRYSTAL OSCILLATOR		Abraccon Part Number / Part Series: ASEAIG		☐ Documentation only ☒ ECN ☐ EOL		☒ Series ☐ Part Number
Affected Revision: C		New Revision: D		Application:		☐ Safety ☒ Non-Safety
Prior to Change: Electrical Specifications: Rise and Fall Time (Tr/Tf)						
Rise and Fall Time (Tr/Tf)	Vdd = 3.3 V	2.5	4.0	2.5	ns	
	Vdd = 3.0 V	2.5	4.0	2.5		
	Vdd = 2.5 V	3.0	5.0	3.0		
	Vdd = 1.8 V	3.0	6.0	3.0		
After Change: Electrical Specifications: Rise and Fall Time (Tr/Tf)						
Rise and Fall Time (Tr/Tf)	Vdd = 3.3 V		2.5	4.0	ns	
	Vdd = 3.0 V		2.5	4.0		
	Vdd = 2.5 V		3.0	5.0		
	Vdd = 1.8 V		3.0	6.0		
Cause/Reason for Change: Incorrect rise and fall time specifications resulted from a typographical error introduced during content transfer between document revisions.						
Change Plan						
Effective Date: 07/20/2026		Additional Remarks: N/A				
Change Declaration: The changes attached do not impact electrical nor mechanical performance of this series.						
Issued Date: 07/20/2026		Issued By: Brooke Cushman		Issued Department: Engineering		
Approval: Thomas Culhane Engineering Director		Approval: Reuben Quintanilla Quality Director		Approval: Ying Huang Purchasing Director		
For Abracon EOL only						
Last Time Buy (if applicable): N/A			Alternate Part Number / Part Series: N/A			
Additional Approval:		Additional Approval:		Additional Approval:		
Customer Approval (If Applicable)						
Qualification Status: ☐ Approved ☐ Not accepted <i>Note: It is considered approved if there is no feedback from the customer 1 month after ECN/PCN is released.</i>						
Customer Part Number:			Customer Project:			
Company Name:		Company Representative:		Representative Signature:		
Customer Remarks:						

[illegible]

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory



ESD Sensitive



3.2 x 2.5 x 1.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Features

- AEC-Q200 Qualified
- Automotive Grade 1: -40°C to +125°C
- TS16949 Production Line Certified
- PPAP Available Upon Request
- Hermetically Seam-sealed Ceramic Package
- RoHS/RoHS II Compliant and Pb free

Applications

- Infotainment Systems
- Keyless Entry & Startup
- GPS & Navigation
- Comfort control
- ADAS (Advanced Driver Assistance Systems)
- Vehicle to Vehicle Communication
- LiDAR (Light Detection and Ranging)
- In-vehicle Networking
- Powertrain & Drive Control
- Power Control & Conversion
- Industrial Control & Automation

Key Electrical Specifications

Parameters		Min.	Typ.	Max.	Units	Notes
Frequency Range		1.25		156.25	MHz	
Operating Temperature		-40		+125	°C	Option "blank"; See options
Storage Temperature		-55		+125	°C	Option "X, blank, L, N"
Overall Frequency Stability ^[Note 1]		-50		+50	ppm	Option "C"; See options
		-100		+100		Option "blank"; See options
		-150		+150		Option "R"; See options
Supply Voltage (Vdd)		+1.71	+1.8 ~ +3.3	+3.465	V	Option "5"
		+3.135	+3.3	+3.465		Option "blank"
		+2.85	+3.0	+3.15		Option "1"
		+2.375	+2.5	+2.625		Option "2"
		+1.71	+1.8	+1.89		Option "3"
Supply Current (Idd) into 15pF Load	Vdd = 3.3 V		2.5	7.0	mA	1.250~20.000 MHz
			4.4	13.0		20.999~40.000 MHz
			6.5	19.0		40.999~60.000 MHz
			20.0	40.0		60.999~156.0000 MHz
	Vdd = 3.0 V		2.5	7.0		1.250~20.000 MHz
			4.4	13.0		20.999~40.000 MHz
			6.5	19.0		40.999~60.000 MHz
			20.0	40.0		60.999~156.0000 MHz
	Vdd = 2.5 V		2.0	8.0		1.250~20.000 MHz
			3.0	8.0		20.999~40.000 MHz
			5.0	15.0		40.999~60.000 MHz
			20.0	40.0		60.999~156.0000 MHz
	Vdd = 1.8 V		1.0	4.0		1.250~20.000 MHz
			2.0	4.0		20.999~40.000 MHz
			3.0	6.0		40.999~60.000 MHz
			15.0	20.0		60.999~156.0000 MHz

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory



ESD Sensitive



3.2 x 2.5 x 1.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Parameters		Min.	Typ.	Max.	Units	Notes
Disable Current				10.0	μA	
Output Load				15	pF	CMOS
Output Voltage	V _{OH}	0.9*V _{dd}			V	
	V _{OL}			0.1*V _{dd}		
Tri-state function		"1" (VIH≥0.7*V _{dd}) or Open: Oscillation; "0" (VIH<0.3*V _{dd}): No oscillation/Hi Z				
Aging		-2.0		+2.0	ppm	@25°C± 3°C First year
Symmetry @1/2V _{dd}		40	50	60	%	Option "blank"
		45	50	55		Option "S"
Start-up Time			2.0	5.0	ms	
Rise and Fall Time (Tr/Tf)	V _{dd} = 3.3 V		2.5	4.0	ns	
	V _{dd} = 3.0 V		2.5	4.0		
	V _{dd} = 2.5 V		3.0	5.0		
	V _{dd} = 1.8 V		3.0	6.0		
RMS Phase Jitter @ +25°C (10 - 39MHz: 12kHz to 5MHz) (>39MHz: 12kHz to 20MHz)	V _{dd} = 3.3 V		0.5	< 1.0	ps	
	V _{dd} = 3.0 V		0.5	< 1.0		
	V _{dd} = 2.5 V		0.5	< 1.0		
	V _{dd} = 1.8 V		0.5	< 1.0		
Period Jitter RMS	V _{dd} = 3.3 V		3.0	5.0	ps	
	V _{dd} = 3.0 V		3.0	5.0		
	V _{dd} = 2.5 V		3.0	5.0		
	V _{dd} = 1.8 V		3.0	5.0		

Note 1: Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and 1st year

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory



ESD Sensitive



3.2 x 2.5 x 1.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Options and Part Identification (left blank if standard)

ASEAIG - MHz - - - -

Supply Voltage
Blank: 3.3V±5%
1: 3.0V±5%
2: 2.5V±5%
3: 1.8V±5%
5: 1.8V±5% ~ 3.3±5%

Freq. in MHz
e.g. 24.576MHz 14.31818MHz 26.000MHz

Operating Temp.
Blank: -40°C to +125°C
N: -30°C to +85°C
L: -40°C to +85°C
X: -40°C to +105°C

Packaging
Blank: Bulk
T: 1k pcs / reel
T3: 3k pcs / reel

Duty Cycle
Blank: 40/60% @ 1/2Vdd
S: 45/55% @ 1/2Vdd

Overall Freq. Stability
Blank: ±100ppm
R: ± 150 ppm
C: ±50ppm
P: ± 45 ppm (*)
F: ± 40 ppm (*)
H: ± 35 ppm (*)
K: ± 30 ppm (*)
W: ± 25 ppm (*)
J: ± 20 ppm (*)

(*) Contact Abracon for Availability

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory






ESD Sensitive




3.2 x 2.5 x 1.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Mechanical Dimensions



Pin #	Function
1	Tri-State
2	GND/Case
3	Output
4	Vdd

Recommended Land Pattern



Dimensions: mm

Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory



ESD Sensitive



3.2 x 2.5 x 1.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process

Classification Temperatures (Tc)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2

Pb-Free Process

Classification Temperatures (Tc)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (Tssmin)	100°C	150°C
Temperature maximum (Tssmax)	150°C	200°C
Time (Tssmin to Tssmax) (ts)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (Tssmax to Tp)	3°C/sec. max	3°C/sec. max
Liquidous temperature (Tc)	183°C	217°C
Time at liquidous (tl)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (Tp)*	see Table 1	see Table 2
Time (tp)** within 5°C of the specified classification temperature (Tc)	20 sec.	30 sec.
Ramp-down rate (Tp to Tssmax)	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (Tp) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (tp) is defined as supplier minimum and a user maximum.

Automotive & Industrial Grade CMOS-compatible SMD Crystal Oscillator

ASEAIG

Request Samples



Check Inventory



ESD Sensitive



3.2 x 2.5 x 1.2 mm

RoHS/RoHS II Compliant


MSL Level = N/A

Packaging:

Tape and Reel:

T: 1,000pcs/reel

T3: 3,000pcs/reel



Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



Phone: 512-371-6159 | Fax: 512-351-858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-17-26

ABRACON IS
ISO9001-2015
CERTIFIED