
PXle-8285

Specifications

2026-08-27



Contents

PXIe-8285 Specifications 3

PXIe-8285 Specifications

PXIe-8285 Specifications

These specifications describe the PXIe-8285.

Definitions

Warranted specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

Characteristics describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- *Typical* specifications describe the performance met by a majority of models.
- *Nominal* specifications describe an attribute that is based on design, conformance testing, or supplemental testing.


Specifications are *Typical* unless otherwise noted.

Conditions

Specifications are valid when operating the product within the limits defined in [Environmental Characteristics](#).

PXle-8285 Front Panel

Figure 1. PXle-8285 Front Panel



ETH 0 and ETH 1 Connectors

The PXle-8285 front panel features two SFP28 Ethernet ports, which support up to 25 GbE per connector. You can connect Mellanox-compatible active optical SFP28 or passive direct attach copper SFP28 cables to the ETH 0/1 connectors.

Communication Characteristics

Ethernet connectivity		
Port type	SFP28 port based on Mellanox OCP card	
Port number	Two	
Data rate supported per port		Up to 25 GbE

PXI Express link configuration	Gen3 x8 PCI Express connection
--------------------------------	--------------------------------

Environmental Guidelines



Notice This product is intended for use in indoor applications only.



Notice All cabling should be strain-relieved near input connectors. Take care not to directionally bias cable connectors within input connectors when applying strain relief.

Environmental Characteristics

Temperature		
Operating ¹		0 °C to 55 °C
Storage		-40 °C to 71 °C
Humidity		
Operating	10% RH to 90% RH, noncondensing	
Storage	5% RH to 95% RH, noncondensing	
Pollution Degree		2
Maximum altitude		2,000 m

1. The PXIe-8285 requires a chassis with slot cooling capacity ≥ 58 W. Not all chassis with slot cooling capacity ≥ 58 W can achieve this ambient temperature range. Refer to PXI chassis specifications to determine the ambient temperature ranges your chassis can achieve.

Shock and vibration	
Operating vibration	5 Hz to 500 Hz, 0.3 g RMS
Non-operating vibration	5 Hz to 500 Hz, 2.4 g RMS
Operating shock	30 g, half-sine, 11 ms pulse

Environmental Standards

This product meets the requirements of the following environmental standards for electrical equipment.

- IEC 60068-2-1 Cold
- IEC 60068-2-2 Dry heat
- IEC 60068-2-78 Damp heat (steady state)
- IEC 60068-2-64 Random operating vibration
- IEC 60068-2-27 Operating shock



Note To verify marine approval certification for a product, refer to the product label or visit ni.com/certification and search for the certificate.

Power Requirements

The PXle-8285 draws current from a combination of the 3.3 V and 12 V power rails. The maximum current drawn from each of these rails can vary depending on the cable connected to the module.

Table 1. PXle-8285 Power Requirements

Cable Type	Power Rail	Typical	Maximum
Passive Direct Connect	+3.3 V DC	1.21 A	1.82 A
	+12 V DC	1.21 A	1.82 A

Cable Type	Power Rail	Typical	Maximum
	Total Power	18.51 W	27.77 W
Optical	+3.3 V DC	1.69 A	2.54 A
	+12 V DC	1.16 A	1.74 A
	Total Power	19.50 W	29.25 W

Physical Characteristics

Dimensions	131 mm × 21 mm × 214 mm (5.16 in. × 0.83 in. × 8.43 in.)
Weight	375 g (13.23 oz)
PXIe slots	One



Note For detailed dimensional drawings and 3D models, visit ni.com/dimensions and search for PXIe-8285.

Safety Compliance Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1



Note For safety certifications, refer to the product label or the [Product Certifications and Declarations](#) section.

EMC Standards

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions



Note Group 1 equipment is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note In Europe, Australia, and New Zealand (per CISPR 11) Class A equipment is intended for use in non-residential locations.

Product Certifications and Declarations

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit ni.com/product-certifications, search by model number, and click the appropriate link.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *Engineering a Healthy Planet* web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

EU and UK Customers

-  **Waste Electrical and Electronic Equipment (WEEE)**—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法（中国RoHS）

-  **中国RoHS**—NI符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于NI中国RoHS合规性信息，请登录 ni.com/environment/rohs_china。 (For information about China RoHS compliance, go to ni.com/environment/rohs_china.)