



Features

- 2 × 4mm Square LED Lamps
- Low power consumption
- Excellent product quality and reliability
- Lead-free device

**RoHS
Compliant**

Applications

- Electronic signs and signals
- Bright ambient lighting conditions
- Backlight
- General purpose indicators

Specifications

Emitting Colour : Yellow
Lens Colour : Yellow Diffused
Material : GaAsP

Absolute Maximum Ratings: (T _A = 25°C)			
Parameter	Symbol	Value	Unit
Power Dissipation	P _D	65	mW
Forward Current	I _F	25	mA
Peak Forward Current ^{*1}	I _{FP}	60	mA
Reverse Voltage	V _R	5	V
Operating Temperature	T _{OPR}	-40°C to +85°C ▲	
Storage Temperature	T _{STG}	-40°C to +100°C	
Soldering Temperature ^{*2}	T _{SOI}	260°C For 5 Seconds Δ	

Notes:

*1: Pulse width ≤ 0.1ms, Duty cycle ≤ 1/10

*2: Δ At the Position of 3mm below package base.

*3: ▲ Please refer to the curve of forward current vs. temperature


Electrical / Optical Characteristics at T _A = 25°C						
Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Forward Voltage	V _F	1.7	2	2.5	V	I _F = 20mA
Reverse Current	I _R	-	-	10	uA	V _R = 5V
Dominant Wavelength	λ _d	584	588	594	nm	I _F = 20mA
Peak Wavelength	λ _p	-	590	-	nm	
Spectral Line Half-Width	Δλ	-	16	-	nm	
Luminous Intensity	I _V	40	85	200	mcd	
Power Angle	2θ _{1/2}	-	180	-	Deg.	

Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or dominant wavelength), the typical accuracy of the sorting process is as follows:

1. Dominant Wavelength: +/- 1nm
2. Chromatic Coordinates: +/- 0.01
3. Luminous Intensity: +/- 15%
4. Forward Voltage: +/- 0.1V

Dimensions









Notes:

1. Tolerance is ± 0.25 unless otherwise noted.
2. Lead spacing is measured where the leads emerge from the package.
3. Specifications are subject to change without notice.

Dimensions : Millimetres

Typical Electrical/Optical Characteristics Curves



Part Number Table

Description	Part Number
Single Colour LED, Rectangular, 2 × 4 × 7, Yellow	MP017018

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.