

**RoHS
Compliant**

Description

This transistor is designed for high-voltage, high-speed, power switching in inductive circuits where fall time is critical. They are particularly suited for 115 and 220 volt line operated switch-mode applications

Features

- High Temperature Performance Specified for:
- Reversed Biased SOA with Inductive Loads
- Switching Times with Inductive Loads
- Saturation Voltages
- Leakage Currents

Application

- Switching Regulators
- PWM Inverters and Motor Controls
- Solenoid and Relay Drivers
- Deflection Circuits

Absolute Maximum Ratings (Ta = 25°C)

Description	Symbol	2N6052	Unit
Collector-Emitter Voltage	$V_{CEO(sus)}$	400	V DC
Collector-Emitter Voltage	$V_{CEX(sus)}$	450	
Collector-Emitter Voltage	V_{CEV}	850	
Emitter Base Voltage	V_{EB}	9	
Collector Current – Continuous – Peak (2)	I_C I_{CM}	15 30	A DC
Base Current – Continuous – Peak (2)	I_B I_{BM}	10 20	
Emitter Current – Continuous – Peak (2)	I_E I_{EM}	25 35	
Total Power Dissipation @ Tc = 25°C @ Tc = 100°C Derate above 25°C	P_D	175 100 1	Watts W/°C
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +200	°C

Thermal Resistance

Description	Symbol	Value	Unit
Thermal Resistance, Junction to Case	R_{JC}	1	°C/W
Maximum Lead Temperature for Soldering Purposes: 1/8 from Case for 5 Seconds	T_L	275	°C

Electrical Characteristics

Parameter	Symbol	Test Condition	Min.	Max.	Unit
Collector-Emitter Sustaining Voltage	V _{CEO(sus)}	I _C =100mA, I _B =0	400	--	V DC
Collector-Emitter Sustaining Voltage	V _{CEX(sus)}	I _C = 8A V _{clamp} -Rated V _{CEX} , T _C =100°C	300	--	
Collector Cut off Current	I _{CEV}	V _{CEV} = Rated Value, V _{BE(off)} = 1.5V DC) V _{CE} = Rated Value, V _{BE(off)} = 1.5V DC), T _C = 100°C	--	1 4	mAdc
Collector Cut Off Current	I _{CER}	V _{CE} = Rated V _{CEV} , R _{BE} = 150, T _C = 100°C		5	
Emitter Cut Off Current	I _{EBO}	V _{BE} =9V, I _C =0		1	
Second Breakdown					
Second Breakdown Collector Current with base forward biased	I _{S/b}	t = 1 s (non-repetitive) (V _{CE} =100 V _{DC})	0.2	--	A DC
On Characteristics (1)					
DC Current Gain	h _{FE}	I _C =5A, V _{CE} =2V DC	1.2	60	
		I _C =10ADC, V _{CE} =2V	6	30	
Collector Emitter Saturation Voltage	V _{CE (sat)}	I _C =10A DC, I _B =2A DC	--	1.5	V DC
		I _C =15A DC, I _B =3A DC		5	
		I _C =10A DC, I _B =2A DC, T _C = 100°C		2.5	
Base Emitter Saturation Voltage	V _{BE(sat)}	I _C =10A DC, I _B =2A DC		1.6	
		I _C =10A DC, I _B =2A DC, T _C = 100°C			
Dynamic Characteristic					
Current-Gain — Bandwidth Product	f _T	I _C =500mAdc, V _{CE} =10Vdc, f _{test} =1KHz	6	28	MHz
Output Capacitance	C _{ob}	V _{CB} = 10V DC, I _E = 0, f _{test} =1KHz	125	500	pF
Switching Characteristics					
Resistive Load					
Delay Time	t _d	(V _{CC} =250 V, I _C = 10A I _{B1} = I _{B2} = 2A, t _p = 100 s Duty Cycle ≤ 2%	--	0.05	u s
Rise Time	t _r			1	
Storage Time	t _s			4	
Fall Time	t _f			0.7	
Inductive Load, Clamped					
Storage Time	t _s	I _C = 10 A(pk), V _{clamp} = Rated V _{CEX} , I _{B1} = 2A V _{BE(OFF)} = 5V DC, T _C = 100°C	--	5	u s
Fall Time	t _f			1.5	
			Typical		
Storage Time	t _s	I _C = 10 A(pk), V _{clamp} = Rated V _{CEX} , I _{B1} = 2A V _{BE(OFF)} = 5V DC, T _C = 25°C	2		u s
Fall Time	t _f		0.09		

(1) Pulse Test : Pulse Width = 300 s, Duty Cycle = 2%

Typical Characteristics Curves




Figure 1. DC Current Gain




Figure 2. Collector Saturation Region




Figure 3. "On" Voltages




Figure 4. Temperature Coefficients




Figure 5. Turn-On Time




Figure 6. Turn-Off Time




Figure 7. Forward Bias Safe Operating Area




Figure 8. Reverse Bias Safe Operating Area




Figure 9. Power Derating





Figure 10. Thermal Response


Package Details



DIM	MIN	MAX
A	--	39.37
B	--	22.22
C	6.35	8.5
D	0.96	1.09
E	--	1.77
F	29.9	30.4
G	10.69	11.18
H	5.2	5.72
J	16.64	17.15
K	11.15	12.25
L	--	26.67
M	3.84	4.19

PIN CONFIGURATION

- 1. BASE
- 2. EMITTER
- 3. COLLECTOR



Part Number Table

Description	Part Number
Bipolar Transistor, PNP, 400V, 15A, TO-3	2N6547..

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.