

FLAT HEAT PIPE / MHP-1520A150A

General Specification

Item		Description
Part Number		MHP-1520A150A
Material of Container		Aluminium 3003
Wick Structure		Groove
Working Fluid		Acetone
Dimension	Thickness	1.5 mm
	Width	20.0 mm
	Length	150 mm
Weight		8g (Unit Weight)
Q _{max}	Horizontal	9 W (at 50°C)
	Vertical	25.0 W (at 50°C)
Typical Thermal Resistance		<0.25°C / W (Average)
Operating Inclination, Ø		0 ~ 90°
Operating Temperature		-40 ~ 180°C

Dimensions

The dimensional attributes of this shall conform to the following figure.



Thickness (t)	Width (W)	Length (L)	Ineffective Length (a)	Ineffective Length (b)
1.5 ± 0.1	20.0 ± 0.15	150.0 + 0/-1	3.0	3.0

Dimensions are in mm

Material

Container	Aluminium 3003
Working Fluid	Acetone
Surface Treatment	None


AMEC Thermasol

1-2 Steam Mill Lane, Great Yarmouth, Norfolk, NR31 0HP


Telephone: +44(0) 1493 668622

Email: sales@amecthermasol.co.uk Website: www.amecthermasol.co.uk

FLAT HEAT PIPE / MHP-1520A150A



Qmax Test Apparatus



AMEC Thermasol

1-2 Steam Mill Lane, Great Yarmouth, Norfolk, NR31 0HP

Telephone: +44(0) 1493 668622

Email: sales@amecthermasol.co.uk **Website:** www.amecthermasol.co.uk

FLAT HEAT PIPE / MHP-1520A150A




Fig. 4 Maximum Heat Transfer Rate at $\theta=90^\circ$, Tadia=50°C,
Chiller=25°C (Le=20mm, La=50mm, Lc=30mm)




Fig. 5 Maximum Heat Transfer Rate vs. Inclination at Tadia=50°C,
Chiller=25°C (Le=20mm, La=50mm, Lc=30mm)

AMEC Thermasol

1-2 Steam Mill Lane, Great Yarmouth, Norfolk, NR31 0HP

Telephone: +44(0) 1493 668622

Email: sales@amecthermasol.co.uk **Website:** www.amecthermasol.co.uk



FLAT HEAT PIPE / MHP-1520A150A

Operating Range

	Operating	Storage
Temperature	-40 ~ 180°C	-10 ~ 40°C
Humidity	80 % RH Max (at 60°C)	80 % RH Max (at 60°C)
Tilt Angle	0 ~ 90 degree	Horizontal

High Temperature Leak Test

Every manufactured component is sealed with a mechanical pinch system. The mechanical pinch of container results in a cold weld seal. The average leak temperature is about 170°C.




Fig. 6 Leak Test at High Temperature

AMEC Thermasol

1-2 Steam Mill Lane, Great Yarmouth, Norfolk, NR31 0HP

Telephone: +44(0) 1493 668622

Email: sales@amecthermasol.co.uk Website: www.amecthermasol.co.uk

FLAT HEAT PIPE / MHP-1520A150A

Thermal Response Test

A thermal response test and vacuum leakage check are carried out to ensure its operation. The experimental test bench is schematically shown in Fig.6. Water bath temperature, (**Tw**) is set at 50°C and the temperature of other end, **Tt** is measured immediately after it is placed vertically into the water bath. The criterion for acceptance is 5°C ($T_w - T_t$).




Fig. 7 Thermal Response Test Apparatus

ANNOTATION

All specifications shown herein are typical values and are not guaranteed. It is recommended to test in the application for suitability.

AMEC Thermasol

1-2 Steam Mill Lane, Great Yarmouth, Norfolk, NR31 0HP

Telephone: +44(0) 1493 668622

Email: sales@amecthermasol.co.uk Website: www.amecthermasol.co.uk