

# SPECIFICATION FOR APPROVAL

CUSTOMER : \_\_\_\_\_

CUSTOMER PART NO. : \_\_\_\_\_

|                      |                                                                                                  |                                                                                                                                                                                    |                                                                                                    |
|----------------------|--------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|
| CUSTOMER<br>APPROVED | APPROVED BY<br> | CHECKED BY<br>  | PREPARED BY<br> |
|----------------------|--------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|

MODEL NO. : AG06024XB257B03 P.S. \_\_\_\_\_

DESCRIPTION : \_\_\_\_\_

SPEC NO. : SA-0120190219009

ISSUE DATE : 2025.11.06

REVISION : A03

THIS OFFER IS MADE ACCORDING TO YOUR CURRENT INQUIRY.  
UNLESS OTHERWISE REVISED, THIS SPECIFICATION WILL BE FINAL FOR  
ALL FUTURE PRODUCTION OF ORDERS FROM YOUR RESPECTED COMPANY

KINDLY STUDY IN DETAILS AND RETURN TO US THE DUPLICATE DULY  
SIGNED AS YOUR CONFIRMATION OF SAME.



**ADDA CORPORATION**

|                       |
|-----------------------|
| <b>Revised Record</b> |
|-----------------------|

協成電機股份有限公司  
研發處  
2025.11.06  
發行章

DATA-SHEET

Engineering

Printed On: 25/11/06

## BRUSHLESS AXIAL COOLING FANS

|                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                           |                                                                                                                                               |             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| Customer                                                                                                                                                                                                                                                                                                                                                                                                                                         | :                         |                                                                                                                                               | Ref: (RoHS) |
| Adda Model No                                                                                                                                                                                                                                                                                                                                                                                                                                    | :                         | AG06024XB257B03                                                                                                                               |             |
| Samples attached                                                                                                                                                                                                                                                                                                                                                                                                                                 | :                         | Piece(s),                                                                                                                                     |             |
| Safety Approval                                                                                                                                                                                                                                                                                                                                                                                                                                  | :                         | UL,CUL,TUV,CE,UKCA                                                                                                                            |             |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                           | TUV:EN 62368-1: 2014+A11<br>UL:UL 507<br>CE: EN 61000-6-1: 2019<br>EN 61000-6-3: 2021<br>UKCA: BS EN 61000-6-1: 2019<br>BS EN 61000-6-3: 2021 |             |
| <u>Specifications</u>                                                                                                                                                                                                                                                                                                                                                                                                                            |                           |                                                                                                                                               |             |
| ITEM                                                                                                                                                                                                                                                                                                                                                                                                                                             | SPECIFICATION / CONDITION |                                                                                                                                               |             |
| DIMENSIONS                                                                                                                                                                                                                                                                                                                                                                                                                                       | :                         | 60x60x25 mm                                                                                                                                   |             |
| BEARING TYPE                                                                                                                                                                                                                                                                                                                                                                                                                                     | :                         | TWO BALL                                                                                                                                      |             |
| RATED VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                    | :                         | 24.0 VDC                                                                                                                                      |             |
| OPERATING VOLTAGE RANGE                                                                                                                                                                                                                                                                                                                                                                                                                          | :                         | 22.8 VDC — 25.2 VDC                                                                                                                           |             |
| OPERATING DUTY CYCLE RANGE                                                                                                                                                                                                                                                                                                                                                                                                                       | :                         | 30% ~ 100%                                                                                                                                    |             |
| START-UP DUTY CYCLE                                                                                                                                                                                                                                                                                                                                                                                                                              | :                         | 30% Max (AT RATED VOLTAGE)                                                                                                                    |             |
| REAL CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                     | :                         | 0.18 Amp                                                                                                                                      |             |
| REAL POWER                                                                                                                                                                                                                                                                                                                                                                                                                                       | :                         | 4.32 Watt                                                                                                                                     |             |
| RATED CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                    | :                         | 0.23 Amp + 10 %MAX (Duty cycle 100%)                                                                                                          |             |
| RATED POWER                                                                                                                                                                                                                                                                                                                                                                                                                                      | :                         | 5.52 Watt (Duty cycle 100%)                                                                                                                   |             |
| RATED SPEED                                                                                                                                                                                                                                                                                                                                                                                                                                      | :                         | 7000 RPM ± 10 % (Duty cycle 100%)                                                                                                             |             |
| (IN FREE AIR AT RATED VOLTAGE)                                                                                                                                                                                                                                                                                                                                                                                                                   |                           |                                                                                                                                               |             |
| AIR FLOW                                                                                                                                                                                                                                                                                                                                                                                                                                         | :                         | 36.977 CFM (min.: 33.279 CFM)                                                                                                                 |             |
| AIR FLOW                                                                                                                                                                                                                                                                                                                                                                                                                                         | :                         | 1.046 CMM (min.: 0.941 CMM)                                                                                                                   |             |
| (IN FREE AIR AT RATED VOLTAGE)                                                                                                                                                                                                                                                                                                                                                                                                                   |                           |                                                                                                                                               |             |
| STATIC AIR PRESSURE                                                                                                                                                                                                                                                                                                                                                                                                                              | :                         | 0.622 Inch H <sub>2</sub> O (min.: 0.503 Inch H <sub>2</sub> O)                                                                               |             |
| STATIC AIR PRESSURE                                                                                                                                                                                                                                                                                                                                                                                                                              | :                         | 15.798 mm H <sub>2</sub> O (min.: 12.796 mm H <sub>2</sub> O)                                                                                 |             |
| (IN FREE AIR AT RATED VOLTAGE)                                                                                                                                                                                                                                                                                                                                                                                                                   |                           |                                                                                                                                               |             |
| NOISE LEVEL                                                                                                                                                                                                                                                                                                                                                                                                                                      | :                         | 46.7 dB (A) (max.: 50.7 dB(A))                                                                                                                |             |
| MOTOR PROTECTION                                                                                                                                                                                                                                                                                                                                                                                                                                 | :                         | BY IC                                                                                                                                         |             |
| POLARITY PROTECTION                                                                                                                                                                                                                                                                                                                                                                                                                              | :                         | YES                                                                                                                                           |             |
| CONNECTION LEAD TYPE                                                                                                                                                                                                                                                                                                                                                                                                                             | :                         | WIRE, AWG# 26                                                                                                                                 |             |
| LIFE EXPECTANCY                                                                                                                                                                                                                                                                                                                                                                                                                                  | :                         | 70000 Hours at 40°C / 65% RH                                                                                                                  |             |
| NET WEIGHT                                                                                                                                                                                                                                                                                                                                                                                                                                       | :                         | 62 Gram.                                                                                                                                      |             |
| PACKING                                                                                                                                                                                                                                                                                                                                                                                                                                          | :                         | 300 pcs. Per Export Carton.                                                                                                                   |             |
| <p>* If no PWM signal is present (no connection to the PWM drive signal),<br/>the fan should be run at rated speed RPM.</p> <p>* The fan should be run,at Max of start -up duty cycle.</p> <p>Unless otherwise stated, the relative humidity is 65%, and the temperature is 25°C<br/>for the standard testing.</p> <p>Should you have any doubt, please refer to the environmental conditions specified in the<br/>acknowledgement document.</p> |                           |                                                                                                                                               |             |
| ADDA CORPORATION                                                                                                                                                                                                                                                                                                                                                                                                                                 |                           | Model No.: AG06024XB257B03                                                                                                                    | Page 1/6    |



## SPECIFICATION

### 1 · 0 SCOPE

- 1.1 If the information or other related document is inconsistent with this acknowledgement document, please refer to the acknowledge document.
- 1.2 This documentation defines the mechanical & electrical characteristics of DC brushless fans.
- 1.3 The specification of this product is described in details in the acknowledgement document. No guarantee is given to our product under the use of over specifications.
- 1.4 For any change or amendment to the specifications, such change will be noticed in writing beforehand.
- 1.5 If the product is used on the MIS system, please specify the specification in the purchase order.

### 2 · 0 MATERIAL

- 2 · 1 Frame : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 2 Fan Blade : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 3 RoHS : ( V ) YES
- HF : ( ) YES


### 3 · 0 DIMENSIONS & CONSTRUCTION

All dimensions, Direction of rotation and air flow were specified as per drawing attached.

### 4 · 0 CHARACTERISTICS & DEFINITION

- 4 · 1 All rated characteristics were specified as per data sheet enclosed.
- 4 · 2 Rated Current : Rated Current shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 3 Rated Speed : Rated Speed shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 4 Start Voltage : The voltage which is able to start the fan to operate by suddenly switching ' ON ' .
- 4 · 5 Input Power : Input Power shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 6 Locked Rotor Current : Locked current shall be measured within one minute of rotor locked, after 3 minutes of continuous rotation at rated voltage in clean air.
- 4 · 7 Air Flow & Static Pressure : The air flow data and static pressures should be determined in accordance with AMCA-210 standard in a doublechamber testing with intake – side measurement.
- 4 · 8 Noise Level : The measurement of noise level is carried out with reference to ISO7779 in a semi-anechoic chamber with the microphone positioned 1 meter from the fan intake. Testing fan shall be hung in the free air.

#### NOISE LEVEL MEASUREMENT



## SPECIFICATION

### 5.0 MECHANICAL INSPECTION

#### 5.1 Rotation Direction

Counterclockwise when look into impeller side.

#### 5.2 Protection

All fans have integrated protection against locked rotor condition so that there will be no damage to winding or any electronic component.

Restarting is automatic as soon as any constraint to rotation has been released.

As fan placed at dead angle position, and the switch was changed from off to on. Restarting was automatic normal as soon as and proved that this fan is good fan.

#### 5.3 Locked Rotor Protection

No damage shall be found after 72 hours continuously at condition of rotation locked.

Restarting is automatic as soon as constraint to running has been released.

#### 5.4 Avoid the damage, check the correct voltage and proper polarity before connecting with power.

#### 5.5 Free Drop Shock

In minimum package condition, the fan should withstand drops on any three faces from a height of 30cm onto a wood board of 10mm thick.

#### 5.6 Please do not stick a grease and/or an oil to the fan housing or blade which may have a harmful influence by a chemical reaction at high humidity.

#### 5.7 If the fan is reinstalled, please pay special attention to the noise due to the vibration (or resonance).

#### 5.8 During the testing of the fan, please make sure the finger guard is used for safety.

### 6.0 ELECTRICAL INSPECTION

#### 6.1 Insulation Resistance

Not less than 10M ohm between housing and positive end of lead wire (red) at 500V DC.

#### 6.2 Dielectric Strength

No damage should be found at 500 VAC for 60 seconds, measured with 1mA trip current between housing and positive end of lead wire.

#### 6.3 Life Expectancy

The continuous duty life at given temperature after which, 90% of testing units shall still be running.

#### 6.4 While the fan is running, do not intentionally lock the fan for a long time since the overheating of the motor produced by the long-time locking will damage the fan.

### 7.0 ENVIRONMENTAL

#### 7.1 Improper use such as disassembling the fan, being covered with dust, or dipping the fan in water that results in defects is not covered in the warranty. Do not use the fan in the environment with corrosive air or liquid.

#### 7.2 Operating Temperature / Humidity

-10°C to +70°C at humidity 65%+/-20% RH.

#### 7.3 Storage Temperature

All function shall be normal after 500 hours storage at -40°C to +70 °C with a 24 hour recovery period at room temperature.

#### 7.4 Humidity

After 96 hours, 95% RH, 40+/-2°C per MIL-STD-202F, method 103B humidity test, the measured data on insulation resistance and dielectric strength shall meet the specification.

#### 7.5 Do not place or store the fan in the environment with high/low temperature/humidity.

If the fan is stored for more than 6 months, functional test is highly recommended before using.




## SPECIFICATION

### 8.0 REMARKS

- 8.1 Material and construction are subject to change without advance notice. The changes should be within specification.
- 8.2 All fans shall meet the quality inspection under sampling plan MIL-STD-105E as follow:

|          |       |
|----------|-------|
| Critical | 0.25% |
| Major    | 1.00% |
| Minor    | 2.50% |

### 9.0 OUTLINE STYLING & DIMENSIONS



LEAD WIRES : UL 1061, AWG26, L =  $320 \pm 10$  mm  
Red = positive ; Black = negative.  
White = FG ; Blue = PWM

### 10.0 Notes:


- 10.1 Please do not touch and push Fan Blade with fingers or others, fan blade and ball bearings may be damaged and it causes noise defect.
- 10.2 Do not carry the fan by its lead wires.
- 10.3 If the fan does not have the polarity protection function, the connection of the colored wires should be red + red, and black + black, or else the fan will be damaged in no time.
- 10.4 For the models without reverse connection of polarity protection, please do not connect the lead wire in reverse
- 10.5 Please don't install this fan in series with 2x voltage inputs. For example, if a single fan rated at 12V, then don't install two of them in series with 24V input.
- 10.6 Every specific fan is designed for its certain application (project). Therefore, if you want to use this fan in other application (project), please inform ADDA first so that we can confirm whether there is any issue which might be incurred from the reason of this different application (project) or not.
- 10.7 The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy in the Test Reports (L10 and MTTF Report) that relate to this fan is for reference only and shall not construe any kind of warranty of ADDA to the life of any specific fan, either expressed or implied.
- 10.8 The period of product warranty, unless otherwise agreed by ADDA in written, shall be 12 months starting from the date of production.
- 10.9 In Lead Wire, there is a possibility to come off from frame.
- 10.10 In order to avoid abnormal bumping or interference caused by deformed impeller when fan is fastened, suggested distance of at least 0.5mm is strongly reserved in front of the frame (the sight from the impeller face).
- 10.11 Hot swapping or Hot plugging is not allowed to cause damage to fans. Notice in advance is strongly requested if design for Hot swapping or Hot plugging is needed.



## PROVISION OF DIGITAL PWM SPEED CONTROL & LOCKED SIGNAL(F.G)

- OUTPUT OF LOCKED SIGNAL -----OPEN DRAIN TYPE

(External signal function design is decided by customer)



\*MOSFET Q1 AT "ON" POSITION

DRAIN CURRENT----- $I_D=5\text{mA MAX}$

SATURATION VOLTAGE----- $V_{OL}=1\text{V MAX}$

\*MOSFET Q1 AT "OFF" POSITION


RELEASE VOLTAGE----- $V_{OH}=30\text{V MAX}$


\*DIGITAL PWM SPEED CONTROL POSITION

PWM INPUT VOLTAGE HIGH----- $V_{IH}=3\text{V}\sim 5.5\text{V}$

PWM INPUT VOLTAGE LOW----- $V_{IL}=0\text{V}\sim 0.5\text{V}$

\*PWM INPUT FREQUENCY-----  $FPWM:18\text{KHZ}\sim 30\text{KHZ}$





# CERTIFICATE OF COMPLIANCE

Certificate Number E132139  
Report Reference E132139-20171023  
Issue Date 2020-APRIL-20

Issued to: ADDA CORP  
NO 6 E SECTION INDUSTRY 6 RD  
PING TUNG  
900 TAIWAN

This certificate confirms that  
representative samples of COMPONENT - FANS, ELECTRIC  
Refer to addendum page for Models/Product

Have been investigated by UL in accordance with the  
component requirements in the Standard(s) indicated on  
this Certificate. UL Recognized components are incomplete  
in certain constructional features or restricted in  
performance capabilities and are intended for installation in  
complete equipment submitted for investigation to UL LLC.


Standard(s) for Safety: UL 507, Electric Fans  
CSA C22.2 No. 113-15, Fans and Ventilators

Additional Information: See the UL Online Certifications Directory at  
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark. Only  
the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified  
and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please  
contact a local UL Customer Service Representative at <http://ul.com/aboutus/locate80nc>



# CERTIFICATE OF COMPLIANCE

Certificate Number E132139  
Report Reference E132139-20171023  
Issue Date 2020-APRIL-20

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Component – DC Fans

Model Nos.

AG06024X(b)257(c)03  
AG06024U(b)257(c)03  
AG06024H(b)257(c)03  
AG06024M(b)257(c)03  
AG06024L(b)257(c)03  
AG06024D(b)257(c)03

\*AB1224UB-Y0(e)  
\*AB1224HB-Y0(e)  
\*AB1224MB-Y0(e)  
\*AB1224LB-Y0(e)  
\*AB1224DB-Y0(e)

AD0305HX-K76  
AD0305MX-K76  
AD0305LX-K76  
AD0305DX-K76  
AD0305DX-K70

Note: Above (b) may be X or B; (c) may be 1, 2, 3, 9, B or F; (e) may be 9, B or F.



*Brue Mahlenholz*

Brue Mahlenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations>



# Zertifikat Certificate



Zertifikat Nr. Certificate No.  
R 50111797

Blatt Page  
0105

| Ihr Zeichen Client Reference | Unser Zeichen Our Reference | Ausstellungsdatum | Date of Issue |
|------------------------------|-----------------------------|-------------------|---------------|
| 12101162/ST250917            | ZTW1-YML- 11011138 097      | 11.10.2017        | (day/mo/yr)   |

## Genehmigungsinhaber License Holder

Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Fertigungsstätte Manufacturing Plant

ADDA Electric Machinery Technology  
(Kunshan), Co., Ltd.  
No. 88, Jiangfeng Road  
Zhangpu Town  
Kunshan City, Jiangsu Province  
P. R. China

## Prüfzeichen Test Mark



Bauart geprüft  
Sicherheit  
Regelmäßige  
Produktions-  
überwachung  
  
www.tuv.com  
ID 2000000000

## Geprüft nach Tested acc. to

EN 60950-1:2006+A11+A1+A12+A2

Zertifiziertes Produkt (Geräteidentifikation)  
Certified Product (Product Identification)

Lizenzentgelte - Einheit  
License Fee - Unit

Ventilator (DC Fan)

wie Blatt (as page) 01

Ergänzung (Addition)

Bezeichnung : AG06024Z122257Z303 (ADDA, BERFLO)  
(Type Designation)

1

Z1 steht für : X, U, H, M, L oder (or) D  
(stands for)

1

Z2 steht für : B oder (or) X  
(stands for)

1

Z3 steht für : 1, 2, 3, 9, B oder (or) F  
(stands for)

Nennspannung : DC 24V

(Rated Voltage)

Nennstrom : siehe Anlage

(Rated Current) (see appendix)

ANLAGE (Appendix): 1.87

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde und es bestätigt die Konformität des Produktes mit den oben genannten Standards und Prüfgrundlagen. Zusätzliche Anforderungen in Ländern, in denen das Produkt in Verkehr gebracht werden soll, müssen zusätzlich betrachtet werden. Die Herstellung des zertifizierten Produktes wird überwacht.  
This certificate is based on our Testing and Certification Regulation and states the conformity of the product with the standards and testing requirements as indicated above. Any additional requirements in countries where the product is going to be marketed have to be considered additionally. The manufacturing of the certified product is subject to surveillance.

TÜV Rheinland LGA Products GmbH - Tillystraße 2 - 90431 Nürnberg

Tel.: (+49/221) 8 06 - 13 71 e-mail: cert-validity@de.tuv.com  
Fax: (+49/221) 8 06 - 39 35 http://www.tuv.com/safety

Zertifizierungsstelle



Dipl.-Ing. (FH) A. Klinker

# Zertifikat Certificate



Zertifikat Nr. Certificate No.  
R 50111797

Blatt Page  
0111

| Ihr Zeichen Client Reference | Unser Zeichen Our Reference | Ausstellungsdatum | Date of Issue |
|------------------------------|-----------------------------|-------------------|---------------|
| 238014414                    | ZTW1-YML- 11011138 103      | 13.08.2020        | (day/mo/yr)   |

## Genehmigungsinhaber License Holder

Adda Corporation  
6, East Section, Industry 6 Road,  
Pingtung City 900  
Taiwan, R.O.C.

## Fertigungsstätte Manufacturing Plant

ADDA Electric Machinery Technology  
(Kunshan), Co., Ltd.  
No. 88, Jiangfeng Road  
Zhangpu Town  
Kunshan City  
Jiangsu  
P.R. China

## Prüfzeichen Test Mark



Bauart geprüft  
Sicherheit  
Regelmäßige  
Produktions-  
überwachung

www.tuv.com  
ID 2000000000

## Geprüft nach Tested acc. to

EN 62368-1:2014+A11

**Zertifiziertes Produkt (Geräteidentifikation)**  
**Certified Product (Product Identification)**

**Lizenzentgelte - Einheit**  
**License Fee - Unit**

Ventilator (DC Fan)

wie Blatt (as page) 01

Änderung  
(Change)

Prüfgrundlage : siehe oben  
(Test Requirement) (see above)

Vermerke: Dieses Netzgerät ist auch geprüft und  
Klassifiziert als MS3 in Tabelle 35 von Abschnitt 8.2.1 in  
Standards EN 62368-1:2014. Wenn nicht anders angegeben,  
anders angegeben, liegen die klassifizierten Bedingungen  
unter der Nennspannung und der normalen Drehzahl des  
Lüfterblatts (Remark: The equipment is also classified as MS3  
according to Table 35 of sub-clause 8.2.1 in standard  
EN 62368-1:2014. Unless otherwise stated the classified  
conditions are under rated voltage and normal rotational  
speed of the fan blade.)

ANLAGE (Appendix): 1.91

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde und es bestätigt die Konformität  
des Produktes mit den oben genannten Standards und Prüfgrundlagen. Zusätzliche Anforderungen  
in Ländern, in denen das Produkt in Verkehr gebracht werden soll, müssen zusätzlich  
betrachtet werden. Die Herstellung des zertifizierten Produktes wird überwacht.  
This certificate is based on our Testing and Certification Regulation and states the conformity  
of the product with the standards and testing requirements as indicated above. Any additional  
requirements in countries where the product is going to be marketed have to be considered  
additionally. The manufacturing of the certified product is subject to surveillance.

**TÜV Rheinland LGA Products GmbH - Tillystraße 2 - 90431 Nürnberg**  
Tel.: (+49/221)8 06 - 13 71 e-mail: cert-validity@de.tuv.com  
Fax: (+49/221)8 06 - 39 35 http://www.tuv.com/safety

Zertifizierungsstelle



Dipl.-Ing. (FH) A. Klinker