


Isolated DC DC Converter multicomp^{PRO}

RoHS
Compliant



Features


- 7PIN SIP package
- No-load input current as low as 5mA
- Continuous short-circuit protection
- High efficiency up to 87%
- Unregulated output types
- 1.5KVDC to 3KVDC isolation
- Operating temperature:-40°C to +105°C
- Industry standard pinout

Specification Table

Typical @ T_A=25°C, nominal input voltage and rated output current unless otherwise specified

Part Number	Output Voltage	Output Current	Efficiency	Capacitive Load μ F
	V DC	mA	%TYP	Max.
MP14DC-05S05NP	5	200	84	2400
MP14DC-24S05NP				
MP14DC-05D12NP	± 12	± 42	85	± 220
MP14DC-05D15NP	± 15	± 34	84	± 220

Temperature Derating Graph



Input Specifications

Parameters	Conditions	Typ	Units
Voltage Range	V _{o,lo} Nom @V _{in} :3.3V, 5V, 9V	± 10	%
Filter	V _{o,lo} Nom@ V _{in} :12V,15V,24V	± 20	

Newark.com/multicom-p-pro
Farnell.com/multicom-p-pro
sg.element14.com/b/multicom-p-pro

multicom^{PRO}

Isolated DC DC Converter **multicomp**PRO

Output Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Tolerance	100% full load	-	-	±5	%
Short Circuit Protection	Continuous				
Line Regulation	For 1.0% OF Vin	-	1.2	-	%
Load Regulation	3.3V (10% to 100% F.L)		15	20	
	5V (10% to 100% F.L)		10	15	
	9V (10% to 100% F.L)		8	10	
	12V (10% to 100% F.L)		7	10	
	15V (10% to 100% F.L)		6	10	
	24V (10% to 100% F.L)		5	10	
Ripple & Noise	BW=DC to 20MHz @Vo:3.3V, 5V, 9V, 12V,15V		30	75	mVp-p
	BW=DC to 20MHz @ Vo:24V		50	100	


General Specifications

Parameters	Conditions	Min	Typ	Max	Units
Isolation Resistance	500V DC	1000			MΩ
Isolation Capacitance	Input-output, 100KHz/0.1V		20		pF
Switching Frequency	Full load, nominal input @3.3V,5V Vin		215/370		KHz
	Full load, nominal input @other Vin		250		
Operating Temperature		-40		+105	°C
Storage Temperature		-55		+125	
Humidity	Non Condensing			95	%
Cooling	Free air Convection				
Case material	DAP				
MTBF	MIL-HDBK-217F@25°C	3500000			Hours
Weight			2.1		g
Dimensions			9.5 × 6 × 10		mm

Electromagnetic Compatibility (EMC)


EMI	CE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
	RE Max.	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
EMS	ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV perf. Criteria B

Tolerance Envelope Graph



Isolated DC DC Converter **multicomp**PRO

Recommended Test Circuit



Vin	Cin	Single Vout	Cout	Dual Vout	Cout
3.3V DC	4.7 μ F/25V	3.3V DC	10 μ F/16V	$\pm$ 3.3V DC	$\pm$ 4.7 μ F/16V
5V DC	4.7 μ F/25V	5V DC	10 μ F/16V	$\pm$ 5V DC	$\pm$ 4.7 μ F/16V
9V DC	4.7 μ F/25V	9V DC	2.2 μ F/16V	$\pm$ 9V DC	$\pm$ 1 μ F/16V
12V DC	2.2 μ F/25V	12V DC	2.2 μ F/25V	$\pm$ 12V DC	$\pm$ 1 μ F/25V
15V DC	2.2 μ F/25V	15V DC	1 μ F/25V	$\pm$ 15V DC	$\pm$ 1 μ F/25V
24V DC	1 μ F/50V	24V DC	1 μ F/50V	$\pm$ 24V DC	$\pm$ 1 μ F/50V

EMC (CLASS B) compliance circuit





Fig.1

EMC recommended circuit value table

EMI	C1	4.7 μ F /50V
	C2	4.7 μ F /50V
	CY	1nF/4kV
	C3, C4	Recommended Test Circuit
	L	6.8 μ H

Markings and Dimensions



PIN Connection

PIN	1	2	4	5	6
Single	+Vin	-Vin	-Vout	No Pin	+Vout
Dual	+Vin	-Vin	-Vout	Com	+Vout

Part Number Table

Description	Part Number
DC To DC Converter, Isolated, 1W, 200mA, 5Vin, 5Vout	MP14DC-05S05NP
DC To DC Converter, Isolated, 1W, 200mA, 24Vin, 5Vout	MP14DC-24S05NP
DC To DC Converter, Isolated, 1W, $\pm$ 42mA, 5Vin, $\pm$ 12Vout	MP14DC-05D12NP
DC To DC Converter, Isolated, 1W, $\pm$ 34mA, 5Vin, $\pm$ 15Vout	MP14DC-05D15NP

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO