

3m Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

Product ID: MXTMMHQ3M



The MXTMMHQ3M High Resolution VGA Cable (3-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor

- High quality VGA connectors with molded PVC strain relief

General

UPC	065030847711
Package Quantity	1
Warranty	Lifetime

Physical & Environmental

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	9.8 ft [3.0 m]
Product Width	1.3 in [33.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	13.3 oz [377.0 g]
Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

Hardware

Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1

Packaging & In-the-Box

Included in Package	1 - 3m Coax High Resolution Monitor VGA Cable - HD15 M/M
---------------------	--

Package Width	13.3 in [33.8 cm]
Package Depth	5.2 in [13.3 cm]
Package Height	1.9 in [49 mm]
Shipping (Package) Weight	13.5 oz [382 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	VGA
Connector 2 (Quantity)	1
Connector 2	VGA

****Product appearance and specifications are subject to change without notice.***