

UT-A SERIES

High Temperature Power Resistors



*RoHS COMPLIANT

Features

- Resistances from 10 Ω to 4.5K Ω
- Resistance tolerances as low as ±1 %
- Power rating: 1 to 10 watts
- Excellent pulse handling
- Low TCR: ±30 PPM/°C standard
- Silicone coated power resistor
- AEC-Q200 compliant
- RoHS compliant*

Applications

- Energy and storage
- Industrial power supplies
- Inverters and motor drives
- Capacitor recharge and discharge
- Voltage regulators
- Telecommunications

Sustainability

- High pallet density for lower CO₂
- Eco-logistics-friendly packing
- Recyclable ESD-safe packaging
- Corrosion-resistant for longevity

Product Overview

Bourns® UT-A Series high-temperature power resistors are AEC-Q200 compliant wirewound components designed to deliver stable, accurate performance in demanding power applications exposed to extreme thermal stress. With a wide power range, resistance values from 10 Ω to 4.5 kΩ, and an operating temperature range of -55 °C to +150 °C, the UT-A Series enables engineers

to standardize on a single qualified resistor family across powertrain, braking, and power conversion systems. Built with a ceramic core and flame-resistant silicone coating, these resistors provide long-term reliability, tight tolerance options, and low TCR to support high-reliability, safety-critical designs.


Specifications

Specification	Value
Tolerance	±1 % to ±10 % (1 % Standard)
Temperature Coefficient	±30 PPM/°C (Other TCR values available - Contact Bourns)
Resistance Range	10 Ω to 4.5K Ω (UT10-A: 1K Ω max.)
Operating Temperature Range	-55 °C to +150 °C
Maximum Working Voltage	$\sqrt{P \cdot R}$
Dielectric Strength	UT1A: 500 VAC Other models: 1000 VAC
Construction	• Centerless ground ceramic core, Matte tin over copper • Flame-resistant/high temperature/trivalent/inorganic silicone coating • All welded terminations

Environmental Performance

Specification	ΔR
Short Time Overload	±1 %
High Temperature Exposure (Storage)	
Biased Humidity	
Operational Life	
Shock/Vibration	
Temperature Cycling	
Resistance to Soldering Heat	

Power Derating Curve



Contact Information


www.bourns.com	Phone	Email
Asia-Pacific	+886-2 2562-4117	asiacus@bourns.com
Europe	+36 88 885 877	eurocus@bourns.com
Mexico	+52 614 478 0400	mexicus@bourns.com
The Americas	+1-951 781-5500	americus@bourns.com

* RoHS Directive 2015/863, Mar 31, 2015 and Annex.
Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



Specifications and Product Dimensions


 DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Model	Power Rating (W)	Dimensions			Designed to Mil-R-26 / MIL-R-39007
		A	B ³	C ¹	
UT1A	1.0	$\frac{10.3 \pm 1.6}{(.406 \pm .062)}$	$\frac{2.4 \pm 0.8}{(.094 \pm .031)}$	$\frac{\mathbf{0.5 \pm 0.05}}{(.020 \pm .002)}$ $\frac{0.6 \pm 0.05}{(.025 \pm .002)}$	RW-70
UT2	1.5	$\frac{8.9 \pm 1.6}{(.350 \pm .062)}$	$\frac{4.0 \pm 0.8}{(.156 \pm .031)}$	$\frac{0.8 \pm 0.05}{(.032 \pm .002)}$	—
UT2B	3.0	$\frac{14.2 \pm 1.6}{(.560 \pm .062)}$	$\frac{4.7 \pm 0.8}{(.187 \pm .031)}$		RW-79
UT2C	3.0	$\frac{12.7 \pm 1.6}{(.500 \pm .062)}$	$\frac{6.4 \pm 0.8}{(.250 \pm .031)}$	$\frac{\mathbf{1.0 \pm 0.05}}{(.040 \pm .002)}$ $\frac{0.8 \pm 0.05}{(.032 \pm .002)}$	—
UT3	4.0	$\frac{17.1 \pm 1.6}{(.675 \pm .062)}$	$\frac{6.9 \pm 0.8}{(.270 \pm .031)}$	$\frac{\mathbf{1.0 \pm 0.05}}{(.040 \pm .002)}$ $\frac{0.8 \pm 0.05}{(.032 \pm .002)}$	—
UT5	5.0	$\frac{22.2 \pm 1.6}{(.875 \pm .062)}$	$\frac{7.9 \pm 0.8}{(.312 \pm .031)}$	$\frac{1.0 \pm 0.05}{(.040 \pm .002)}$	RW-74
UT5A	5.0	$\frac{24.6 \pm 1.6}{(.970 \pm .062)}$	$\frac{5.2 \pm 0.8}{(.250 \pm .031)}$	$\frac{0.8 \pm 0.05}{(.032 \pm .002)}$	—
UT6	5.0	$\frac{26.0 \pm 1.6}{(1.025 \pm .062)}$	$\frac{7.9 \pm 0.8}{(.312 \pm .031)}$	$\frac{1.0 \pm 0.05}{(.040 \pm .002)}$	RW-67
UT7C	7.0	$\frac{31.0 \pm 1.6}{(1.220 \pm .062)}$	$\frac{7.9 \pm 0.8}{(.312 \pm .031)}$		—
UT10	10.0	$\frac{45.2 \pm 1.6}{(1.780 \pm .062)}$	$\frac{9.5 \pm 0.8}{(.375 \pm .031)}$		RW-78

Notes:

¹ Lead Diameter: 18 AWG = 0.040 " / 20 AWG = 0.032 " / 22 AWG = 0.025 " / 24 AWG = 0.020 " / 25 AWG = 0.018 ".

Where more than one lead is listed, the **bold** value is standard.

² For non-inductive windings, divide maximum resistance by 2.

³ For non-inductive windings where $R \leq 0.10$ ohms, tolerance is $+1.6/-0.0$ mm $(+0.063/-0.00$ ").

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



How to Order

UT 5 - 25R F 1 - A - TR14

Model _____

Power Rating Code _____
(See Specifications and Dimensions Table)

Resistance Code _____
For values $\leq 10K \Omega$,
"R" represents decimal point (Example: 25R = 25 Ω)
For values $> 10K \Omega$,
"K" represents decimal point (Example 1K5 = 1.5K Ω)

Tolerance _____
F = $\pm 1\%$ **
G = $\pm 2\%$
H = $\pm 3\%$
J = $\pm 5\%$
K = $\pm 10\%$

Internal Use _____

AEC-Q200 Compliant _____

Packaging Options _____
(Blank) = Bulk Packaging
-TR10 = Tape and Reel (10-inch Reel) *
-TR12 = Tape and Reel (12-inch Reel) *
-TR14 = Tape and Reel (14-inch Reel) *

* Please check the Standard Packaging Quantity Table for the correct reel size.

** Please Contact Bourns.

(Specific TCR values available on request.)

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



Performance Characteristics (AEC-Q200)			
Test	Method	Procedure	Test Limits ΔR
Short Time Overload	IEC 60115-1 4.13	2.5 X rated voltage for 5 sec.	$\pm 1 \%$
High Temperature Exposure (Storage)	AEC-Q200-REV E- Test 3 MIL-STD-202 Method 108	1000 hrs. @ T=150 °C. Unpowered. Measurement at 24 ± 2 hours after test conclusion.	$\pm 1 \%$
Biased Humidity	AEC-Q200-REV E- Test 7 MIL-STD-202 Method 103	1000 hours 85 °C / 85 % RH. TR Measurement at 250, 500, 750, and post 1000 hours.	$\pm 1 \%$
Operational Life	AEC-Q200-REV E- Test 8 MIL-STD-202 Method 108	At rated power, 25 °C for 1000 hours. TR Measurement at 250, 500, 750, and post 1000 hours.	$\pm 1 \%$
External Visual	AEC-Q200-REV E- Test 9 MIL-STD-883 Method 2009	Electrical test not required. Inspect device construction, marking, and workmanship.	Passed
Physical Dimensions	AEC-Q200-REV E- Test 10 JESD22 Method JB-100	Verify physical dimensions to the applicable device detail specifications. Note: User(s) and Suppliers spec. electrical test not required.	Passed
Resistance to Solvents	AEC-Q200-REV E- Test 12 MIL-STD-202 Method 215	In addition to the Method 215 solvents, add an aqueous wash chemical and follow chemical manufacturer's recommended parameters (i.e., solution temperature and immersion time).	Marking and protective layer cannot be detached
Shock/Vibration	AEC-Q200-REV E- Test MIL-STD-202 Method 213, Con C MIL-STD-202 Method 204	Shock: Figure 1 of Method 213. THT: Condition C. Vibration: 5 g for 20 minutes, 12 cycles 3e3ach of 3 orientations. Test from 10 Hz ~ 2000 Hz	$\pm 1 \%$
Resistance to Soldering Heat	AEC-Q200-REV E- Test 15 MIL-STD-202 Method 210, Con C	Condition C: Immerse the specimens in an eutectic solder at 260 ± 5 °C for 20 ± 1 seconds.	$\pm 1 \%$
Temperature Cycling	AEC-Q200-REV E- JESD22-A104	-55 °C / +150 °C. Note: Number of cycles = 1000	$\pm 1 \%$
ESD	AEC-Q200-REV E-002	Verify the voltage setting at 500 V.	$\pm 1 \%$
Solderability	AEC-Q200-REV E- Test 18 J-STD-002	Method A1, category 2 (steam aging 4 hours) at 245 °C . Lead-free solder bath at 245 ± 3 °C. Dipping time: 3 ± 0.5 seconds.	> 95 % area covered with tin
Flammability	AEC-Q200-REV E- Test 17 UL-94	V-0 or V-1 is acceptable. Electrical test not required.	V-0 or V-1
Terminal Strength (Leaded)	AEC-Q200-REV E MIL-STD-202 Method 211	20 N, 5-10 seconds.	Passed

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.





Standard Packaging Quantities

Model	Bulk	10-Inch Reel	12-Inch Reel	14-Inch Reel
UT1A UT2	500	1500	N/A	N/A
UT2B		N/A	1500	
UT2C UT5A			1000	
UT3 UT5 UT6 UT7C		N/A	N/A	1000
UT10	250			500

Packaging Specifications

Model	Dimension O (mm)	Reel Size (Inches) Dimension X	Pitch (Inches) Dimension P	Clean Lead to Clean Lead Eccentricity (Max.) Dimension L1–L2	Lead Extension (Max.) - Zero is Preferred Dimension L3	Lead Bending Dimension Z	Exposed Adhe- sive (Max.) Dimension S	Tape Width (mm) Dimension t	Lead Sandwich (Min.) Dimension H	Overall Width (Max.) Dimension W
UT1A	1.983-2.141	10	0.2	1.4 (.055)	0.8 (.031)	1.0 (.039)	0.8 (.031)	7.0 (177.8)	t/2	123.5 (4.862)
UT2	2.421-2.579									
UT2B	1.983-2.141	12	0.4							
UT2C	2.421-2.579									
UT5A										
UT3										
UT5										
UT6										
UT7C	3.206-3.364	14								
UT10										



REV. 08/26

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."
- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automotive Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.
- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.
- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for a particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <https://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <https://www.bourns.com/docs/Legal/disclaimer.pdf>

K2540 08/26R



CALIFORNIA WARNING: Can expose you to lead, a carcinogen and reproductive toxicant.

See www.P65Warnings.ca.gov