

40Vmax Pipe Belt Sander XGT®

BS002G

190 - 810 m/min, 40 x 760 mm

Model BS002G is a pipe belt sander powered by a 40Vmax XGT Li-Ion battery.

This machine is capable of grinding and polishing along curved surfaces such as stainless steel handrails and pipe weld sections. Maximum diameter pipes for grinding 125mm. Features Constant speed control, Variable speed control by dial.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
Sound Power Level (L_{WA})	91 dB(A)
Sound Pressure Level (L_{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	592 x 198 x 359 mm
Tool weight with battery	4,0 - 5,2 kg
Product net weight	3,3 kg
Belt Speed	190 - 810 m/min
Belt Size	40 x 760 mm
Vibration Level, Sanding Metal Plate	$\leq 2,5 \text{ m/s}^2$
Vibration Uncertainty (K Factor), Sanding Metal Plate	$1,5 \text{ m/s}^2$

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft start for smooth start-ups
- Electric brake for maximum productivity and increased operator safety



Related products

Other

User manual

Parts drawing