

RoHS
Compliant



Features

- 3mm Rounded LED Lamps
- Low power consumption
- Excellent product quality and reliability
- Lead-free device

Applications

- Electronic signs and signals
- Bright ambient lighting conditions
- Backlight
- General purpose indicators

Specifications

Emitting Colour : Red/Kelly
Lens Colour : White Diffuse
Material : GaAsp/Gap

Absolute Maximum Ratings: (T _A = 25°C)				
Parameter	Symbol	Red	Kelly	Unit
Power Dissipation	P _D	65		mW
Forward current	I _F	25		mA
Peak Forward Current*1	I _{FP}	60		
Reverse voltage	V _R	5		V
Operating Temperature	T _{opr}	-40°C to +85°C		
Storage Temperature	T _{STG}	-40°C to +100°C		
Storage Temperature *2	T _{SOL}	260°C For 5 Seconds		

Notes:

*1: Pulse width ≤ 0.1ms, Duty cycle ≤ 1/10

*2: Δ At the Position of 3mm below package base.

*3: ▲ Please refer to the curve of forward current vs. temperature


Electrical / Optical / Characteristics at T _A = 25°C								
Parameter	Symbol		Min.	Typ.	Max.	Unit	Test Conditions	
Forward Voltage	Red	V _F	-	1.8	-	V	I _F =20mA	
	Kelly			2.2	-			
Reverse Current	Red	I _R		-	10	μA	V _R =5V	
	Kelly			-	10			
Dominant Wavelength	Red	λ _D		640	-	nm	I _F =20mA	
	Kelly			570				
Peak Wavelength	Red	λ _P		660				
	Kelly			565				
Spectral line Half-width	Red	Δλ		23				
	Kelly			30				
Luminous Intensity	Red	I _V		30				mcd
	Kelly			20				
Power Angle		2θ _{1/2}		60				Deg.

Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or dominant wavelength), the typical accuracy of the sorting process is as follows:

- DominantWavelength: +/-1nm
- Chromatic Coordinates: +/-0.01
- Luminous Intensity: +/-15%
- Forward Voltage: +/-0.1V

Dimensions









Notes:

1. All dimensions are in millimeters.
2. Tolerance is ±0.25 unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. Specifications are subject to change without notice.
5. The design and working Current for Led is not less than 2mA.




Typical Electrical/Optical Characteristics Curves




Red



Typical Electrical/Optical Characteristics Curves

Kelly





Part Number Table

Description	Part Number
Multi Colour LED, Common Anode, Red and Kelly, 3mm, 65mW	MP017039

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.