

**RoHS
Compliant**

Features

- Wide view angle



Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and back-lighting in telephone and fax.
- Flat backlight for LCD switch and symbol.

Specifications

Dimensions	: 3.5mm × 2.8mm × 1.9mm.
Emitted colour	: Red / Blue / Green
Dice	: (InGaAlP) / (InGaN)
Lens colour	: Water clear.

Absolute Maximum Ratings: (T_A = 25°C)

Parameter	Symbol	Red	Blue	Green	Unit
Power Dissipation	P _D	62	100		mW
Forward current	I _F	25			mA
Peak Forward Current*1	I _{FP}	100			
Reverse voltage	V _R	5			V
Operating Temperature	T _{opr}	-40°C to + 85°C			
Storage Temperature	T _{STG}				

Notes: *1: Pulse width ≤ 0.1ms, Duty cycle ≤ 1/10

Optical / Electrical Characteristics at T_A = 25°C


Parameter	Symbol	Device	Min.	Typ.	Max.	Unit	Test Conditions
Forward Voltage	V _F	Red Blue Green	1.8 2.8 2.8	-	2.6 3.6 3.6	V	I _F =20mA
Reverse Current	I _R	Red Blue Green	-	-	10	μA	V _R =5V
Dominant Wavelength	λ _D	Red Blue Green	617 464 518	-	629 473 530	nm	I _F =20mA
Luminous Intensity	I _V	Red Blue Green	650 385 845	-	1400 845 1800	mcd	I _F =20mA
Viewing Angle	2θ _{1/2}	Red Blue Green	-	120 120 120	-	Deg.	I _F =20mA

Remarks:


If special sorting is required (e.g. binning based on forward voltage, luminous intensity or chromaticity), the typical accuracy of the sorting process is as follows:

- Dominant Wavelength : ±1nm
- Luminous Intensity: ±15%
- Forward Voltage: ±0.1V

Package Dimensions



Recommended soldering pattern








Dimensions : Millimetres (Inches)


Notes:

Tolerance is $\pm 0.25\text{mm}$ unless otherwise noted

Typical Electrical/Optical Characteristics Curves



Radiation Diagram



Part Number Table

Description	Part Number
Multi Colour Led, Common Anode, Red, Blue and Green, Water Clear, SMD 3528, 1.9mm	MP017046

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.