

CSS4C-1216 SERIES
Current Sense Resistor

*RoHS COMPLIANT
**HALOGEN FREE &
AEC-Q200 COMPLIANT

Features

- EB welded metal strip
- High power up to 5 W
- Excellent long term stability
- Four terminals for high accuracy
- RoHS compliant* and halogen free**
- AEC-Q200 compliant

Applications

- Current sensing
- Battery management systems
- Power modules
- Frequency converters
- Industrial

Sustainability

- Energy-saving low-power design
- High efficiency, low power loss
- Small size reduces material use

Product Overview

The CSS4C-1216 Series features an EB welded metal strip design that delivers excellent long-term stability, low inductance (< 2 nH), and high accuracy using a four-terminal Kelvin configuration. With power ratings up to 5 W, resistance values from 0.2 mΩ to 3 mΩ, and TCR as low as ±50 ppm/°C, this series enables improved efficiency and precise current measurement while maintaining

AEC-Q200 compliance and robust performance in demanding automotive and industrial environments. It provides increased flexibility for designers in high-current applications such as battery management systems, power modules, and industrial electronics.

Electrical Characteristics

Characteristic	Model CSS4C-	Value
Resistance Range / Power Rating @ 100 °C	1216T-L200	0.2 mΩ / 5 W
	1216T-L300	0.3 mΩ / 5 W
	1216T-L400	0.4 mΩ / 5 W
	1216T-L500	0.5 mΩ / 5 W
	1216C-L750	0.75 mΩ / 4 W
	1216C-1L00	1.0 mΩ / 3 W
	1216A/N-2L00	2.0 mΩ / 2 W
	1216A-3L00	3.0 mΩ / 2 W
TCR (20~60 °C)	1216T-L200	±150 PPM/°C
	1216T-L300	±100 PPM/°C
	1216T-L400	±100 PPM/°C
	1216T-L500	±50 PPM/°C
	1216C-L750	±50 PPM/°C
	1216C-1L00	±50 PPM/°C
	1216A/N-2L00	±50 PPM/°C
	1216A-3L00	±50 PPM/°C
Tolerance	±1 % / ±3 % / ±5 %	
Inductance	< 2 nH	
Maximum Working Voltage	$V = \sqrt{P \times R}$	

Contact Information

www.bourns.com	Phone	Email
Asia-Pacific	+886-2 2562-4117	asiacus@bourns.com
Europe	+36 88 885 877	eurocus@bourns.com
Mexico	+52 614 478 0400	mexicus@bourns.com
The Americas	+1-951 781-5500	americus@bourns.com

Environmental Characteristics

Specification	Value
Operating Temperature	-65 °C to +170 °C
Storage Conditions	
Temperature	+5 °C ~ +35 °C
Humidity	40 % ~ 75 %
Moisture Sensitivity Level	1

How to Order

CSS 4C - 1216 T - L500 F

Model _____
 CSS = Current Sense Shunt

Number of Terminals and Style _____
 4C = 4 terminals

Package Size _____
 1216 = 1216 in. (3038 mm)

Material _____
 T = Copper Manganese Tin Alloy
 C = Copper Manganese Alloy
 A = FeCrAl Alloy
 N = NiCr Alloy

Resistance Value _____
 "L" represents decimal point in mΩ
 (example: L500 = 0.0005 Ω, 1L00 = 0.001 Ω)

Resistance Tolerance _____
 F = ±1 %
 H = ±3 %
 J = ±5 %

Packaging Type _____
 (blank) = 3,000 pcs. / 13-inch reel

* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

**Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




Performance Characteristics

Test	Conditions	Test Condition	Limit
		Reference	
High Temperature Exposure	1000 hrs. @ T=170 °C Unpowered	AEC-Q200-REV E-Test 3 MIL-STD202 Method 108	$\Delta R < \pm 1 \%$
Temperature Cycling	-55 °C to 150 °C, 1000 Cycles, 30 minutes at each extreme	AEC-Q200-REV E-Test 4 JESD22 Method JA-104	$\Delta R < \pm 0.5 \%$
Biased Humidity	+85 °C & 85 % RH with 10 % operating power, 1000 hours	AEC-Q200-REV E-Test 7 MIL-STD-202 Method 103	$\Delta R < \pm 0.5 \%$
Operational Life	1000 hours at rated power at +125 °C	AEC-Q200-REV E-Test 8 MIL-STD-202 Method 108	$\Delta R < \pm 1 \%$
External Visual	Visual inspection	MIL-STD-883 Method 2009	Visual
Physical Dimension	Dimensional inspection as per SBCL specifications	JESD22 Method JB-100	Shall confirm within tolerance limits
Resistance to Solvents	Clean with aqueous chemical	MIL-STD-202 Method 215	Marking shall be legible
Mechanical Shock	100 g for 6 ms, Half sine shock pulse	AEC-Q200-REV E-Test 13 MIL-STD-202 Method 213	$\Delta R < \pm 0.2 \%$
Vibration	5 g for 20 minutes, 12 cycles each of 3 orientations. 10-2000 Hz	AEC-Q200-REV E-Test 8 MIL-STD-202 Method 108	$\Delta R < \pm 0.2 \%$
Resistance to Soldering Heat	Solder temperature: 260 °C, Time: 10 seconds $\pm$ 1 second dwell	AEC-Q200-REV E-Test 15 MIL-STD-202 Method 210	$\Delta R < \pm 0.5 \%$
Solderability	235 $\pm$ 3 °C Dipping time: 3 $\pm$ 0.5 seconds	AEC-Q200-REV E-Test 18 J-STD-002	>95 % Coverage @ 10x Magnification
Electrical Characterization	Resistance as defined	User spec.	Shall confirm within tolerance limits
Short Time Overload	5x Rated power for 5 seconds	IEC 60115-1 4.13	$\Delta R < \pm 0.5 \%$
Low Temperature Storage	-65 °C for 24 hours	IEC 60115-1-4.23.4 JIS-C5201-4.23.4	$\Delta R < \pm 0.1 \%$

Typical Part Marking



Power Derating Curve




Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




Product Dimensions



DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

Model CSS4C-	Dimensions (Max.)	Alloy
	T	
1216T-L200	2.40 ± 0.35 (.094 ± .014)	Copper Manganese Tin
1216T-L300	2.00 ± 0.35 (.079 ± .014)	
1216T-L400		
1216T-L500	1.90 ± 0.35 (.075 ± .014)	
1216C-L750		Copper Manganese Alloy
1216C-1L00	1.70 ± 0.35 (.067 ± .014)	
1216A-2L00	1.90 ± 0.35 (.075 ± .014)	FeCrAl Alloy
1216N-2L00		NiCr Alloy
1216A-3L00	1.70 ± 0.35 (.067 ± .014)	FeCrAl Alloy

Recommended Layout



DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$


Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




TCR Curves


Typical Resistance Drift – Resistance Alloy -T




Typical Resistance Drift – Resistance Alloy -A



Typical Resistance Drift – Resistance Alloy -N



Typical Resistance Drift – Resistance Alloy -C




Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



Soldering Profile




Profile Feature	Pb Free Assembly
Preheat - Temperature Min. (T_{smin}) - Temperature Max. (T_{smax}) - Time (t_s) from T_{smin} to T_{smax}	150 °C 200 °C 60-120 seconds
Ramp-up Rate (T_L to T_p)	3 °C/second max.
Liquidus temperature (T_L) Time (t_L) maintained above T_L	217 °C 60-150 seconds
Peak package body temperature (T_p)	260 °C
Time (t_p) at $T_c - 5\text{ }^\circ\text{C}$ (T_p should be equal to or less than T_c)	30 seconds*
Ramp-Down Rate (T_p to T_L)	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Packaging Dimensions

Components packaged on plastic tape & reel per DIN EN 60286-3.
Standard Reel Size: 13 inches
Tape Width: 12 mm
Quantity: 3,000 pcs. per reel



USER DIRECTION OF FEED
QTY: 3,000 PCS PER REEL

DIMENSIONS: MM
(INCHES)

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."
- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automotive Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.
- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.
- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for a particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <https://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <https://www.bourns.com/docs/Legal/disclaimer.pdf>

K2540 08/26R



CALIFORNIA WARNING: Can expose you to lead, a carcinogen and reproductive toxicant.

See www.P65Warnings.ca.gov