
Power PCB Relay G2R

- Creepage distance of 8.0 mm (0.31) min. between coil and contact.
- Dual-winding latching type available.
- Plug-in and quick-connect terminals available (see G2R-S(S) data sheet).
- High sensitivity (360 mW) and high capacity (16 A) types available.
- Highly stable magnetic circuit for latching endurance and excellent resistance to vibration and shock.
- Safety-oriented design assuring high surge resistance: 10,000 V min. between coil and contacts.
- UL, CSA approved, marked with CE.



Ordering Information

To order: Select the part number and add the desired coil voltage rating (e.g., G2R-14-DC12).

■ Non-Latching

1-Pole - PCB Types

Туре	Contact material	Contact form	Construction	Model
General purpose	Ag alloy	SPDT	Semi-sealed	G2R-1
			Sealed	G2R-14
		SPST-NO	Semi-sealed	G2R-1A
			Sealed	G2R-1A4
High-capacity		SPDT	Semi-sealed	G2R-1-E
		SPST-NO		G2R-1A-E
High-sensitivity		SPDT		G2R-1-H
			Sealed	G2R-14-H
		SPST-NO	Semi-sealed	G2R-1A-H
			Sealed	G2R-1A4-H

1-Pole - Quick-connect Types

Туре	Contact material	Contact form	Terminal	Model
Upper-mount bracket	Ag alloy	SPDT	Quick connect	G2R-1-T
		SPST-NO		G2R-1A-T

2-Pole - PCB Types

Туре	Contact material	Contact form	Construction	Model
General purpose	Ag alloy	DPDT	Semi-sealed	G2R-2
			Sealed	G2R-24
		DPST-NO	Semi-sealed	G2R-2A
			Sealed	G2R-2A4
High sensitivity]	DPDT	Semi-sealed	G2R-2-H
			Sealed	G2R-24-H
		DPST-NO	Semi-sealed	G2R-2A-H
			Sealed	G2R-2A4-H

Note: 1. Bifurcated button available.

- 2. For individual product agency approvals consult factory.
- 3. Class B coil insulation available.
- 4. CE mark only on quick connect types.

■ Latching

Туре	Contact form	Construction	Model
Dual coil latching	SPDT	Semi-sealed	G2RK-1
	SPST-NO		G2RK-1A
	DPDT		G2RK-2
	DPST-NO		G2RK-2A

Specifications

■ Contact Data

Non-latching general purpose and upper-mount bracket.

Load	1-pole	type	2-ро	le type	
	Resistive load (p.f. = 1)			Inductive load (p.f. = 0.4) (L/R = 7 ms)	
Rated load	10 A at 250 VAC 10 A at 30 VDC	7.5 A at 250 VAC 5 A at 30 VDC	5 A at 250 VAC 2 A at 250 VAC 5 A at 30 VDC 3 A at 30 VDC		
Contact material	Ag-Alloy				
Carry current	10 A		5 A		
Max. operating voltage	380 VAC, 125 VDC				
Max. operating current	10 A		5 A		
Max. switching capacity	2,500 VA, 300 W	1,875 VA, 150 W	1,250 VA, 150 W	500 VA, 90 W	
Min permissible load	100 mA, 5 VDC 10 mA, 5 VDC				

Non-latching high capacity 1-pole type

Load	Resistive load (p.f. = 1)	Inductive load (p.f. = 0.4) (L/R = 7 ms)
Rated load	16 A at 250 VAC 16 A at 30 VDC	8 A at 250 VAC 8 A at 30 VDC
Contact material	Ag-Alloy	
Carry current	16 A	
Max. operating voltage	380 VAC, 125 VDC	
Max. operating current	16 A	
Max. switching capacity	4,000 VA, 480 W	2,000 VA, 240 W
Min. permissible load	100 mA, 5 VDC	

Non-latching high-sensitivity

Load	1-pole type			le type
	Resistive load (p.f. = 1)	Inductive load (p.f. = 0.4) (L/R = 7 ms)	Resistive load (p.f. = 1)	Inductive load (p.f. = 0.4) (L/R = 7 ms)
Rated load	5 A at 250 VAC 5 A at 30 VDC	2 A at 250 VAC 3 A at 30 VDC	3 A at 250 VAC 3 A at 30 VDC	1 A at 250 VAC 1.50 A at 30 VDC
Contact material	Ag-Alloy			
Carry current	5 A		3 A	
Max. operating voltage	380 VAC, 125 VDC			
Max. operating current	5 A		3 A	
Max. switching capacity	1,250 VA, 150 W	500 VA, 90 W	750 VA, 90 W 250 VA, 45 W	
Min permissible load	100 mA, 5 VDC 10 mA, 5 VDC			

Latching

Load	1-pc	ole type	2-pole type		
	Resistive load Inductive load (p.f. = 1) (p.f. = 0.4) (L/R = 7		Resistive load (p.f. = 1)	Inductive load (p.f. = 0.4) (L/R = 7 ms)	
Rated load	5 A at 250 VAC 5 A at 30 VDC	3.50 A at 250 VAC 2.50 A at 30 VDC	3 A at 250 VAC 3 A at 30 VDC	1.50 A at 250 VAC 2 A at 30 VDC	
Contact material	Ag-Alloy	•		•	
Carry current	5 A		3 A		
Max. operating voltage	380 VAC, 125 VDC				
Max. operating current	5 A		3 A		
Max. switching capacity	1,250 VA, 150 W	875 VA, 75 W	750 VA, 90 W 375 VA, 60 W		
Min permissible load	100 mA, 5 VDC	•	10 mA, 5 VDC		

Note: 1. P standard: $\lambda_{50} = 0.10 \text{ x } 10^{-6}$ operation. 2. For individual product agency approvals consult factory.

■ Coil Data

Non-latching DC coil

Rated voltage (VDC)	Rated current (mA)	resistance	Coil inductance (ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption
		(Ω)	Armature OFF	Armature ON	%	of rated voltag	je	(mW)
3	176	17	0.07	0.14	70% max.	15% min.	110% max.	Approx. 530
5	106	47	0.20	0.39			at 70°C	
6	88.20	68	0.28	0.55			(158°F)	
12	43.60	275	1.15	2.29				
24	21.80	1,100	4.27	8.55				
48	11.50	4,170	13.86	22.71				
100	5.30	18,860	67.20	93.20	1			
110	4.80	22,900	81.50	110.60				

Non-latching AC coil

Rated voltage (VAC)	Rated current (mA)	Coil resistance	Coil inductance (ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption (VA)
		(Ω)	Armature OFF	Armature ON	%	% of rated voltage		
6	150	16	0.05	0.10	80% max.	30% min.	110% max.	Approx. 0.9
12	75	65	0.19	0.39			at 70°C	
24	37.50	260	0.81	1.55			(158°F)	
50	18	1,130	3.25	6.73				
110	10.60	4,600	13.34	26.84				
120	7.50	6,500	21	42				
220	5.30	22,000	51.30	102				
240	3.80	30,000	65.50	131				

Non-latching high-sensitivity DC coil

Rated voltage (VDC)	Rated current (mA)	resistance	Coil inductance (ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption
		(Ω)	Armature OFF	Armature ON	% of rated voltage			(mW)
3	120	25	0.13	0.26	70% max.	15% min.	110% max.	Approx. 360
5	71.40	70	0.37	0.75			at 70°C	
6	60	100	0.63	1.07			(158°F)	
12	30	400	2.14	4.27				
24	15	1,600	7.80	15.60	1			
48	7.50	6,400	31.20	62.40				

Latching dual coil type - Set coil

Rated voltage (VDC)	Rated current (mA)	Coil resistance	Coil inductance (ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption
		(Ω)	Armature OFF	Armature ON	% of rated voltage			(mW)
3	227	10.80	0.026	0.052	70% max.	70% max.	110% max.	Approx. 850
5	167	30	0.073	0.146			at 70°C (158°F)	
6	138	43.50	0.104	0.208				
12	70.60	170	0.42	0.83				
24	34.60	694	1.74	3.43				

Latching dual coil type - Reset coil

Rated voltage (VDC)	Rated current (mA)	resistance		ductance alue) (H)	Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption
		(Ω)	Armature OFF	Armature ON	% of rated voltage		(mW)	
3	200	15	0.001	0.002	70% max.	70% max.	110% max.	Approx. 600
5	119	42	0.003	0.006			at 70°C (158°F)	
6	100	60	0.005	0.009				
12	50	240	0.018	0.036				
24	25	960	0.079	0.148				

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C (73°F) with a tolerance of ±10%.

■ Characteristics

Item		Non-latching	Latching		
Contact resistance		100 mΩ			
Operate (set) time		15 ms. max.	20 ms max.		
Release (reset) time		AC: 10 ms max.; DC: 5 ms max.	20 ms max.		
Bounce time	Operate		Mean value approx. 3 ms		
	Release		Mean value approx. 8 ms		
Operating frequency	Mechanical	18,000 operations/hour			
	Electrical	1,800 operations/hour (under rated load)			
Insulation resistance		1,000 MΩ min. (at 500 VDC)			
Dielectric strength		5,000 VAC, 50/60 Hz for 1 minute between coil and contacts			
		1,000 VAC, 50/60 Hz for 1 minute across contacts of same pole			
		3,000 VAC, 50/60 Hz for 1 minute between contact sets, 2-pole non-latching			
		1,000 VAC, 50/60 Hz for 1 minute between set and reset coils of dual coil latching			
Vibration	Mechanical durability	10 to 55 Hz; 1.50 mm (0.06) double amplitude			
	Malfunction durability	10 to 55 Hz; 1.50 mm (0.06) double amplitude			
Shock	Mechanical durability	1,000 m/s ² (approx. 100G)			
	Malfunction durability	200 m/s ² (approx. 20 G) when energized 100 m/s ² (approx. 10 G) when de-energized	500 m/s ² (approx. 50 G) at set 100 m/s ² (approx. 10 G) at reset		
Ambient temperature		-40 to 70°C (-40 to 158°F)			
Humidity		35% to 85% RH			
Service life	Mechanical	AC: 10,000,000 operations min. DC: 20,000,000 operations min. (at 18,000 operations/hour)	10,000,000 operations min. (at 18,000 operations/hour)		
	Electrical	See "Characteristics Data"			
Weight		Approx. 17 g (0.60 oz.)	Approx. 17 g (0.60 oz.)		

Note: Data shown are of initial value.

^{2.} The operating characteristics are measured at a coil temperature of 23°C (73°F).


■ Characteristic Data

Maximum Switching Capacity - Non-latching Types

PCB: Single-pole general purpose Semi-sealed


Quick-connect: Single-pole single button

AC resistiv




Rated operating voltage (V)

PCB: Two-pole high sensitivity




High capacity




Rated operating voltage (V)

PCB: Single-pole general purpose




Rated operating voltage (V)

PCB: Single-pole high sensitivity Two-pole general purpose



PCB: Two-pole general purpose Sealed



Rated operating voltage (V)

Electrical Service Life - Non-latching Types


PCB: Single-pole general purpose

Semi-sealed


High capacity

PCB: Single-pole high sensitivity Two-pole general purpose





Rated operating current (A)



Rated operating current (A)


Service life (x 104 operations) 30 VDC inductive load (L/R = 7 ms) 50 250 VAC 30 VDC resistive load

500

٥٢


Rated operating current (A)

PCB: Two-pole high sensitivity




Rated operating current (A)

PCB: Single-pole general purpose Sealed



Rated operating current (A)


PCB: Two-pole general purpose Sealed



Rated operating current (A)


Maximum Switching Capacity - Latching Types

One pole



Rated operating voltage (V)


Two-pole




Rated operating voltage (V)

Electrical Service Life - Latching Types

One pole



Two-pole



Rated operating current (A)


Rated operating current (A)


Dimensions

Unit: mm (inch)


■ Non-latching

PCB Terminal: SPDT, general purpose & high sensitivity






Terminal arrangement/ Internal connections (Bottom view)





Mounting holes

(Bottom view)




PCB Terminal: SPST-NO, general purpose & high sensitivity






Terminal arrangement/ Internal connections (Bottom view)




Mounting holes


(Bottom view)




- Note: 1. and [] indicate mounting orientation marks.
 - 2. A tolerance of ± 0.10 (0.004) applies to the above dimensions.

PCB Terminal: SPDT, high capacity







Terminal arrangement/ Internal connections (Bottom view)




Mounting holes (Bottom view)




PCB Terminal: SPST-NO, high capacity






Terminal arrangement/ Internal connections (Bottom view)




Mounting holes (Bottom view) 2.5 (.10) 6-1.3 (.05) dia. holes 2.1 (.08)

Quick-connect: SPDT




Terminal arrangement/ Internal connections (Bottom view)



Mounting holes


(Bottom view)




Note: 1. and [] indicate mounting orientation marks.

2. A tolerance of ± 0.10 (0.004) applies to the above dimensions.

Quick-connect: SPST-NO




Terminal arrangement/ Internal connections (Bottom view)





Mounting holes

(Bottom view)




PCB Terminal: DPDT, general purpose & high sensitivity







Terminal arrangement/ Internal connections (Bottom view)



Mounting holes (Bottom view)




PCB Terminal: DPST-NO, general purpose & high sensitivity






Terminal arrangement/ Internal connections (Bottom view)



Mounting holes


(Bottom view)




- Note: 1. Indicate mounting orientation marks.
 - **2.** A tolerance of ± 0.10 (0.004) applies to the above dimensions.

■ Latching


SPDT, Dual coil latching G2RK-1




Dual coil




Dual coil




SPST-NO, Dual coil latching G2RK-1A




Dual coil




Dual coil




DPDT, Dual coil latching G2RK-2




Dual coil




Dual coil




DPST-NO, Dual coil latching G2RK-2A



Dual coil



Dual coil



- and [] indicate mounting orientation marks.
 A tolerance of ±0.10 (0.004) applies to the above dimensions.

■ Approvals


UL (File No. E41643)/ CSA (File No. 31928)

Туре	Contact form	Coil rating	Contact ratings
G2R-1	SPDT	3 to 110 VDC	10 A, 30 VDC (Resistive)
G2R-14		3 to 240 VDC	10 A, 250 VAC (General purpose)
G2R-1-H			10 A, 277 VAC (General purpose)
G2R-14-H			TV-3, 120 VAC (NO contact)
G2R-1-T			360 WT, 120 VAC (Tungsten)
G2R-1A	SPST-NO		1/3 HP, 125 VAC (NO contact)
G2R-1A4			1/2 HP, 250 VAC (NO contact)
G2R-1A-H			1/2 HP, 277 VAC (NO contact)
G2R-1A4-H			TV-8, 120 VAC (NO contact, ASI contacts)
G2R-1A-T			B300 (Pilot duty)
G2R-1-E	SPDT	3 to 110 VDC	20 A, 277 VAC (General purpose)
		3 to 240 VAC	16 A, 30 VDC (Resistive)
			16 A, 250 VAC (General purpose)
			360 WT, 120 VAC (Tungsten)
G2R-1A-E	SPST-NO		TV-3, 120 VAC (NO contact)
			1/2 HP, 240 VAC
			1 HP, 240 VAC
			TV-8, 120 VAC (No contact, ASI contacts)
G2R-2	DPDT	3 to 110 VDC	10 A, 30 VDC (Resistive)
G2R-24		3 to 240 VAC	10 A, 277 VAC (General purpose)
G2R-2-H			5 A, 250 VAC (General purpose)
G2R-24-H			TV-3, 120 VAC (NO contact)
G2R-2-A			1/6 HP, 120 VAC
G2R-2A4			1/3 HP, 240 VAC
G2R-2A-H			1/3 HP, 265 VAC
G2R-2A4-H			250 VA, 120 VAC (Pilot duty)
			B300 (Pilot duty)
G2RK-1	SPDT	3 to 24 VDC	10 A, 30 VDC (Resistive)
G2RK-1A	SPST-NO		10 A, 250 VAC (General purpose)
			TV-3 (NO contact)
			1/6 HP, 120 VAC
			1/2 HP, 120 VAC
			A300 (Pilot duty)
G2RK-2	DPDT	3 to 24 VDC	5 A, 30 VDC (Resistive)
G2RK-2A	DPST-NO		5 A, 250 VAC (General purpose)
ĺ			TV-3 (NO contact)
			1/6 HP, 120 VAC
			1/3 HP, 240 VAC

Note: 1. The rated values approved by each of the safety standards (e.g., UL and CSA) may be different from the performance characteristics individually defined in this catalog.

^{2.} In the interest of product improvement, specifications are subject to change.





Terms and Conditions of Sale

- Offer: Acceptance. These terms and conditions (these "Terms") are deemed part of all quotations, acknowledgments, invoices, purchase orders and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronic Components LLC ("Seller"). Seller hereby objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms.
- Prices: Payment. All prices stated are current, subject to change without notice by Seller. Buyer agrees to pay the price in effect at time of shipment. Payments for Products received are due net 30 days unless otherwise stated
- <u>Discounts.</u> Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Seller's
- payment terms and (ii) Buyer has no past due amounts owing to Seller. Currencies. If the prices quoted herein are in a currency other than U.S. dol lars, Buyer shall make remittance to Seller at the then current exchange rate most favorable to Seller and which is available on the due date; provided that if remittance is not made when due, Buyer will convert the amount to U.S. dol-lars at the then current exchange rate most favorable to Seller available during the period between the due date and the date remittance is actually made.
- Governmental Approvals. Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Seller or required to be collected directly or indirectly by Seller for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Seller.
- Financial. If the financial position of Buyer at any time becomes unsatisfactory to Seller, Seller reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Seller may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid
- <u>Cancellation; Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Seller fully against all costs or expenses arising in connection therewith
- Force Majeure. Seller shall not be liable for any delay or failure in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.

 10. Shipping: Delivery.

 1. Shipments shall be by a carrier selected by Seller:
- - Such carrier shall act as the agent of Buyer and delivery to such carrier shall constitute delivery to Buyer;
 - 3. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Seller), at which point title to and all risk of loss of the Products shall pass from Seller to Buyer, provided that Seller shall retain a security interest in the Products until the full purchase price is paid by Buver:
- paid by Buyer;

 4. Delivery and shipping dates are estimates only.

 5. Seller will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.

 11. Claims. Any claim by Buyer against Seller for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Seller within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products from Seller in the condition claimed.

- 12. <u>Warranties.</u> (a) <u>Exclusive Warranty</u>. Seller's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Seller (or such other period expressed twelve months from the date of sale by Seller (or such other period expressed in writing by Seller). Seller disclaims all other warranties, express or implied. (b) Limitations. SELLER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Seller further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or othany type for clams or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Seller's sole obligation hereunder shall be to replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the noncomplying Product or, at Seller's election, to repay or credit Buyer an amount equal to the purchase price of the Product; provided that in no event shall Seller be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Seller's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of ject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Seller before shipment. Seller shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies, or any other materials or substances or environ-
- circuits, system assembles, or any other materials of substances of environments. Any advice, recommendations or information given orally or in writing are not to be construed as an amendment or addition to the above warranty. Limitation on Liability: Etc. SELLER SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Seller exceed the individual price of the Product on which liability is asserted.
- which liability is asserted.
 <u>Indemnities</u>. Buyer shall indemnify and hold harmless Seller, its affiliates and its employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Seller is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Seller and defend or settle any action brought against Seller to the extent that it is based on a claim that any Product made to Buyer specifications infringed intellectual property rights
- of another party.

 Property: Confidentiality. The intellectual property embodied in the Products is the exclusive property of Seller and its affiliates and Buyer shall not attempt to duplicate it in any way without the written permission of Seller. Notwithstand to the product of the property of the product of the produc ing any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Seller. All information and materials supplied by Seller to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and
- etary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.

 16. Miscellaneous. (a) Waiver. No failure or delay by Seller in exercising any right and no course of dealing between Buyer and Seller shall operate as a waiver of rights by Seller. (b) Assignment. Buyer may not assign its rights hereunder without Seller's written consent. (c) Law. These Terms are governed by Illinois law (without regard to conflict of law principles). Federal and state courts in Illinois shall have exclusive jurisdiction for any dispute hereunder. (d) Amendment. These Terms constitute the entire agreement between Buyer and Seller relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability. If any provision hereof is rendered ineffective or invalid such provision shall not invalidate any hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff. Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice.. (g) Definitions. As used herein, "including" means "including without limitation".

Certain Precautions on Specifications and Use

- Suitability for Use. Seller shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in Buyer's application or use of the Product. At Buyer's request, Seller will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the partic-Buyer shall be solely responsible for determining appropriateless of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:

 (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.

 - (ii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.

(iii)Use in consumer products or any use in significant quantities. (iv)Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Seller shall not be responsible for the user's
- programming of a programmable product, or any consequence thereof.

 Performance Data. Performance data given in this publication is provided as a guide for the user in determining suitability and does not constitute a warranty It may represent the result of Seller's test conditions, and the users must corre late it to actual application requirements. Actual performance is subject to Seller's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our pract tice to change part numbers when published ratings or features are changed or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for you application. Please consult with your Seller representative at any time to con firm actual specifications of purchased Product.

 <u>Errors and Omissions</u>. The information in this publication has been carefully

checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors, or omissions.

RoHS Compliance. Where indicated, our products currently comply, to the bes

of our knowledge as of the date of this publication, with the requirements of the European Union's Directive on the Restriction of certain Hazardous Sub stances ("RoHS"), although the requirements of RoHS do not take effect until July 2006. These requirements may be subject to change. Please consult our website for quirage information. website for current information.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at www.components.omron.com - under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON ELECTRONIC COMPONENTS LLC

55 E. Commerce Drive, Suite B Schaumburg, IL 60173

847-882-2288

OMRON CANADA, INC.

885 Milner Avenue Toronto, Ontario M1B 5V8

416-286-6465

OMRON ON-LINE

Global - http://www.omron.com USA - http://www.components.omron.com Canada - http://www.omron.ca