TDC600

British plug top fuse fast-acting




RoHS

Product features

- 1/4" x 1" fast-acting, high breaking capacity fuse.
- Ceramic tube - end caps: silver-plated copper.
- High breaking capacity
- 600 Vac
- Standards BS1362
- cULus recognized :File E19180

Dimension-mm



Operating temperature -40 ℃ to +125 ℃

Electrical Ratings (Part number and Amperes)

600 Vac

TDC600-2-R

TDC600-10-R


Rated Current	Rated Voltage (V)	Breaking Capacity	Power Dissipation (W)	Marking color	Approvals
2 A 10 A	600	200 A,600 V 10 kA, 250 V p.f. 0.7 - 0.8	1 Watt @ Rated Current	Blue	Asta, BSI, cULus

Limits for Pre-arcing Time

	1.0 In.	1.6 In.	1.9 In.
In	MIN	MIN	MAX
2A, 10A	1000 hours	30 min.	30 min.

Packaging prefix:

Blank	5 pieces in a container
BK-	100 pieces in carton
BK1-	1,000 pieces in carton



Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. 2081 PCN18031
August 2018

Powering Business Worldwide

Eaton is a registered trademark.

All other trademarks are property of their respective owners.