


Hot air tools made for professionals




WELDY PRO WELDY およりえ METDA およがなし METDA おのMES

rminal display with memory function for memory function for the work



Hot air tools WELDY PRO made for professionals

Accessories















- Welding nozzle
- Reflector nozzle
- Glass protection nozzle
- Wide-slot nozzle
- Reduction nozzle Ø 20 mm
- Overlap welding nozzle
- Pressure roller




Basic hot air tool


- Electronic temperature adjustment from 100°C to 550°C
- Air flow adjustment via a two-step switch
- Electronics flicker conformity



Drying of paint



Forming of pipes




Loosening of screws



Hot air tools WELDY POWER made for professionals

Accessories

















- Reduction nozzle Ø 20 mm
 - Overlap welding nozzle
 - Pressure roller
- Wide-slot nozzle

Welding nozzle Reflector nozzle

Multi-functional hot air tool

• Intelligent terminal display

Glass protection nozzle

- Stand-by for eco drive
- Memory function
- 11 Function programmes



Edge-banding

Manual drive



Shrinking





Forming



Laboratory applications



Welding





Power consumption 2300 W Temperature range 80°C to 650°C Weight 620 g


Soldering








By operating the select key, the required user program with set values for temperature and airflow can be adjusted. As required, the operator can program these values himself within the set range for the program.



Forming



Edge-banding



Laboratory applications



Hot air tools made for professionals

Accessories











- Welding nozzle
- Reflector nozzle
- Wide-slot nozzle
- Overlap welding nozzle
- Pressure roller

Multi-functional welding tool

- Intelligent terminal display
- Stand-by for eco drive
- Memory function
- 11 Function programmes for welding applications



Manual drive



Shrinking



Forming



PP-EPDM



Power consumption 2000 W Temperature range 80°C to 650°C Weight 620 g

HD-PE





PVC-U



ABS





Flooring



By operating the select key, the required user program with set values for temperature and airflow can be adjusted. As required, the operator can program these values himself within the set range for the program.



Welding foils



Repairing bumpers




Welding bitumen and roofing felt




Hot air tools WELDY PLUS made for professionals

Accessories













- Welding nozzle
- Reflector nozzle
- Glass protection nozzle
- Wide-slot nozzle
- Reduction nozzle Ø 20 mm
- Overlap welding nozzle
- Pressure roller



Multi-functional hot air tool

- Intelligent terminal display
- Stand-by for eco drive
- Memory function
- The last select functions (function program) are immediately available again after switching the tool off and then on again.
- 7 Function programmes
















Manual operation

By operating the select key, the required user program with set values for temperature and airflow can be adjusted. As required, the operator can program these values himself within the set range for the program.



Shrinking



Soldering of copper pipes



Paint stripping

	unctional hot air nade for professi		WELDY PRO	WELDY PLUS	WELDY PLAST	WELDY
Power consumption		W	1800	2000	2000	2300
Temperatur range		°C	100-550	80-650	80-650	80-650
Air flow	· · · · · · · · · · · · · · · · · · ·	l/min.	250/550	200-550	200-550	200-600
Static pressure max.		Pa	1300	1200	1200	1200
Weight		g	570	620	620	620
LCD display				•	•	•
Electronics: Flicker conformity			•	•	•	•
Stand-by for Eco drive (lowest set	ting)			•	•	•
Memory function				•	•	•
7 Function programmes		V		•		
11 Function programmes					•	•
Air flow adjustment: Two-step sw	vitch		•			
	th menu control			•	•	•
Heating element: Protected			•			
All ceramic, protected				•	•	•
Function Programmes						
Тетр	erature °C / Air Flow					
Set/stepless adjustment	80-650 / 2-6			•	•	•
Shrink/shrinking	450 / 6			•	•	•
Form/forming	500 / 5			•	•	•
Weld/welding	350 / 4			•		•
Solder/soldering	550 / 4			•		•
Paint/paint stripping	425 / 6			•		
Dry/drying	550 / 6			•		
Edge/edge-banding	380 / 6	- LP 2401 2 1				•
Cure/curing	400 / 4					•
Lab/laboratory application	425 / 5					•
Glue/gluing	450 / 4			******		•
Loose/loosening	600 / 6					•
Dry/drying	650 / 6					•
Welding						
PP-EPDM	280 / 6				•	
HD-PE	300 / 4				•	
PP	320 / 4				•	
PVC-U	340 / 4				•	
ABS	360 / 4	745-1			•	
PC	370 / 4				•	
Floor/welding of floorcoverings	450 / 4				•	
Foil/welding of foils	450 / 4				•	
Accessories						
Wide-slot nozzle			•	•	•	•
Reflector nozzle			•	•	•	•
Glas protection nozzle	····		•	•		•
Welding nozzle			•	•	•	•
Reduction nozzle Ø 20 mm			•	•		•
Overlap welding nozzle					I 🛖	

Preliminary data

SEV tested, CCA-certified

_ ISO 9001 _

CE-Konform