

JTL40 Series



- 4:1 Input Range
- High Power Density
- Single and Dual Outputs
- High Efficiency - Up to 92%
- Remote On/Off
- 1600 VDC Isolation
- 3 Year Warranty

Specification

Input

- Input Voltage Range • 24 V (9-36 VDC), 48 V (18-75 VDC)
- Input Current • See table
- Undervoltage Lockout • 24 V models: ON 8.6 V, OFF 7.9 V typical
48 V models: ON 17.8 V, OFF 16 V typical
- Input Surge • 24 V models 50 VDC for 100 ms
48 V models 100 VDC for 100 ms

Output

- Output Voltage • See table
- Output Voltage Trim • $\pm 10\%$ on single outputs models only
- Minimum Load • No minimum load required for single output models, 10% required for dual output models
- Line Regulation • $\pm 0.5\%$ max
- Load Regulation • Single output models: $\pm 0.5\%$ max
Dual output models: $\pm 1\%$ max balanced outputs
- Cross Regulation • $\pm 5\%$ for dual outputs, see note 2
- Setpoint Accuracy • $\pm 1\%$
- Start Up Time • 25 ms typical
- Ripple & Noise • 50 mV pk-pk max for 3.3 V & 5 V models,
75 mV pk-pk max for other single output models,
150 mV pk-pk max for dual output models, see note 3
- Transient Response • 3% max deviation, recovery to within 1% in $< 250 \mu\text{s}$ for a 25% load change
- Temperature Coefficient • $0.02\%/^{\circ}\text{C}$
- Overvoltage Protection • 3.3 V models: 3.9 V typical
5 V models: 6.2 V typical
12 V models: 15 V typical
15 V models: 18 V typical
 ± 12 V models: ± 15 V typical
 ± 15 V models: ± 18 V typical
- Overload Protection • $> 150\%$
- Short Circuit Protection • Trip & restart (Hiccup mode), auto recovery
- Remote On/Off • On = Logic High (> 3.0) or Open
Off = Logic Low (< 1.2 V) or short pin 2 to 3

General

- Efficiency • See table
- Isolation • 1600 VDC Input to Output
1600 VDC Input to Case
1600 VDC Output to Case
- Isolation Capacitance • 2500 pF max
- Switching Frequency • 270 kHz, typical
- MTBF • 150 kHrs min to MIL-HDBK-217F at 25 $^{\circ}\text{C}$, GB

Environmental

- Operating Temperature • -40°C to $+85^{\circ}\text{C}$, see derating curve
- Case Temperature • $+105^{\circ}\text{C}$ max
- Cooling • Convection-cooled
- Operating Humidity • 5-95% RH, non-condensing
- Storage Temperature • -40°C to $+125^{\circ}\text{C}$

Models and Ratings


Input Voltage	Output Voltage	Output Current	Input Current ⁽¹⁾		Maximum Capacitive Load	Efficiency	Model Number
			No Load	Full Load			
9-36 VDC	3.3 V	10.00 A	80 mA	1600 mA	25000 µF	89%	JTL4024S3V3
	5.0 V	8.00 A	100 mA	1900 mA	13000 µF	91%	JTL4024S05
	12.0 V	3.35 A	50 mA	1930 mA	2300 µF	90%	JTL4024S12
	15.0 V	2.65 A	50 mA	1910 mA	1500 µF	90%	JTL4024S15
	±12.0 V	±1.65 A	60 mA	1920 mA	±1200 µF	89%	JTL4024D12
	±15.0 V	±1.35 A	60 mA	1960 mA	±750 µF	89%	JTL4024D15
18-75 VDC	3.3 V	10.00 A	60 mA	800 mA	25000 µF	89%	JTL4048S3V3
	5.0 V	8.00 A	60 mA	940 mA	13000 µF	92%	JTL4048S05
	12.0 V	3.35 A	30 mA	970 mA	2300 µF	90%	JTL4048S12
	15.0 V	2.65 A	30 mA	940 mA	1500 µF	91%	JTL4048S15
	±12.0 V	±1.65 A	30 mA	950 mA	±1200 µF	90%	JTL4048D12
	±15.0 V	±1.35 A	30 mA	970 mA	±750 µF	90%	JTL4048D15

Notes

1. Input current specified at nominal 24 V or 48 V input.
2. Cross regulation for duals is ±5% when one output is at 100% and the other is varied between 25% and 100%.
3. Measured with 1 µF ceramic capacitor across output rails.

Mechanical Details

Weight: 0.07 lbs (30 g) approx




PIN CONNECTIONS		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	-Sense	+Vout
5	+Sense	Com
6	+Vout	Com
7	-Vout	-Vout
8	Trim	Trim

Notes

1. All dimensions are in inches (mm).
2. Pin diameter: 0.04 ±0.002 (1.0 ±0.05)
3. Pin pitch tolerance: ±0.014 (±0.35)
4. Case tolerance: ±0.02 (±0.5)

Application Notes

Derating Curve



Remote On/Off Control

- Output On >3.0 VDC or open circuit
- Output Off <1.2 VDC or short circuit pins 2 & 3