



*Compatible with Flir DM266

Key Features:

- Control at your fingertips to take the reading or image without removing your hands from the leads
- Probe holder design that allows for seamless control of your leads while capturing measurements
- Next generation wireless control to document problems quickly

Specifications

Flir TA93	
Button Operation	Snapshot and Display Hold Functions
Communication	Wireless (RF)
Radio Frequency	433.92 MHz
Operating Distance	1 meter (3.3 ft) Maximum
Power	CR1220 (3 V) Coin Battery
Weight	10 g (.35 oz)
Operating Temperature and Relative Humidity (RH)	-10°C to 30°C (14°F to 86°F), <85% RH 30°C to 40°C (86°F to 104°F), <75% RH 40°C to 50°C (104°F to 122°F), <45% RH
Storage Conditions	-20°C to 60°C (-4°F to 140°F), <80% RH
Dimensions (L × W × H)	42.7 × 21 × 24.9 mm (1.65 × .82 × .98 in)
Weight	10 g (.35 oz)

Specifications subject to change. For the most up-to-date specifications, visit flir.com.

For technical or sales support, please visit:
www.flir.com

This product is subject to United States export regulations and may require US authorization prior to export, reexport, or transfer to non-US persons or parties. Diversion contrary to US law is prohibited.

For assistance with confirming the Jurisdiction & Classification of Teledyne Flir, LLC products, please contact exportquestions@flir.com. ©2026 Teledyne Flir, LLC. All rights reserved.

Flir_TA93_Datasheet-LTR 26-0497-INS

08/11/26