



Specification Table

Part Number : Varies with colour and packing.

Description: Sub-miniature Cable, 16-2-1C, to Def Stan 61-12 (Part 6).

Conductors: 0.5mm² tinned annealed copper wires to IEC 60228, (as far as applicable), class 5.

: Maximum resistance at 20°C (finished cable) = 38.2 Ohms/km.

Insulation: Type 2 PVC compound to BS 7655-3.2

: Minimum point radial thickness: Minimum diameter: Maximum diameter: 1.45mm.: Maximum diameter: 1.65mm.

Lay Up : N/A

Screen : N/A

Sheath : N/A

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies. : Spark test, voltage : 4000V a.c. : Voltage test : 1500V a.c. : Minimum insulation resistance at $20^{\circ}C$: $50 \text{ M}\Omega/\text{km}$.

Conformity Declaration to EU Directive 2002/95/EC (RoSH)

This Cable Does not contain:

Lead, cadmium, mercury, hexavalent chromium, PBB's and PBDE's.

Please note that this declaration does not exclude irrelevant trace levels (extreme low levels) of the listed substances that may be unintentionally present.



Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-2C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20° C = 40.1Ω /km.

Insulation : Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 2 cores; red, blue.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor = 0.7 (91% coverage).

Sheath : Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 6.9mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature
 : Nominal capacitance, core to core
 : core to screen
 : Approximate mass/unit length
 : 70°C.
 : 130pF/m.
 : 220pF/m.
 : 74.0kg/km.



Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-3C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20° C = 40.1Ω /km.

Insulation : Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 3 cores; red, blue, green.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 0.6mm.
: 6.4mm.
: 7.2mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

Page <3>

: Maximum (conductor) operating temperature
 : Nominal capacitance, core to core
 : core to screen
 : Approximate mass/unit length
 : 70°C.
 : 120pF/m.
 : 220pF/m.
 : 81kg/km.





Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-4C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20° C = 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 4 cores; red, blue, green, yellow.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor = 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 0.6mm.
: 6.9mm.
: 7.7mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature : 70°C.
: Nominal capacitance, core to core : 120pF/m
: core to screen : 220pF/m.
: Approximate mass/unit length : 93kg/km.

Conformity Declaration to EU Directive 2002/95/EC (RoHS)

This cable does not contain : lead, mercury, cadmium, hexavalent chromium, PBB or PBDE.

Please note that this declaration does not exclude irrelevant trace levels (extremely low levels) of the listed substances that may be unintentionally present.

.



Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-6C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20° C : 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 6 cores; (dummy centre), red, blue, green, yellow, white, black.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 8.7mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature : 70°C.
: Nominal capacitance, core to core : 120pF/m;
: core to screen : 220pF/m.
: Approximate mass/unit length : 125.0kg/km.



Specification Table

Part Number : (Varies with packing length).

Description: Sub-miniature Cable, 16-2-8C to Def Stan 61-12 (Part 5), a.f.a.a.

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20°C : 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 8 cores

: Centre : red,

: Outer : blue, green, yellow, white, black, brown, violet.

: Polyester tape.

Screen : 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point : 0.6mm. : Minimum overall diameter : 8.4mm. : Maximum overall diameter : 9.2mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature
: Nominal capacitance, core to core:
: 120pF/m;
: core to screen
: 220pF/m.
: Approximate mass/unit length
: 144.0kg/km.



Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-12C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20°C : 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 12 cores

: Centre : red, blue, green.

: Outer : yellow, white, black, brown, violet, orange, pink, turquoise, grey.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 10.0mm.
: 11.0mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature
 : Nominal capacitance, core to core
 : core to screen
 : 220pF/m
 : Approximate mass/unit length
 : 195.0kg/km.

Page <7>



Specification Table

Part Number : (Varies with packing and colour).

Description: Small Multi-core Cable, 16-2-18C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20°C : 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness : 0.35mm. : Minimum core diameter : 1.75mm. : Maximum core diameter : 1.90mm.

Lay Up : 18 cores

: Dummy centre

: (1st. layer), red, blue, green, yellow, white, black

: (2nd. layer), brown, violet, orange, pink, turquoise, grey, red/blue, green/red, yellow/red,

white/red, red/black, red/brown.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 11.5mm.
: 12.5mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature:
: 70°C.
: Nominal capacitance, core to core:
: 120pF/m.
: core to screen
: 220pF/m.
: Approximate mass/unit length
: 265.0kg/km.



Specification Table

Part Number : (Varies with packing and colour).

Description : Small Multi-core Cable, 16-2-25C to Def Stan 61-12 (Part 5).

Conductors : 0.5mm² (16/0.2mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5.

: Maximum resistance (completed cable) at 20°C : 40.1Ω /km.

Insulation: Type TI 1 PVC compound to BS EN 50363.

: Minimum radial thickness: Minimum core diameter: Maximum core diameter: 1.75mm.: 1.90mm.

Lay Up : 25 cores

: (1st. layer), red, blue, green

: (2nd. layer), yellow, white, black, brown, violet, orange, pink, turquoise;

: (3rd. layer), grey, red/blue, green/red, yellow/red, white/red, red/black, red/brown

yellow/blue, white/blue, blue/black, orange/blue, yellow/green, white/green, orange/green.

: Polyester tape.

Screen: 0.2mm tinned annealed copper braid.

: Minimum filling factor : 0.7 (91% coverage).

Sheath: Type 6 PVC compound to BS 7655.

: Minimum radial thickness at any point
: Minimum overall diameter
: Maximum overall diameter
: 13.6mm.
: 14.6mm.

Service Data : For local interconnection between instruments and electronic equipment.

: Not suitable for direct connection to mains power supplies.

: Maximum working voltage : 440V ac. rms.

: Maximum (conductor) operating temperature:
: 70°C.
: Nominal capacitance, core to core:
: 120pF/m.
: core to screen
: 220pF/m.
: Approximate mass/unit length
: 343kg/km.



Part Number Table

Description	Part Number
CABLE, DEF 16-2-1C, 1CORE, 100M	860038 100M
CABLE, DEF 16-2-2C, 2CORE, 25M	860008 25M
CABLE, DEF 16-2-2C, 2CORE, 100M	860008 100M
CABLE, DEF 16-2-3C, 3CORE, 25M	860155 25M
CABLE, DEF 16-2-3C, 3CORE, 100M	860155 100M
CABLE, DEF 16-2-4C, 4CORE, 25M	860009 25M
CABLE, DEF 16-2-4C, 4CORE, 100M	860009 100M
CABLE, DEF 16-2-6C, 6CORE, 25M	860010 25M
CABLE, DEF 16-2-6C, 6CORE, 100M	860010 100M
CABLE, DEF 16-2-8C, 8CORE, 25M	860011 25M
CABLE, DEF 16-2-8C, 8CORE, 100M	860011 100M
CABLE, DEF 16-2-12C, 12CORE, 25M	860012 25M
CABLE, DEF 16-2-12C, 12CORE, 100M	860012 100M
CABLE, DEF 16-2-18C, 18CORE, 25M	MCCP-1620T-N18C-AXX-61
CABLE, DEF 16-2-18C, 18CORE, 100M	MCCP-1620T-N18C-AXX-64
CABLE, DEF 16-2-25C, 25CORE, 25M	MCCP-1620T-N25C-AXX-61
CABLE, DEF 16-2-25C, 25CORE, 100M	7001551

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The information is subject to change without notice and replaces all data sheets previously supplied. The information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-Power is the registered trademark of the Group. © Premier Farnell plc 2010.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

