



Features

- High voltage and current rating
- Surge protection
- Straight and kinked lead styles available
- Fast response time
- Bidirectional
- RoHS compliant*
- Agency listing: US

Applications


- Power supplies
- Power systems
- Line voltage
- Telecom systems
- White goods / appliances

Sustainability

- Eco-logistics-friendly packing
- Corrosion-resistant for longevity
- ISO 14001, low-impact energy
- Responsibly sourced and produced

Product Overview

The 10 mm radial leaded varistor MOV-10DxxxK Series protects against overvoltage transients such as lightning, power contact and power induction. The metal oxide varistors offer a choice of varistor voltages from 200 V to 820 V and V_{rms} voltages from 130 V to 510 V.



The devices have a high current handling, high energy absorption capability and fast response times to protect against transient faults up to rated limits.

Contact Information

www.bourns.com	Phone	Email
Asia-Pacific	+886-2 2562-4117	asiacus@bourns.com
Europe	+36 88 885 877	eurocus@bourns.com
Mexico	+52 614 478 0400	mexicus@bourns.com
The Americas	+1-951 781-5500	americus@bourns.com

Industry Standard Compliance

Standard	UL 1449
File Number	E313168
Standard	UL 1449
MOV-10D201KC, MOV-10D361KC, MOV-10D391KC, MOV-10D431KC	Will pass 600 V rms, 600 W, 1 A, 0.2 s, 5 cycles, every 1 min. condition

Absolute Maximum Ratings (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Temperature	T_{OPR}	-40	25	+105	$^\circ\text{C}$
Storage Temperature	T_{STG}	-40	25	+125	$^\circ\text{C}$
Rated Wattage	P_W			0.40	Watt
Varistor Voltage Temperature Coefficient	V_{TC}	0		0.05	% / $^\circ\text{C}$
Response Time	T_r		10	25	ns
Varistor Voltage Tolerance	V_{tol}	-10	0	10	%

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Bourns Part No.	Max. Continuous Voltage (V)		Voltage @ 1 mA DC (V)			Voltage @ Class Current		Max. Peak Current	Max. Energy	Typ. Cap.
	r.m.s.	d.c.	Min.	Nom.	Max.	(8/20 μs)		(8/20 μs)	(J)	(pF)
						Class Current (A)	Max. Clamping Voltage (V)	One Time	8/20 μs	1 kHz
MOV-10D201KC	130	170	185	200	225	25	340	2500	30	600
MOV-10D221KC	140	180	198	220	242	25	360	2500	32	540
MOV-10D241KC	150	200	216	240	264	25	395	2500	35	504
MOV-10D271KC	175	225	243	270	297	25	455	2500	40	444
MOV-10D301KC	190	250	270	300	330	25	500	2500	40	396
MOV-10D331KC	210	275	297	330	363	25	550	2500	43	360
MOV-10D361KC	230	300	324	360	396	25	595	2500	47	336
MOV-10D391KC	250	320	351	390	429	25	650	2500	60	312
MOV-10D431KC	275	350	387	430	473	25	710	2500	65	276
MOV-10D471KC	300	385	423	470	517	25	775	2500	70	252
MOV-10D511KC	320	415	459	510	561	25	845	2500	70	240
MOV-10D561KC	350	460	504	560	616	25	925	2500	70	216
MOV-10D621KC	385	505	558	620	682	25	1025	2500	70	192
MOV-10D681KC	420	560	612	680	748	25	1120	2500	70	180
MOV-10D751KC	460	615	675	750	825	25	1240	2500	75	156
MOV-10D781KC	485	640	702	780	858	25	1290	2500	80	156
MOV-10D821KC	510	670	738	820	902	25	1355	2500	85	132

* RoHS Directive 2015/863, Mar 31, 2015 and Annex.
Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




Product Dimensions

This is an RoHS compliant molded radial package with 100 % Sn plating on the terminations.

Straight Leads



Kinked Leads (Outward)



Bourns Part Number	Dim T (Max.)	Dim a (Typ.)
MOV-10D201KC	$\frac{3.8}{(.150)}$	$\frac{1.9}{(.075)}$
MOV-10D221KC	$\frac{3.9}{(.154)}$	$\frac{2.0}{(.079)}$
MOV-10D241KC	$\frac{4.0}{(.157)}$	$\frac{2.1}{(.083)}$
MOV-10D271KC	$\frac{4.2}{(.165)}$	$\frac{2.3}{(.091)}$
MOV-10D301KC	$\frac{4.4}{(.173)}$	$\frac{2.6}{(.102)}$
MOV-10D331KC	$\frac{4.6}{(.181)}$	$\frac{2.7}{(.106)}$
MOV-10D361KC	$\frac{4.8}{(.189)}$	$\frac{2.8}{(.110)}$
MOV-10D391KC	$\frac{5.0}{(.197)}$	$\frac{2.9}{(.114)}$
MOV-10D431KC	$\frac{5.2}{(.205)}$	$\frac{3.1}{(.122)}$

Bourns Part Number	Dim T (Max.)	Dim a (Typ.)
MOV-10D471KC	$\frac{5.4}{(.213)}$	$\frac{3.3}{(.130)}$
MOV-10D511KC	$\frac{5.5}{(.217)}$	$\frac{3.5}{(.138)}$
MOV-10D561KC	$\frac{5.9}{(.232)}$	$\frac{3.8}{(.150)}$
MOV-10D621KC	$\frac{6.2}{(.244)}$	$\frac{4.0}{(.157)}$
MOV-10D681KC	$\frac{6.4}{(.252)}$	$\frac{4.0}{(.157)}$
MOV-10D751KC	$\frac{6.6}{(.260)}$	$\frac{4.1}{(.161)}$
MOV-10D781KC	$\frac{6.8}{(.268)}$	$\frac{4.1}{(.161)}$
MOV-10D821KC	$\frac{7.2}{(.283)}$	$\frac{4.2}{(.165)}$

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Bourns Part Number	Dim T (Max.)	Dim a (Typ.)
MOV-10D201KCC	$\frac{3.8}{(.150)}$	$\frac{1.9}{(.075)}$
MOV-10D221KCC	$\frac{3.9}{(.154)}$	$\frac{2.0}{(.079)}$
MOV-10D241KCC	$\frac{4.0}{(.157)}$	$\frac{2.1}{(.083)}$
MOV-10D271KCC	$\frac{4.2}{(.165)}$	$\frac{2.3}{(.091)}$
MOV-10D301KCC	$\frac{4.4}{(.173)}$	$\frac{2.6}{(.102)}$
MOV-10D331KCC	$\frac{4.6}{(.181)}$	$\frac{2.7}{(.106)}$
MOV-10D361KCC	$\frac{4.8}{(.189)}$	$\frac{2.8}{(.110)}$
MOV-10D391KCC	$\frac{5.0}{(.197)}$	$\frac{2.9}{(.114)}$
MOV-10D431KCC	$\frac{5.2}{(.205)}$	$\frac{3.1}{(.122)}$

Bourns Part Number	Dim T (Max.)	Dim a (Typ.)
MOV-10D471KCC	$\frac{5.4}{(.213)}$	$\frac{3.3}{(.130)}$
MOV-10D511KCC	$\frac{5.5}{(.217)}$	$\frac{3.5}{(.138)}$
MOV-10D561KCC	$\frac{5.9}{(.232)}$	$\frac{3.8}{(.150)}$
MOV-10D621KCC	$\frac{6.2}{(.244)}$	$\frac{4.0}{(.157)}$
MOV-10D681KCC	$\frac{6.4}{(.252)}$	$\frac{4.0}{(.157)}$
MOV-10D751KCC	$\frac{6.6}{(.260)}$	$\frac{4.1}{(.161)}$
MOV-10D781KCC	$\frac{6.8}{(.268)}$	$\frac{4.1}{(.161)}$
MOV-10D821KCC	N/A See Kinked Leads (In-line) Configuration	

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



Product Dimensions (Continued)

This is an RoHS compliant molded radial package with 100 % Sn plating on the terminations.

Kinked Leads (In-line)



Bourns Part Number	Dim T (Max.)
MOV-10D201KCC	N/A See Kinked Leads (Outward) Configuration
MOV-10D221KCC	
MOV-10D241KCC	
MOV-10D271KCC	
MOV-10D301KCC	
MOV-10D331KCC	
MOV-10D361KCC	
MOV-10D391KCC	
MOV-10D431KCC	

Bourns Part Number	Dim T (Max.)
MOV-10D471KCC	N/A See Kinked Leads (Outward) Configuration
MOV-10D511KCC	
MOV-10D561KCC	
MOV-10D621KCC	
MOV-10D681KCC	
MOV-10D751KCC	
MOV-10D781KCC	
MOV-10D821KCC	7.2 (.283)

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Typical Part Marking

Bourns Part Number	Bourns Part Marking
MOV-10D201KC	10D201KC
MOV-10D221KC	10D221KC
MOV-10D241KC	10D241KC
MOV-10D271KC	10D271KC
MOV-10D301KC	10D301KC
MOV-10D331KC	10D331KC
MOV-10D361KC	10D361KC
MOV-10D391KC	10D391KC
MOV-10D431KC	10D431KC
MOV-10D471KC	10D471KC
MOV-10D511KC	10D511KC
MOV-10D561KC	10D561KC
MOV-10D621KC	10D621KC
MOV-10D681KC	10D681KC
MOV-10D751KC	10D751KC
MOV-10D781KC	10D781KC
MOV-10D821KC	10D821KC

NOTE: The "5" marking on MOV products is for traceability of production assembly for quality assurance compliance.

How to Order

MOV - 10D nn (n) K _ C (TR)

Model Designator _____
MOV = Metal Oxide Varistor

Disc Diameter _____
10D = 10 mm

Nominal Varistor Voltage _____
See Electrical Characteristics Table

Multiplier of Voltage Digits _____
0 = No multiplier
1 = nn * 10¹

Varistor Voltage Tolerance _____
K = 10 %

Lead Style _____
Blank = Straight Leads
K = Kinked Leads

Electrode _____
C = Copper-based Electrode

Packaging _____
Blank = Bulk
TR = Tape & Reel


Examples:

MOV-10D201KC = 200 V, Straight Leads, Bulk Pack
MOV-10D331KKCTR = 330 V, Kinked Leads (Outward), Tape & Reel



Performance Graphs

V-I Characteristics





Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.



Pulse Rating Curves



Internal Construction




Environmental Specifications

Moisture Sensitivity Level.....	1
ESD Classification (HBM)	N/A



Packaging Specifications

TAPE & REEL - Straight Leads



Item	Symbol	10 mm Disc
Reel Outside Diameter	RD	355 (13.98)
Reel Inner Diameter	RD1	30 (1.181)
Tape Width	RW	55 (2.16)
Reel Width	RW1	63 max. (2.48)
Pitch of Component	P	25.4 ± 1.0 (1.00 ± 0.04)
Feed Hole Pitch	P0	12.7 ± 0.2 (0.50 ± 0.008)
Feed Hole Center to Pitch	P1	8.95 ± 0.7 (0.352 ± 0.03)
Feed Hole Center to Component Center	P2	12.7 ± 0.7 (0.50 ± 0.03)
Lead to Lead Distance	F	7.50 ± 0.8 (0.30 ± 0.03)
Component Alignment	Dh	2.0 max. (0.79)
Tape Width	W	18.0 ± 0.5 (0.71 ± 0.02)
Hole Down Tape Width	W0	12.0 ± 0.8 (0.47 ± 0.03)
Hole Position	W1	9.0 ± 0.5 (0.35 ± 0.02)
Hole Down Tape Position	W2	3.0 max. (0.12)
Height From Center to Component Base	H	19.0 ± 1.0 (0.75 ± 0.04)
Component Height	H1	36.0 max. (1.42)
Feed Hole Diameter	D0	4.0 ± 0.2 (0.16 ± 0.08)
Total Tape Thickness	t	0.6 ± 0.3 (0.02 ± 0.01)
Quantity per Reel (10D201KC – 10D361KC)	-	1000
Quantity per Reel (10D391KC – 10D821KC)	-	500

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$


Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




Packaging Specifications (Continued)

TAPE & REEL - Kinked Leads



Item	Symbol	10 mm Disc
Reel Outside Diameter	RD	$\frac{355}{(13.98)}$
Reel Inner Diameter	RD1	$\frac{30}{(1.181)}$
Tape Width	RW	$\frac{55}{(2.16)}$
Reel Width	RW1	$\frac{63}{(2.48)} \text{ max.}$
Pitch of Component	P	$\frac{25.4 \pm 1.0}{(1.00 \pm 0.04)}$
Feed Hole Pitch	P0	$\frac{12.7 \pm 0.2}{(0.50 \pm 0.008)}$
Feed Hole Center to Pitch	P1	$\frac{8.95 \pm 0.7}{(0.352 \pm 0.03)}$
Feed Hole Center to Component Center	P2	$\frac{12.7 \pm 0.7}{(0.50 \pm 0.03)}$
Lead to Lead Distance	F	$\frac{7.50 \pm 0.8}{(0.30 \pm 0.03)}$
Component Alignment	Dh	$\frac{2.0}{(0.79)} \text{ max.}$
Tape Width	W	$\frac{18.0 \pm 0.5}{(0.71 \pm 0.02)}$
Hole Down Tape Width	W0	$\frac{12.0 \pm 0.8}{(0.47 \pm 0.03)}$
Hole Position	W1	$\frac{9.0 \pm 0.5}{(0.35 \pm 0.02)}$
Hole Down Tape Position	W2	$\frac{3.0}{(0.12)} \text{ max.}$
Height From Component Top to Kinked Base	H	$\frac{17.5}{(0.69)} \text{ max.}$
Seating Plane Height	H0	$\frac{16.0 \pm 0.5}{(0.63 \pm 0.02)}$
Component Height	H1	$\frac{36.0}{(1.42)} \text{ max.}$
Feed Hole Diameter	D0	$\frac{4.0 \pm 0.2}{(0.16 \pm 0.08)}$
Total Tape Thickness	t	$\frac{0.6 \pm 0.3}{(0.02 \pm 0.01)}$
Quantity per Reel (10D201KKC – 10D361KKC)	-	1000
Quantity per Reel (10D391KKC – 10D821KKC)	-	500

BULK



QUANTITY:
 MOV-10D201KC – 10D561KC = 1000 PCS. PER BOX
 MOV-10D621KC – 10D821KC = 800 PCS. PER BOX



REV. 08/26

Specifications are subject to change without notice.
 Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."
- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automate Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.
- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.
- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <https://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <https://www.bourns.com/docs/Legal/disclaimer.pdf>

K2540 05/26R



CALIFORNIA WARNING: Can expose you to lead, a carcinogen and reproductive toxicant.

See www.P65Warnings.ca.gov

