


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680						
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
1017	A	RELEASED	JWM	5/9/02	HO	5/9/02	DJC	5/9/02	



### Specifications

- AC Voltage: 6 - 12 - 24 - 50 - 120 - 220 - 400V
- DC Voltage: 6 - 12 - 24 - 50 - 120 - 220 - 400V
- Display: LED
- Load Current: 30mA
- Test Duration: 30 Seconds
- Ambient Temperature: -10°C to 50°C
- Frequency Response: 0 to 100Hz

SPC-F004.DWG

**DISCLAIMER:**  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	5/9/02
CHECKED BY:	DATE:
Hisham Odish	5/9/02
APPROVED BY:	DATE:
Daniel Carey	5/9/02

DRAWING TITLE:			
Universal Voltage tester			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	72-6793	23C2632.dwg	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1