

Details:

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000 -Total (substrate and adhesive)	0.0053 inch (0.135 mm)
Adhesion to:	ASTM D 1000	
-Stainless Steel	20 minute dwell 24 hour dwell	128 oz/in (140 N/100 mm) 146 oz/in (160 N/100 mm)
-Textured ABS	20 minute dwell 24 hour dwell	45 oz/in (49 N/100 mm) 43 oz/in (47 N/100 mm)
-Polypropylene	20 minute dwell 24 hour dwell	80 oz/in (88 N/100 mm) 108 oz/in (119 N/100 mm)
-Painted Enamel	20 minute dwell 24 hour dwell	133 oz/in (146 N/100 mm) 142 oz/in (156 N/100 mm)
-Powder Coated Metal	20 minute dwell 24 hour dwell	78 oz/in (86 N/100 mm) 78 oz/in (86 N/100 mm)
Tack	ASTM D 2979 Polyken™ Probe Tack 0.5 second dwell	Greater than 24.7 oz (700 g)
Tensile Strength and Elongation	ASTM D 1000 - Machine Direction	59 lbs/in (1033 N/100mm), 5%

Performance properties tested on B-486 printed with alphanumerics, and a 5 mil and 10 mil minimum X dimension barcode using Series R4300 and R6200 ribbons and a BradyPrinter™ THT 300X Thermal Transfer Printer. Printed samples of B-486 were laminated to aluminum before exposure to the indicated environmental condition. Results the same for both ribbons unless noted otherwise.

PERFORMANCE PROPERTIES	TEST METHODS	TYPICAL RESULTS
Long Term High Service Temperature	30 days at 248°F (120°C)	No visible effect
Long Term Low Service Temperature	30 days at -40°F (-40°C)	No visible effect
Humidity Resistance	30 days at 100°F (37°C), 95% R.H.	No visible effect
UV Light Resistance	30 days in UV Sunlighter™ 100	No visible effect
Weatherability	ASTM G155, Cycle 1 30 days in Xenon Arc Weatherometer	No visible effect
Salt Fog Resistance	ASTM B 117 30 days in 5% salt fog solution chamber	No visible effect
Abrasion Resistance	Taber Abraser, CS-10 grinding wheels, (Fed.Std.191A, Method 5306) 500g/arm, 100 cycles	Print still legible after 100 cycles

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
----------------------	---------------------

Samples were printed with R4300 ribbon using a Brady 300X printer, laminated to flat aluminum panels and allowed to dwell 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical followed by 30 minute recovery periods. After the final immersion the flat samples were rubbed 10 times with cotton swabs. Testing was conducted at room temperature.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE	
	EFFECT UPON IMMERSION	EFFECT AFTER COTTON SWAB RUB
Methyl Ethyl Ketone	No visible effect	Slight smear when rubbed
1,1,1-Trichloroethane	No visible effect	Moderate smear when rubbed
Toluene	No visible effect	Moderate smear when rubbed
Freon® TMS	No visible effect	Slight smear when rubbed
Isopropyl Alcohol	No visible effect	No visible effect
Mineral Spirits	No visible effect	Slight smear when rubbed
JP-8 Jet Fuel	No visible effect	Moderate smear when rubbed
ASTM #3 Oil	No visible effect	No visible effect
Mil 5606 Oil	No visible effect	No visible effect
Skydrol® 500B-4	No visible effect	Slight smear when rubbed
Super Agitene®	No visible effect	No visible effect
Deionized Water	No visible effect	No visible effect
3% Alconox® Detergent	No visible effect	No visible effect
10% Sodium Hydroxide Solution	No visible effect	No visible effect
10% Sulfuric Acid Solution	No visible effect	No visible effect

Samples were printed with R6200 ribbon using a Brady 300X printer, laminated to flat aluminum panels and allowed to dwell 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical followed by 30 minute recovery periods. After the final immersion the flat samples were rubbed 10 times with cotton swabs. Testing was conducted at room temperature.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE	
	EFFECT UPON IMMERSION	EFFECT AFTER COTTON SWAB RUB
Methyl Ethyl Ketone	No visible effect	Severe smear when rubbed
1,1,1-Trichloroethane	No visible effect	Slight smear when rubbed
Toluene	No visible effect	Moderate smear when rubbed
Freon® TMS	No visible effect	Moderate smear when rubbed
Isopropyl Alcohol	No visible effect	No visible effect
Mineral Spirits	No visible effect	No visible effect
JP-8 Jet Fuel	No visible effect	No visible effect
ASTM #3 Oil	No visible effect	No visible effect
Mil 5606 Oil	No visible effect	No visible effect
Skydrol® 500B-4	No visible effect	Severe smear when rubbed
Super Agitene®	No visible effect	No visible effect
Deionized Water	No visible effect	No visible effect
3% Alconox® Detergent	No visible effect	No visible effect
10% Sodium Hydroxide Solution	No visible effect	No visible effect
10% Sulfuric Acid Solution	No visible effect	No visible effect

Product testing, customer feedback, and history of similar products, support a customer performance expectation of at least **two years from the date of receipt** for this product as long as this product is stored in its original packaging in an environment *below 80 degrees F (27 degrees C) and 60% RH*. We are confident that our product will perform well beyond this time frame. However, it remains the responsibility of the user to assess the risk of using such product. We encourage customers to develop functional testing protocols that will qualify a product's fitness for use, in their actual applications.

Trademarks:

ASTM: American Society for Testing and Materials (U.S.A.)

CSA: Canadian Standards Association

SAE: Society of Automotive Engineers (U.S.A.)

UL: Underwriters Laboratories Inc. (U.S.A.)

Alconox® is a registered trademark of Alconox Co.

BradyPrinter™ is a trademark of Brady Worldwide, Inc.

Freon® is a registered trademark of Du Pont de Nemours, E.I. and Company

Polyken™ is a trademark of Testing Machines Inc.

Skydrol® is a registered trademark of the Monsanto Company

Sunlighter™ is a trademark of the Test Lab Apparatus Company

Super Agitene® is a registered trademark of Graymills Corporation

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Specification Of Thermal Transfer Printable Labels

Application(s):	General & Industrial Identification
Agency	CSA Approved, UL Recognized
Approval(s)/Compliance:	
Size:	2.750" W x 1.250" H (69.850 mm W x 31.750 mm H)
Printable Area:	2.750" W x 1.250" H (69.850 mm W x 31.750 mm H)
Web Width:	2.950" (74.93 mm)
Label Type/Style:	Label
Vertical Repeat:	1.375" (34.93 mm)
Color:	Silver
Finish:	Matte
Qty Per Row:	1
Material Type:	Polyester
Material Description:	Ultra Aggressive Metallized Polyester
Brady Material #:	B-486
General ID Catalog:	pg. 33
Recommended Ribbon Series:	4300
Suggested Ribbon Part#:	R4300
Acceptable Ribbon Series:	6200, 4500 (colors)
Printer Compatibility:	BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady IP, Tagus T200, Tagus T300, Thermal Transfer Printers
Surface:	Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough
Special Properties:	Designed for powder coated surfaces, Ultra-aggressive adhesive
RoHS Compatibility:	Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.
QTY/UOM:	3,000/Roll