

at meets UL94V-0

Part Number	Tolerance	Capacitance	Voltage	Temperature	Dissipation Factor max. (%)	Equivalent Series Resistance @ 100kHz Max. (ohms)	Case Size	Dimensions		
								D Max. Inches [mm]	H Max. Inches [mm]	S ± .02 [0.5] Inches [mm]
DT100M10-2	±10%	100	20	125	1	1	K	0.335 [8.5]	0.276 [7.0]	0.2 [5.0]
DT150M10-2	±10%	150	20	125	1	0.8	N	0.35 [8.9]	0.276 [7.0]	0.2 [5.0]
DT68M10-1	±10%	68	20	125	8	1.3	H	0.276 [7.0]	0.413 [10.5]	0.2 [5.0]
DT47K10-1	±10%	47	10	125	8	1.7	G	0.236 [6.0]	0.394 [10.0]	0.1 [2.5]
DT33K10-1	±10%	33	10	125	8	2.1	F	0.236 [6.0]	0.394 [10.0]	0.1 [2.5]
DT22K10-1	±10%	22	10	125	8	2.7	E	0.217 [5.5]	0.354 [9.0]	0.1 [2.5]
DT15K10-1	±10%	15	10	125	8	3.7	D	0.197 [5.0]	0.354 [9.0]	0.1 [2.5]
DT10K10-1	±10%	10	10	125	8	5	C	0.197 [5.0]	0.335 [8.5]	0.1 [2.5]
DT6.8K10-1	±10%	6.8	10	125	6	6	B	0.177 [4.5]	0.295 [7.5]	0.1 [2.5]
DT4.7K10-1	±10%	4.7	10	125	6	8	A	0.177 [4.5]	0.276 [7.0]	0.1 [2.5]
DT2.2K10-1	±10%	2.2	10	125	6	10	A	0.177 [4.5]	0.276 [7.0]	0.1 [2.5]
DT1.5K10-1	±10%	1.5	10	125	6	13	A	0.177 [4.5]	0.276 [7.0]	0.1 [2.5]
DT800M10-2	±10%	800	20	125	1	1	K	0.335 [8.5]	0.276 [7.0]	0.2 [5.0]
DT560M10-2	±10%	560	20	125	1	0.8	N	0.35 [8.9]	0.276 [7.0]	0.2 [5.0]

F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:	CAPACITORS
	DANIEL CAREY	7/22/99	DIPPER	
	CHECKED BY:	DATE:	SIZE:	ANALOG FILE
	JOHN COLE	8/6/99		155.DWG
APPROVED BY:	JEFF MCVICAR			REV C
SHEET: 1 OF 2				

