
Current Transducer HTFS 200..800-P

For the electronic measurement of currents : DC, AC, pulsed, mixed, with a galvanic isolation between the primary circuit (high power) and the secondary circuit (electronic circuit).






All Data are given with a $R_1 = 10 \text{ k}\Omega$



Electrical data Primary nominal Primary current Type r.m.s. current measuring range $I_{P}(A)$ I_{PN}(A) 200 ±300 HTFS 200-P 400 +600**HTFS 400-P** 800 HTFS 800-P ±1200 Analog output voltage @ I_P $\mathbf{V}_{\text{REF}} \pm (1.25 \cdot \mathbf{I}_{\text{P}} / \mathbf{I}_{\text{PN}})$ V_{OUT} V $\mathbf{V}_{\text{REF}} \pm 0.025$ V $I_{p} = 0$ \mathbf{V}_{REF} $1/2V_{c} \pm 0.025$ Internal Reference¹⁾ - Output voltage V V_{REF} Output impedance typ. 200 Ω V_{REF} Load impedance ≥ 200 kΩ kΩ \mathbf{R}_{\perp} Output load resistance ≥ 2 $\mathbf{R}_{\mathrm{out}}$ Output impedance < 10 Ω $\mathbf{C}_{\scriptscriptstyle L}$ Max. output capacitive load < 1 μF V_{c} Supply voltage (± 5 %) 5 V I_c Current consumption @ $V_{c} = 5 V$ 22 mΑ Accuracy - Dynamic performance data % of $I_{_{\rm PN}}$ Х Accuracy $^{\scriptscriptstyle 2)}$ @ $\boldsymbol{I}_{_{PN}}$, $\boldsymbol{T}_{_{A}}$ = 25°C ≤±1 % of I_{PN} Linearity 0 .. 1.5 x $I_{_{PN}}$ e. ≤±0.5 **TCV**_{OUT} Thermal drift of **V**_{OUT} @ **I**_P = 0 ≤±0.3 mV/K $\textbf{TCV}_{\text{\tiny REF}}$ Thermal drift of $\textbf{V}_{\text{\tiny REF}}$ ≤±0.01 %/K $\text{TCV}_{\text{OUT}}/\text{V}_{\text{REF}}$ Thermal drift of $\text{V}_{\text{OUT}}/\text{V}_{\text{REF}}$ @ \textbf{I}_{P} = 0 ≤±0.2 mV/K TCe Thermal drift of the gain ≤±0.05% of reading/K Residual voltage @ $I_p = 0$, after an overload of 3 x $I_{PNDC} <\pm 0.5$ \mathbf{V}_{OM} % of I_{PN} Reaction time @ 10 % of $I_{_{\rm PN}}$ < 3 \mathbf{t}_{ra} μs Response time @ 90 % of $I_{_{PN}}$ < 7 μs t di/dt di/dt accurately followed > 100 A/µs Output noise (DC ..10 kHz) < 15 mVpp (DC .. 1 MHz) < 40 mVpp f Frequency bandwidth (-3 dB)³⁾ DC .. 20 kHz General data °C \mathbf{T}_{A} Ambient operating temperature - 40 .. + 105 °C Ambient storage temperature - 40 .. + 105



Features

- Hall effect measuring principle
- Galvanic isolation between primary and secondary circuit
- Low power consumption
- Single power supply +5V
- Ratiometric offset
- T_a = -40..+105 °C
- Fixation by M3 nuts and screws

Advantages

- · Small size and space saving
- Only one design for wide current ratings range
- · High immunity to external interference.
- V_{RFF} IN/OUT

Applications

Forklift drives

V

g

- AC variable speed drives
- Static converters for DC motor drives
- Battery supplied applications
- Uninterruptible Power Supplies (UPS)
- Switched Mode Power Supplies (SMPS)
- · Power supplies for welding applications.


Current Transducer HTFS 200..800-P

| Ins | sulation category | | | |
|-----------------------|--|----------------------|--------|----------|
| V _b | Nominal Voltage with IEC 61010-1 standards and f - Single insulation - Over voltage category III - Pollution degree 2 - Heterogeneous field | following conditions | 150 | V r.m.s. |
| V _b | Nominal Voltage with EN 50178 standards and foll - Reinforced insulation - Over voltage category III - Pollution degree 2 - Heterogeneous field | owing conditions | 150 | V r.m.s. |
| V _d | R.m.s. voltage for AC isolation test | . 50/60 Hz. 1 mn | 2.5 | kV |
| V _e | R.m.s. voltage for partial discharge extinction @ 10pC | | >1 | kV |
| v _w | Impulse withstand voltage 1.2/50 | • | 4 | kV |
| | If insulated cable is used for the proveled to the proveled to the improveled to the improveled to the insulation (primary) HAR 03 HAR 05 HAR 07 | • | able : | |

Notes : ¹⁾It is possible to overdrive **V**_{REF} with an external reference voltage between 2 - 2.8 V providing its ability to sink or source approx. 2.5 mA. ²⁾Excluding offset.

³⁾Small signal only to avoid excessive heatings of the magnetic core.

| Safety : Caution, risk of danger | This transducer shall be used in accordance with manufacturer instruction. Power supply shall be a low voltage source and shall have an efficient protective system against over current. Power supply must incorporate a circuit breaker. This transducer shall be used in an electric/electronic equipment in respect of standards rules and applicable safety requirements. |
|--|---|
| A Caution, risk of electrical shock | Primary bar and output terminals can provide hazardous voltage. This transducer is a built in device, of which conducting parts must be inaccessible by installation. Protective envelope or additional shield must be used. |



LEM reserves the right to carry out modifications on its transducers, in order to improve them, without previous notice.