

# A\_TE-1W Series



**FIXED INPUT ISOLATED & UNREGULATED  
1W OUTPUT  
DUAL OUTPUT  
UTRALMINIATURE SMD PACKAGE**

## FEATURES

- RoHS compliant
- High Efficiency up to 79%
- Positive & Negative Output Voltage
- Small Footprint
- SMD Package Style
- Industry Standard Pin Out
- UL94-V0 Package
- No Heatsink Required
- 1kVDC Isolation
- High Power Density
- Temperature Range: -40°C ~+85°C
- No External Components Required
- Low Cost
- Custom Service Available

## APPLICATIONS

The A\_TE-1W Series are specially designed for applications where a group of polar power supplies are isolated from the input power supply in a distributed power supply system on a circuit board.

These products apply to:

- 1) Where the voltage of the input power supply is fixed (voltage variation  $\leq \pm 10\%$ );
- 2) Where isolation is necessary between input and output (isolation voltage = 1000VDC);
- 3) Where the regulation of the output voltage and the output ripple noise are not demanding.


Such as: purely digital circuits, ordinary low frequency analog circuits, and IGBT power device driving circuits.

These products don't apply to:

- 1) Where the input supply voltage varied (variation  $\geq \pm 10\%$ ), otherwise our company's WRA series is recommended;
- 2) Where the isolation voltage between input and output is required to be > 1000VDC, otherwise our company's E\_TE-1W Series of products are recommended;
- 3) Circuits in which the output voltage regulation is demanding, otherwise our company's IA Series or WRA Series are recommended.
- 4) When the actual output power is less than 0.25w, the A\_TE-0.25W/0.5W series are recommended.

## MODEL SELECTION

A0505TE-1W



**MORNSUN Science & Technology Ltd.**

**Address:** 8th floor 8th building, Huangzhou Industrial Park, Guangzhou, China  
Tel: 86-20-85571041  
Fax: 86-20-85536272  
<http://www.mornsun.cn>

## PRODUCT PROGRAM

Part Number	Input		Output			Efficiency (% Typ.)	Package Style
	Voltage (VDC)		Voltage (VDC)	Current (mA)			
	Nominal	Range		Max.	Min.		
A0505TE-1W	5	4.5~5.5	$\pm 5$	$\pm 100$	$\pm 10$	72	SMD
A0509TE-1W	5	4.5~5.5	$\pm 9$	$\pm 56$	$\pm 6$	75	SMD
A0512TE-1W	5	4.5~5.5	$\pm 12$	$\pm 42$	$\pm 5$	78	SMD
A0515TE-1W	5	4.5~5.5	$\pm 15$	$\pm 33$	$\pm 4$	78	SMD
A1205TE-1W	12	10.8~13.2	$\pm 5$	$\pm 100$	$\pm 10$	74	SMD
A1209TE-1W	12	10.8~13.2	$\pm 9$	$\pm 56$	$\pm 6$	76	SMD
A1212TE-1W	12	10.8~13.2	$\pm 12$	$\pm 42$	$\pm 5$	79	SMD
A1215TE-1W	12	10.8~13.2	$\pm 15$	$\pm 33$	$\pm 4$	79	SMD

Note: 3.3V input and output models are also available.

## COMMON SPECIFICATIONS

Short circuit protection	1 second
Temperature rise at full load	25°C Max., 15°C Typ.
Cooling	Free air convection
Operating temperature range	-40°C ~+85°C
Storage temperature range	-55°C ~+125°C
Lead temperature	260°C
Storage humidity range	$\leq 95\%$
Case material	Plastic (UL94-V0)
MTBF	>1,000,000 hours

## ISOLATION SPECIFICATIONS

Item	Test conditions	Min.	Typ.	Max.	Units
Isolation voltage	Tested for 1 minute	1000			VDC
Isolation resistance	Test at 500VDC	1000			MΩ



## OUTPUT SPECIFICATIONS

Item	Test conditions	Min.	Typ.	Max.	Units
Output power		0.1		1	W
Line regulation	For $V_{in}$ change of 1%			1.2	%
Load regulation	10% to 100% load (5V output)		10	12	%
	10% to 100% load (9V output)		6.5	8.0	
	10% to 100% load (12V output)		6.0	8.5	
	10% to 100% load (15V output)		6.0	7.0	
Output voltage accuracy	See tolerance envelope graph				
Temperature drift	100% full load			0.03	%/°C
Output ripple	20MHz Bandwidth		50	75	mVp-p
Switching frequency	Full load, nominal input	100	150	200	kHz

Notes:


1. All data above were measured at  $T_A=25^\circ\text{C}$ , humidity < 75%, nominal input voltage and rated output load unless otherwise specified.
2. See below recommended circuits for more details.

## TYPICAL CHARACTERISTICS




## PIN CONNECTIONS


Pin	Function
1	GND
2	Vin
3	NC
4	0V
5	-Vo



Pin	Function
6	NC
7	+Vo
8	NC
9	NC
10	NC




<Figure 1>



<Figure 2>

## OUTLINE DIMENSIONS & RECOMMENDED FOOTPRINT DETAILS



Note: All Pins on a 2.54mm pitch; all pin diameters are 0.50mm; all dimensions in mm.

## APPLICATION NOTE

### Filtering

In some circuits which are sensitive to noise and ripple, a filtering capacitor may be added to the DC/DC output end and input end to reduce the noise and ripple. However, the capacitance of the output filter capacitor must be proper. If the capacitance is too big, a startup problem might arise. For every channel of output, provided the safe and reliable operation is ensured, the greatest capacitance of its filter capacitor sees the external capacitor table. To get an extremely low ripple, an "LC" filtering network may be connected to the input and output ends of the DC/DC converter, which may produce a more significant filtering effect. It should also be noted that the inductance and the frequency of the "LC" filtering network should be staggered with the DC/DC frequency to avoid mutual interference (see figure 1).

### Requirement on output load

To ensure this module can operate efficiently and reliably, a minimum load is specified for this kind of DC/DC converter in addition to a maximum load (namely full load). During operation, make sure the specified range of input voltage is not exceeded, the minimum output load is **not less than 10%** of the full load, and that this product should **not be operated under no load!** If the actual output power is very small, please connect a resistor with proper resistance at the output end in parallel to increase the load, or use our company's products with a lower rated output power (A\_TE-0.25W/0.5W series).

### Overload Protection

Under normal operating conditions, the output circuit of these products has no protection against over-current and short-circuits. The simplest method is to connect a self-recovery fuse in series at the input end or add a circuit breaker to the circuit.


### Output Voltage Regulation and Over-voltage Protection Circuit

The simplest device for output voltage regulation, over-voltage and over-current protection is a linear voltage regulator with overheat protection that is connected to the input or output end in series (see Figure 2).

### External Capacitor Table

V <sub>in</sub>	External capacitor	V <sub>out</sub>	External capacitor
5VDC	4.7uF	5VDC	4.7uF
12VDC	2.2uF	9VDC	2.2uF
24VDC	1uF	12VDC	1uF
--	--	15VDC	0.47uF

## Recommended Reflow Soldering



MORNSUN Science & Technology Ltd.

Address: 8th floor 8th building, Huangzhou Industrial Park, Guangzhou, China  
Tel: 86-20-85571041  
Fax: 86-20-85536272  
Http: //www.mornsun.cn