

step slides

- Set of 4 step slides.
- Step slide kit with brackets, enabling depth adjustment of the chassis on 12.5 mm pitch.
- Material: treated steel.
- Supplied with fixings and assembly instructions.
- For widths 1000 and 1200 mm:
 - mounting of a single chassis on the 6 backstuds: no additional accessories required.
 - mounting of 2 chassis on the 6 backstuds, order a set of 2 brackets ref. **51732**.
 - mounting of 2 stand-off chassis with depth adjustment, order a set of 2 bars ref. **51731** and a set of 2 brackets ref. **51732**.



step slides reference	for enclosure depth
51720	200
51725	250
51730	300
51740	400
51731	300 (1)

(1) Set of 2 step slides and 2 brackets for mounting 2 chassis with depth adjustment in enclosures width 1000 and 1200.

set of 2 brackets reference
51732

wall fixing lugs

- Set of 4 wall fixing lugs.
- Mounted vertically or horizontally directly on enclosure rear panel.
- Two lug types, steel and stainless steel 304, for 10 mm spacing from wall.
- Maximum permissible load: 4 x 60 kg.
- Supplied with fixings and protection seals.
- Fixing centres, see page **19068/2**.



reference	material
51206	steel
51207	stainless steel 304

canopy

- Direct fixing on enclosure body.
- Material: sheet steel, textured polyester powder paint finish, colour grey RAL 7032.
- Fixings included.
- Dimensions, see page **19068/4**.



reference	for enclosures	
	width	depth
50515	200	150
50502	300	150
50503	300	200
50512	400	150
50523	400	200
50524	400	250
50522	500	200
50535	500	250
50528	600	200
50529	600	250
50530	600	300
50539	600	400
50540	800	250
50541	800	300
50542	800	400
50543	1000	300
50545	1200	300

plinth

- Sheet steel, textured epoxy-polyester powder paint finish, colour black RAL 7022. Maximum load: 650 kg.
- Available in heights 100 and 200 mm. Can be stacked.
For plinth height 25 mm, consult your local Sarel sales office.
- Can be butt-mounted using the side plates for coupling 2 plinths.
- Supplied in kit form.
- Dimensions, see page **19068/4**.



plinth reference:	height	for enclosures	
		width	depth
100 mm	200 mm		
69063	69263	600	300
69064	69264	600	400
69083	69283	800	300
69084	69284	800	400
69103	69303	1000	300
69123	69323	1200	300