Photoelectrics Retro-Reflective Type CGPS-UG, DC, Plastic Housing





- · Ultra short body length
- 3m & 6m sensing ranges
- Some models with polarizing filter
- Dual output N.O. & N.C.
- Supply Voltage: 10 to 30 VDC
- · Cable and plug versions
- IP66
- CE marked, UL and cUL approved

Product Description

The CGPS-UG... is a family of cost-effective general-purpose retro-reflective photoelectric sensors in a compact and versatile 18mm housing. They are useful for simple applications where a basic sensor provides adequate sensing performance, or for applications requiring a compact sensor with exceptional sensing range. The sensors are simple to use and easy to install. The sensors have both Normally open and Normally closed outputs, making them versatile for any installation.

Ordering Key	CGPS-UG-6MN-M8	
Type Mode		
Sensing Distance - Output - Connection		

Type Selection

Housing Diameter	Sensing Distance	Output N.O. & N.C.	2 m cable	M8 Connector	M8 Connector w/lead
M18	3m	NPN	CGPS-UG-3MNE*	CGPS-UG-3MNE-M8*	CGPS-UG-3MNE-PG*
M18	3m	PNP	CGPS-UG-3MPE*	CGPS-UG-3MPE-M8*	CGPS-UG-3MPE-PG*
M18	6m	NPN	CGPS-UG-6MN	CGPS-UG-6MN-M8	CGPS-UG-6MN-PG
M18 *Polarized	6m	PNP	CGPS-UG-6MP	CGPS-UG-6MP-M8	CGPS-UG-6MP-PG

Specifications

Sensing Distance (S _n) Standard	6m	Ambient Light Immunity	Lamplight < 10, 000 Lux Sunlight < 20,000 Lux
Polarized	3m	Response Time Operating Frequency Output indication (LED functions) Environment Overvoltage Category Pollution degree Degree of protection Operating Temperature	1 ms 1 KHz
Sensitivity	Fixed		Green: Power ON Yellow: Output ON
Rated Operational Voltage (U _B)	10 - 30 VDC		III 3 IP 66 -20 °C to +80 °C; -4F to +176F 35% - 85% RH
Ripple (U _{rpp})	< 20%		
Output Current	150 mA maximum		
No Load Supply Current (I _O)	< 25 mA		



2.5 kV

2m M8 x 1

82 g 23 g 18 g

UL, cUL, CE

Intensive PBT PMMA


M8 Plug w / 6" Cable

CONG5A - .. series

Specifications (con't):


specifications (con t):		
Leakage Current	0.8 mA Maximum	Dielectric Voltage
Residual Voltage	0.1 V Maximum	Material Housing Lens
Protection	Short Circuit, Reverse Polarity	Connection Cable Plug Pig-tail
Transit Voltage	2 kV / 1µ s	Mating Cable M8 plug
Light Source	Red LED, 624 nm	Weight Cable version M12 M8 plug version
		Approvals

Dimensions:






Wiring Diagram:



Connection Diagram:



Pin1: +v Brown

Pin2: Output N.C. White Pin4: Output N.O. Black

Pin3: 0v Blue

Other Information:

Accessories:	CONM54NF for models with M8 plug
Delivery Contents:	Photoelectric sensor
	• 1 nut
	• 1 mounting bracket
	1 screwdriver (on models with adjustable sensitivity)
Compliancy/Approvals:	
	$(f(U_L)_c(U_L)$