48 Precision Internal Circlip Pliers (bore holes)



- ► for fitting circlips on bore holes, range of application from 8 – 140 mm dia.
- inserted tips of high density drawn spring wire
- ► heavy duty under continuous use; up to 10 times longer service life
- precise, smoothly-operating screw joint
- ► forged
- ► large contact faces on the tips: no distortion of circlips, easy fitting
- slim head style allows use in confined areas
- handles with non-slip plastic coating
- ► Chrome Vanadium electric steel



The new KNIPEX Precision

Circlip Pliers meet highest requirements.
Positive locked high density spring wire tips offer
10 times longer sevice life compared with conventional circlip pliers and high stability when loosening tight circlips. Circlips are held securely thanks to the large contact faces of the tips.



Sturdy, inserted tips: made from high density drawn spring wire



Circlips are held securely: large contact faces and the position of the tips make it difficult for the circlip to bounce off



Slim head style: allows use in confined areas



Screw joint: high precision and optimum drive

Article-No.	EAN-	Style	Head	Handles	Size of bore		47
Size	Code		•	•	•	Length	1
	4003773-				ø mm	mm	g
48 11 J0 J1 J2 J3	048510	1	grey atramentized	with non-slip plastic coating	8 - 13	140	100
	048527				12 - 25	140	100
	048534				19 - 60	180	180
	048541	1 1			40 - 100	225	260
J4	048558	straight			85 - 140	320	580
18 21 J01	048619		grey atramentized	with non-slip plastic coating	8 - 13	130	100
J11	048633				12 - 25	130	100
J21 J31	048640				19 - 60	165	180
	048657				40 - 100	210	260
J41	048664				85 - 140	305	580

Loosen tight circlips before removing these.

Only use circlip pliers for the specified diameter range.

We recommend wearing safety goggles when working with these pliers.