

DS9637A

Dual Differential Line Receiver

General Description


The DS9637A is a Schottky dual differential line receiver which has been specifically designed to satisfy the requirements of EIA Standards RS-422 and RS-423. In addition, the DS9637A satisfies the requirements of MIL-STD 188-114 and is compatible with the International Standard CCITT recommendations. The DS9637A is suitable for use as a line receiver in digital data systems, using either single ended or differential, unipolar or bipolar transmission. It requires a single 5V power supply and has Schottky TTL compatible outputs. The DS9637A has an operational input common mode range of ±7V either differentially or to ground.

Features

- Dual channel
- Single 5V supply
- Satisfies EIA standards RS-422 and RS423
- Built-in ±35 mV hysteresis
- High input common mode voltage range
- High input impedance
- TTL compatible outputs
- Schottky technology
- Extended temperature range

Connection Diagram

8-Lead DIP and SO-8 Package



Top View

Order Number DS9637ACM or DS9637ACN See NS Package Number M08A or N08E For Complete Military Product Specifications, refer to the appropriate SMD or MDS.

Order Number DS9637AMJ/883 See NS Package Number J08A

Absolute Maximum Ratings (Note 2)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Storage Temperature Range

Ceramic DIP -65° C to + 175 $^{\circ}$ C Molded DIP -65° C to + 150 $^{\circ}$ C

Lead Temperature Ceramic DIP

(Soldering, 30 seconds) 300°C

Molded DIP and SO Package

(Soldering, 10 seconds) 265°C

Maximum Power Dissipation (Note 1) at 25°C

Cavity Package 1300 mW

Molded Package 930 mW

SO Package 810 mW

V_{CC} Lead Potential to Ground -0.5V to 7.0V

Input Potential to Ground ±15V

Differential Input Voltage ±15V

Output Potential to Ground -0.5V to +5.5V

Output Sink Current 50 mA

Recommended Operating Conditions

DS9637AM	Min	Max	Units
Supply Voltage (V _{CC})	4.5	5.5	V
Operating Temperature (T _A)	-55	+125	°C
DS9637AC			
Supply Voltage (V _{CC})	4.75	5.25	V
Operating Temperature (T _A)	0	+70	°C

Note 1: Derate cavity package 8.7 mW/°C above 25°C; derate molded DIP package 7.5 mW/°C above 25°C; derate SO package 6.5 mW/°C above 25°C.

Electrical Characteristics (Notes 3, 4)

Over recommended operating temperature and supply voltage ranges, unless otherwise specified

Symbol	Parameter	Conditions	Min	Тур	Max	Units
V_{TH}	Differential Input	$-7.0V \le V_{CM} \le +7.0V$	-0.2		+0.2	V
	Threshold Voltage (Note 6)					
V _{TH(R)}	Differential Input	$-7.0V \le V_{CM} \le +7.0V$	-0.4		+0.4	V
	Threshold Voltage (Note 7)					
I ₁	Input Current	$V_{I} = 10V, \ 0V \le V_{CC} \le +5.5V$		1.1	3.25	mA
	(Note 8)	$V_{I} = -10V, \ 0V \le V_{CC} \le +5.5V$		-1.6	-3.25	
V _{OL}	Output Voltage LOW	I _{OL} = 20 mA, V _{CC} = Min		0.35	0.5	V
V _{OH}	Output Voltage HIGH	$I_{OH} = -1.0 \text{ mA}, V_{CC} = \text{Min}$	2.5	3.5		V
I _{os}	Output Short Circuit	$V_O = 0V$, $V_{CC} = Max$	-40	-75	-100	mA
	Current (Note 5)					
I _{cc}	Supply Current	$V_{CC} = Max, V_I + = 0.5V,$		35	50	mA
		V _I - = GND				
V _{HYST}	Input Hysteresis	V _{CM} = ±7.0V (See Curves)		70		mV

Note 2: "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. They are not meant to imply that the devices should be operated at these limits. The tables of "Electrical Characteristics" provide conditions for actual device operation.

Note 3: Unless otherwise specified Min/Max limits apply across the -55° C to $+125^{\circ}$ C temperature range for DS9637AM and across the 0° C to $+70^{\circ}$ C range for the DS9637ASC. All typicals are given for $V_{CC} = 5V$ and $T_A = 25^{\circ}$ C.

Note 4: All currents into the device pins are positive; all currents out of the device pins are negative. All voltages are referenced to ground unless otherwise specified.

Note 5: Only one output at a time should be shorted.

Note 6: V_{DIFF} (Differential Input Voltage) = $(V_{I}+)$ – $(V_{I}-)$. V_{CM} (Common Mode Input Voltage) = $V_{I}+$ or $V_{I}-$.

Note 7: $500\Omega \pm 1\%$ in series with inputs.

Note 8: The input not under test is tied to ground.

Switching Characteristics

 $V_{CC} = 5.0V, T_A = 25^{\circ}C$

Symbol	Parameter	Conditions	Min	Тур	Max	Units
t _{PLH}	Propagation Delay Time	See AC Test Circuit		15	25	ns
	Low to High					
t _{PHL}	Propagation Delay Time	See AC Test Circuit		13	25	ns
	High to Low					







FIGURE 1. Equivalent Circuit

Typical Input/Output Transfer Characteristics






AC Test Circuit and Waveforms



 \mathbf{C}_{L} includes jig and probe capacitance. All diodes are FD700 or equivalent.


FIGURE 2.



Amplitude: 1.0V Offset: 0.5V Pulse Width: 100 ns PRR: 5.0 MHz $t_r = t_f \leq 5.0 \text{ ns}$

FIGURE 3.

Typical Applications




Notes:


 $R_T \geq 50\Omega$ for RS-422 operation.

 $\mbox{R}_{\mbox{\scriptsize T}}$ combined with input impedance of receivers must be greater than $90\Omega.$


FIGURE 4. RS-422 System Application (FIPS 1020) Differential Simplex Bus Transmission


Physical Dimensions inches (millimeters) unless otherwise noted






Ceramic Dual-In-Line Package (J) Order Number DS9637AMJ/883 NS Package Number J08A





Molded Surface Mount Package (M) Order Number DS9637ACM NS Package Number M08A

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Molded Dual-In-Line Package (N) Order Number DS9637ACN **NS Package Number N08E**

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

For the most current product information visit us at www.national.com.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

BANNED SUBSTANCE COMPLIANCE

National Semiconductor certifies that the products and packing materials meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor **Americas Customer** Support Center

Tel: 1-800-272-9959

Email: new.feedback@nsc.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86 Email: europe.support@nsc.com

Deutsch Tel: +49 (0) 69 9508 6208 English Tel: +44 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com **National Semiconductor** Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560