
Engineering/Process Change Notice

ECN/PCN No.: R0447

For Manufacturer			
Product Description: SMD 915MHz SAW Filter	**Abracon Part Number / Part Series:** ABSES5AD-1E3M012M	☐ Documentation only ☒ ECN ☐ EOL	☒ Series ☐ Part Number
Affected Revision: B	**New Revision:** C	**Application:**	☐ Safety ☒ Non-Safety

Prior to Change:



After Change:



Engineering/Process Change Notice

Cause/Reason for Change:
Updated templates, no design or performance updates

Change Plan

Effective Date:	**Additional Remarks:**
12/4/2025	

Change Declaration:

Issued Date:	**Issued By:**	**Issued Department:**
12/4/2025	Allan	Engineering
Approval: *Saravanan Subramanian* Engineering Manager	**Approval:** *Reuben Quintanilla* Quality Director	**Approval:** *Ying Huang* Purchasing Director

For Abracon EOL only

Last Time Buy (if applicable):	**Alternate Part Number / Part Series:**

Additional Approval:	**Additional Approval:**	**Additional Approval:**

Customer Approval (If Applicable)

Qualification Status:

☐ Approved ☐ Not accepted

Note: It is considered approved if there is no feedback from the customer 1 month after ECN/PCN is released.

Customer Part Number:	**Customer Project:**

Company Name:	**Company Representative:**	**Representative Signature:**

Customer Remarks:

ABRACON Ecliptek FOX ILSI MMD OSCILENT

SMD 915MHz SAW Filter




ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Description

This SMD 915 MHz SAW filter is engineered for the 902–928 MHz ISM band, supporting LPWA, LoRa, Sigfox, Wi-SUN, Wi-Fi HaLow, and Amazon Sidewalk protocols. Housed in a compact 1.4 x 1.1 x 0.7 mm package with 26 MHz bandwidth, it delivers low 1.6 dB typical insertion loss and exceptional out-of-band rejection exceeding 36 dB for superior interference suppression. Rated for +10 dBm input power and RoHS-compliant with MSL Level 3, this filter ensures reliable performance for smart metering, irrigation systems, home security cameras, and agricultural sensing applications.



Features

- Frequency Range: 902 – 928 MHz
- Bandwidth: 26 MHz
- Small Form Factor: 1.4 x 1.1 x 0.7 mm
- Low Insertion Loss: 1.6 dB Typ.
- Out-of-Band Rejection: > 36 dB Typ.
- Maximum Input Power: +10 dBm
- RoHS Compliant | MSL Level 3

Applications

- LPWA / LoRa / Sigfox / Wi-SUN
- Wi-Fi HaLow (IEEE 802.11ah)
- Amazon Sidewalk
- Home Security Cameras
- Smart Metering Solutions
- Smart Irrigation Systems
- Agriculture/Environment Sensing

Ordering Information

Part Number	Description
ABSES5AD-1E3M012M	SMD 915MHz SAW Filter on Tape & Reel

Note: Other options not listed may be available upon request via Abracon online support

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter



ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Electrical Specification

Parameters	Minimum	Typical	Maximum	Units	Notes
Center Frequency (fc)	-	915	-	MHz	-
VSWR (1)	-	1.5	2.0	:1	902 - 928 MHz
Insertion Loss (1)	-	1.6	2.6	dB	902 - 928 MHz
Amplitude Ripple (1)	-	0.6	1.5	dB	902 - 928 MHz
Attenuation (1)	50.0	53.0	-	dB	0.10 - 702.00 MHz
	49.0	53.0	-		738.00 - 764.00 MHz
	42.0	50.0	-		820.00 - 846.00 MHz
	42.0	50.0	-		990.00 - 1010.00 MHz
	49.0	53.0	-		1072.00 - 1092.00 MHz
	40.0	42.0	-		1128.00 - 1804.00 MHz
	40.0	42.0	-		1804.00 - 1856.00 MHz
	30.0	36.0	-		1856.00 - 3000.00 MHz
Group Delay (1)	-	42	53	ns	902 - 928 MHz
Group Delay Ripple (1)	-	7.0	11.4	ns	902 - 928 MHz
Source Impedance (single ended)	-	50	-	Ω	-
Load Impedance (single ended)	-	50	-	Ω	-
Input Power Level	-	-	10	dBm	-
DC Voltage (V)	-	-	3	V	-

Notes: (1) Averaged values of linear S-Parameters at +25ºC

Mechanical Specification

Parameters	Specifications
Dimension	1.4 x 1.1 x 0.7 mm
Mounting Type	Surface Mount
Additional Resources	Download STEP File, Package Drawing, 3D PDF

Environmental Specification

Parameters	Specifications
Operating & Storage Temperature (Unpackaged Component)	-40ºC ~ +85ºC
Storage Temperature in Packaging	-5ºC ~ +40ºC
Packaging Storage Relative Humidity	70% (Max.)
MSL level	3

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter




ABSES5AD-1E3M012M


Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3


Product Dimensions



TOP VIEW



BOTTOM VIEW



FRONT VIEW

Unit: inches [mm]

Pin No.	Description
C	Input
A	Output
B, D, E	Ground

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED


SMD 915MHz SAW Filter

ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Recommended Land Pattern



Land Pattern

Unit : mm

Please note: The line width should be designed to achieve a 50-ohm characteristic impedance, depending on the PCB material and thickness. For technical assistance, please contact Abracon online support through our online support platform.

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter




ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Measurement Circuit



Pin No.	Description
C	Input Impedance: 50 Ω
A	Output Impedance: 50 Ω
B, D, E	Ground

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter


ABSES5AD-1E3M012M


Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Frequency Characteristics

S21 narrow band





ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED


SMD 915MHz SAW Filter

ABSES5AD-1E3M012M


Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

S21 wide band



Group Delay



ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED


SMD 915MHz SAW Filter


ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

VSWR (S11 & S22)





ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter


ABSES5AD-1E3M012M

Request Samples | Check Inventory


1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Smith Chart (S11 & S22)

Smith chart S11 (902~928MHz)



Smith chart S22 (902~928MHz)



ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter



ABSES5AD-1E3M012M

Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process Classification Temperatures (T_c)		
Package Thickness	**Volume mm³ <350**	**Volume mm³ ≧350**
<2.5mm	235°C	220°C
≧2.5mm	220°C	220°C

Table 2

Pb-Free Process Classification Temperatures (T_c)			
Package Thickness	**Volume mm³ <350**	**Volume mm³ 350-2000**	**Volume mm³ >2000**
<1.6mm	260°C	260°C	260°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	180°C
Time (T_{smin} to T_{smax}) (t_s)	60 – 120 sec.	60 – 90 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	220°C
Time at Liquidous (T_L)	60 – 150 sec.	50 – 80 sec.
Peak package body temperature (T_p)*	**See Table 1**	**See Table 2**
Time (T_p)** within 5°C of the specified classification temperature (T_c)	20 sec.	20 ~ 40 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.
**Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.


ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

SMD 915MHz SAW Filter



ABSES5AD-1E3M012M


Request Samples | Check Inventory

1.4 x 1.1 x 0.7 mm
RoHS Compliant
MSL Level = 3

Packaging

Tape & Reel (5,000 pcs / reel)

1. Tape & Reel Dimension



Carrier Tape Specifications (mm)												
Do	D_1	E_1	P_0	P_2	T	F	P_1	W	A_0	B_0	K_0	Reel Qty
1.55 ± 0.05	0.6 ± 0.05	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.05	0.2 ± 0.03	3.5 ± 0.05	4.0 ± 0.1	8.0 ± 0.1	1.3 ± 0.05	1.6 ± 0.05	0.77 ± 0.05	5,000

Reel Specifications (mm)				
A	W_1	N	C	B
180.9 ± 0.15	8.48 ± 0.15	57.12 ± 0.15	13.12 ± 0.15	2.2 ± 0.2

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-04-25

ABRACON IS ISO9001-2015 CERTIFIED

Brand	Affected PN	Discontinued/EOL PN	Added PN	Series	ECO#	Datasheet Link	ECN Notification Link
Abracon	ABSES5AD-1E3M012M			ABSES5AD-1E3M012M	R0447	https://abracon.com/datasheets/ABSES5AD-1E3M012M.pdf	https://abracon.com/downloads/ECN-PCN/ECN-PCN-Notification_ECOR0447_ABSES5AD-1E3M012M.pdf
Abracon	ABSES5AD-1E3M012M-EVB			ABSES5AD-1E3M012M	R0447	https://abracon.com/datasheets/ABSES5AD-1E3M012M.pdf	https://abracon.com/downloads/ECN-PCN/ECN-PCN-Notification_ECOR0447_ABSES5AD-1E3M012M.pdf