


Magnifier Luminaire




FGL 118

connected load	230 V; 50 Hz
fitted with	1 x compact fluorescent lamp TC-L 18 W neutral white
workequipment	conventional ballast
mains lead	approx. 3.0 m; shock-proof plug
luminaire body	
material	plastic
tubular sections	
material	steel tube
surface	painted
weight (net)	approx. 4,1 kg
fastening	table clamp (accessory)~wall bracket (accessory)
technology	switchable
usage	switch
lamp cover	acrylic; white opal
balance of articulation joints	spring
class of protection	I
colour luminaire body	light grey
colour of tubular sections	light grey
lens; dimensions	162 x 105
lens; diopters	3
article no.	111711018



E_{min}: 1031 lx
E_m: 3436 lx
E_{max}: 6824 lx



measuring conditions: d=15cm

