

Magnifier Luminaire



RLL 122 T


connected load
fitted with

work equipment
mains lead
luminaire body material
tubular sections material
weight (net)
fastening technology
usage
lamp cover
balance of articulation joints
class of protection
colour luminaire body
colour of tubular sections
lens; dimensions
lens; diopters
article no.


230 V; 50 Hz
1 x fluorescent lamp T29-R 22 W
neutral white
conventional ballast
approx. 2.9 m; Euro plug

plastic

plastic
approx. 3,1 kg
table clamp (accessory)~wall bracket (accessory)
switchable
switch
polycarbonate; white opal
spring
II
light grey
light grey
Ø 120 mm
4
111851000



Emin: 838 lx
Em: 2162 lx
Emax: 3255 lx



measuring conditions: d=15cm

