

Magnifier Luminaire



RLL 122 T

connected load
fitted with

work equipment
mains lead
luminaire body
material

tubular sections
material

weight (net)

fastening
technology

usage

lamp cover

balance of articulation joints

class of protection

colour luminaire body

colour of tubular sections

lens; dimensions

lens; diopters

article no.

230 V; 50 Hz

1 x fluorescent lamp T29-R 22 W
neutral white

conventional ballast

approx. 1.9 m; three-prong plug (BS1363A)

plastic

plastic

approx. 3,1 kg

table clamp (accessory)~wall bracket (accessory)

switchable

switch

polycarbonate; white opal

spring

II


light grey

light grey


Ø 120 mm

4

111851022



Emin: 838 lx
Em: 2162 lx
Emax: 3255 lx



measuring conditions: d=15cm

