


## Magnifier Luminaire




**SNL 319**

connected load	230 V; 50 Hz
fitted with	3 x compact fluorescent lamp TC-S 9 W neutral white
work equipment	conventional ballast
mains lead	approx. 4.0 m; three-prong plug (BS1363A)
luminaire body	plastic
material	steel tube
tubular sections	painted
material	approx. 4,5 kg
surface	screw-down flange~table clamp (accessory)~wall bracket (accessory)
weight (net)	multi-stage switchable
fastening	switch
technology	screen; milky
usage	spring
lamp cover	I
balance of articulation joints	light grey
class of protection	light grey
colour luminaire body	162 x 105
colour of tubular sections	3
lens; dimensions	111961011
lens; diopters	
article no.	



E<sub>min</sub>: 1967 lx  
E<sub>m</sub>: 4252 lx  
E<sub>max</sub>: 6096 lx



measuring conditions: d=15cm

