


# **Panasonic** ideas for life

# 4 A CAPACITY, THE VARIETY OF CONTACT **ARRANGEMENTS**

# **S RELAYS**



mm inch

### **FEATURES**

- The variety of contact arrangements 2 Form A 2 Form B, 3 Form A 1 Form B, 4 Form A
- · Latching types available
- · High sensitivity in small size 100 mW pick-up and 200 mW nominal operating power
- High shock and vibration resistance Shock: 50 G Vibration: 10 to 55 Hz at double amplitude of 3 mm .118 inch
- Wide switching range From 100μA 100 mV DC to 4 A 250 V AC
- Low thermal electromotive force Approx. 3 µV
- Dual-In-Line packaging arrangement
- Amber types available

# **SPECIFICATIONS**

#### **Contacts**

Arrangemen	t	2 Form A 2 Form B, 3 Form A 1 Form B, 4 Form A			
	t resistance, r drop 6 V DC 1	50 mΩ			
Initial contac	t pressure		Approx. 12 g .42 oz		
Contact mate	erial		Gold clad silver alloy		
Electrostatic	capacitance		Approx. 3pF		
Thermal electronic (at nominal continuation)	ctromotive forecoil voltage)	Approx. 3μV			
	Nominal swi	tching capacity	4 A 250 V AC, 3 A 30 V DC		
	Maximum sv	vitching power	1,000 VA, 90 W		
Rating (resistive)	Maximum sv	vitching voltage	250 V AC, 30 V DC (48 VDC at less than 0.5 A)		
	Max. switchi	ng current	4 A (AC), 3 A (DC)		
	Min. switchin	ng capacity#1	100μA 100 m V DC		
Expected	Mechanical	(at 50 cps)	108		
life (min.	Electrical	4 A 250 V AC	10⁵		
operations)	(at 20 cpm)	3 A 30 V DC	2 × 10 <sup>5</sup>		

#### Coil (polarized) (at 20°C 68°F)

Single side stable	Minimum operating power	Approx. 100 mW
	Nominal operating power	Approx. 200 mW
Latching	Minimum set and reset	Approx. 100 mW
	Nominal set and reset	Approx. 200 mW

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the

#### Remarks

- \* Specifications will vary with foreign standards certification ratings.
  \*1 Measurement at same location as "Initial breakdown voltage" section
- \*2 Detection current: 10mA
- \*3 Excluding contact bounce time
- \*4 Half-wave pulse of sine wave: 11ms; detection time: 10μs
- \*5 Half-wave pulse of sine wave: 6ms
- \*6 Detection time: 10μs
- \*7 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT


## Characteristics (at 25°C 77°F 50% Relative humidity)

Max. operation	ng speed		20 cpm for maximum load, 50 cps for low-level load (1 mA 1 V DC)					
Initial insulat	ion resista	ance*1	I	10,000 MΩ at 500 V DC				
	Betweer	open	contacts	750 Vrms				
Initial breakdown	Betweer	n conta	act sets	1,000 Vrms				
voltage*2	Betweer coil	onta	acts and	1,500 Vrms				
Operate time (at nominal v		t 20°C	<b>;</b> )	Max. 15 ms (Approx. 8 ms)				
Release time (at nominal v				Max. 10 ms (Approx. 5 ms)				
Set time*3 (la (at nominal v		t 20°C	;)	Max. 15 ms (Approx. 8 ms)				
Reset time*3 (at nominal v	`	,	Max. 15 ms (Approx. 8 ms)					
Initial contac	t bounce,	max.		1 ms				
Temperature (at nominal v		t 20°C	Max. 35°C with nominal coil voltage and at maximum switching current					
Fui		Fund	ctional*4	Min. 490 m/s <sup>2</sup> {50 G}				
Shock resistance		Destructive*5		Min. 980 m/s <sup>2</sup> {100 G}				
Vibration resistance		Functional*6		176.4 m/s <sup>2</sup> {18 G}, 10 to 55 Hz at double amplitude of 3 mm				
		Destructive		235.2 m/s <sup>2</sup> {24 G}, 10 to 55 Hz at double amplitude of 4 mm				
Conditions for operation, transport and storage*7			Ambient temp.	-40°C to +65°C -40°F to +149°F				
(Not freezing and condensing at low temperature)			Humidity	5 to 85% R.H.				
Unit weight				Approx. 8 g .28 oz				

# TYPICAL APPLICATIONS

Telecommunications equipment, data processing equipment, facsimiles, alarm equipment, measuring equipment.

# ORDERING INFORMATION



- (Notes) 1. Standard packing Carton: 50 pcs. Case: 500 pcs.
  2. 1 coil latching also available as option. Contact our sales office for details.
  - 3. UL/CSA approved type is standard.
  - 4. 1 coil latching type available.

# TYPES AND COIL DATA at 20°C 68°F

# Single side stable

Туре	Nominal voltage, V DC	Pick-up voltage, V DC (max.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA	Coil resistance, Ω (±10%)	Inductance, mH	Nominal operating power, mW	Maximum allowable voltage, V DC (40°C)
S□EB-3V	3	2.1	0.3	66.7	45	23	200	5.5
S□EB-5V	5	3.5	0.5	38.5	130	65	192	9.0
S□EB-6V	6	4.2	0.6	33.3	180	93	200	11.0
S□EB-12V	12	8.4	1.2	16.7	720	370	200	22.0
S□EB-24V	24	16.8	2.4	8.4	2,850	1,427	202	44.0
S□EB-48V	48	33.6	4.8	5.6	8,500	3,410	271	75.0


#### 2 coil latching

Туре	Nominal voltage, V DC	Set and reset voltage, Nominal operat current,		Coil resistance, Ω (±10%)		Inductance, mH		Nominal operating power,	Maximum allowable voltage,
		V DC (max.)	mA	Coil I	Coil II	Coil I	Coil II	mW	V DC (40°C)
S□EB-L2-3V	3	2.1	66.7	45	45	10	10	200	5.5
S□EB-L2-5V	5	3.5	38.5	130	130	31	31	192	9.0
S□EB-L2-6V	6	4.2	33.7	180	180	40	40	200	11.0
S□EB-L2-12V	12	8.4	16.7	720	720	170	170	200	22.0
S□EB-L2-24V	24	16.8	8.4	2,850	2,850	680	680	202	44.0
S□EB-L2-48V	48	33.6	7.4	6,500	6,500	1,250	1,250	355	65.0

Note: Insert 2, 3 or 4 in ☐ for contact form required.

# **DIMENSIONS**

mm inch



**12-1.3 DIA** .047-.051 [


PC board pattern (Copper-side view)


General tolerance:  $\pm 0.3 \pm .012$ 


#### Tolerance: ±0.1 ±.003

# Schematic (Bottom view)

Single side stable **Deenergized position**  2a2b










#### 2 coil latching

Diagram shows the "reset" position when terminals 6 and 7 are energized. Energize terminals 1 and 12 to transfer contacts.









# REFERENCE DATA

#### 1. Maximum switching power




2. Life curve




3. Contact reliability
Condition: 1V DC, 1mA
Detection level 10 Ω


Tasted Sample: S4EB-24V, 10pcs




4.-(1) Coil temperature rise Tested Sample: S4EB-24V, 4 Form A




4.-(2) Coil temperature rise Tested Sample: S4EB-24V, 4 Form A





5. Operate and release time (Single side stable type) Tested Sample: S4EB-24V, 10pcs



6. Influence of adjacent mounting







# **ACCESSORIES**





#### **Specifications**

<u>'</u>					
Breakdown voltage	1,500 Vrms between terminals				
Insulation resistance	More than 100 $\text{M}\Omega$ between terminals at 500 V DC Mega				
Heat resistance	150 ±3°C (302 ±5.4°F) for 1 hour.				
Maximum continuous current	4 A				

(Note: Don't insert or remove relays while in the energized condition.)

#### **Dimensions** mm inch






PC board pattern (Copper-side view)


#### Inserting and removing method


Inserting method: Insert the relay as shown in Fig. 1 unit the rib of the relay snaps into the clip of the socket.

#### Removing method:

- (1) Remove the relay straight from the socket holding the shaded portion of the relay as shown in Fig. 2.
- (2) When sockets are mounted in close proximity, use a slotted screw driver as shown in Fig. 3.








# **NOTES**

- 1. Special use of 2 coil latching types: 2 ways can be considered if 2 coil latching types are used as 1 coil latching types.
- (A) Reverse polarity is applied to the set coil of 2 coil latching type.
- (B) By shorting terminals 12 and 7, apply plus to 1, minus to 6 at set and plus to 6, minus to 1 at reset. Applied coil voltage should be the same as the nominal. Operating power will be reduced to one-half.


#### Reset position of 2a2b type



2. Soldering operations should be accomplished as quick as possible; within 10 seconds at 250°C 482°F solder temperature or 3 seconds at 350°C 662°F. The header portion being sealed with epoxy resin, undue subjection to heat may cause loss of seal. Solder should not be permitted to remain on the header.

# **CAUTIONS FOR USE**

Based on regulations regarding insulation distance, there is a restriction on same-channel load connections between terminals No. 2, 3 and 4, 5, as well as between No. 8, 9 and 10, 11. See the figure below for an example.



Between 2, 3 and 4, 5: different channels, therefore not possible
 Between 10, 11 and 8, 9: different channels, therefore not possible

Between 2, 3 and 4, 5: same channels, therefore possible
 Between 10, 11 and 8, 9: same channels, therefore possible

No good

# Good

# For Cautions for Use, see Relay Technical Information