

BELDENCable™

9843 Paired - Low Capacitance Computer Cables for EIA RS-485 Applications

 	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p> <p>Color Code Chart : No. 5 for Paired Cables (Western Electric Standard).pdf</p>
--	--

Description:

24 AWG stranded (7x32) TC conductors, polyethylene insulation, twisted pairs, overall Beldfoil® (100% coverage) + TC braid shield (90% coverage), 24 AWG stranded TC drain wire, PVC jacket

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Pairs	3
Total Number of Conductors	6
AWG	24
Stranding	7x32
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PE - Polyethylene
---------------------	-------------------

Lay Length :

Lay Length (in.)	Direction	Twists/ft (twist/ft)
1.0	Left Hand Lay	12

Twists/ft. 12

Pair Color Code Chart :

Number	Color	Number	Color
1	White/Blue & Blue/White	3	White/Green & Green/White
2	White/Orange & Orange/White		

OUTER SHIELD:

Outer Shield Material Trade Name	Beldfoil®
----------------------------------	-----------

Outer Shield Type	Tape/Braid
-------------------	------------

Outer Shield Material :

Layer Number	Material Trade Name	Type	Material	% Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90



9843 Paired - Low Capacitance Computer Cables for EIA RS-485 Applications

OUTER SHIELD DRAIN WIRE :	
Outer Shield Drain Wire AWG	24
Outer Shield Drain Wire Stranding	7x32
Outer Shield Drain Wire Conductor Material	TC - Tinned Copper

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	.360 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-30°C To +80°C
UL Temperature Rating	80°C (UL AWM Style 2919)
Bulk Cable Weight	73 lbs/1000 ft.
Max. Recommended Pulling Tension	105.5 lbs.
Min. Bend Radius (Install)	3.75 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CM
CEC/C(UL) Specification	CM
AWM Specification	UL Style 2919 (300 V 80°C)
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004

FLAME TEST:

UL Flame Test	UL1685 UL Loading
---------------	-------------------

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

ELECTRICAL CHARACTERISTICS:

Nom. Characteristic Impedance	120 Ohms
Nom. Capacitance Conductor to Conductor @ 1 KHz	23 pF/ft
Nom. Cap. Cond. to Other Cond. & Shield @ 1 KHz	12.8 pF/ft
Nominal Velocity of Propagation	66 %
Nominal Delay	1.6 ns/ft
Nom. Conductor DC Resistance @ 20 Deg. C	24 Ohms/1000 ft
Nominal Outer Shield DC Resistance @ 20 Deg. C	2.3 Ohms/1000 ft
Nom. Attenuation (dB/100 ft)	0.6 (@ 1 MHz) dB/100 ft.



9843 Paired - Low Capacitance Computer Cables for EIA RS-485 Applications

Max. Operating Voltage - UL	300 V RMS (UL AWM Style 2919)
Max. Recommended Current	1.54 Amps per conductor @ 25°C

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
9843 060100	3 PR #24 PE SH PVC	100	7.1	CHROME	
9843 0601000	3 PR #24 PE SH PVC	1000	67	CHROME	C
9843 060500	3 PR #24 PE SH PVC	500	34.5	CHROME	C

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 07-21-2005

© 2005 Belden Wire & Cable Company
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden CDT Electronics Division believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden CDT Electronics Division declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.