


ENERGIZER NO. L92


AAA





Dimensions in mm (inches)



Chemical System: Lithium/Iron Disulfide (Li/FeS₂)
Designation: ANSI-24LF, IEC-FR03
Battery Voltage: 1.5 Volts
Typical Weight: 7.6 grams (0.3 oz.)
Typical Volume: 3.8 cubic centimeters (0.2 cubic inch)
Average Capacity: 1250 mAh (to 1.0 volts)
 (Rated capacity at 100 mA drain)
Max Discharge: 1.5 Amps Continuous
 2.0 Amps Pulse, 2 sec on/8 sec off
 (to 1.0 volts)
Storage Temp: -40°C to 60°C (-40°F to 140°F)
Operating Temp: -40°C to 60°C (-40°F to 140°F)
Lithium Content: Less than 0.5 grams (0.02 oz.) per cell
Jacket: Non-magnetic Plastic Label
Transportation: Meets requirements of 49CFR 173.185 (b) and IATA special provisions A45
Shelf Life: 15 years



Typical Battery Performance



Important Notice


This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.


© Energizer - All Rights Reserved

ENERGIZER NO. L92







Typical Battery Performance



Temperature Effects



ANSI - IEC Industry Standard Tests @ 20° C



Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

© Energizer - All Rights Reserved