

Lithium Coin Cell - CR2032JHT

- Reliable energy for your application
- Standard cells and customized packs
- ESD protection
- UL recognized
- Battery Certification Experts

RoHS 2011/65/EC compliant

Pb free

REACH compliant

Conflict mineral free


Technical Data Sheet · CR2032JHT

SPECIFICATIONS


Nominal Voltage	3V
Jauch part number	251845
Nominal Capacity	200 mAh
Standard Load	15 kΩ
Standard Curent	0.2 mA
Max. Pulse Current	15 mA
Operating Temperature	- 40°C to + 125°C*
Weight	Approx. 3.1 gr.
Chemistry	Li/MnO_2
UL1642	MH62838

* In applications where the battery is exposed to temperatures >100°C, please contact Jauch.


DIMENSION




DISCHARGE CHARACTERISTICS




TEMPERATURE CHARACTERISTICS



INTERNAL RESISTANCE/TEMPERATURE



LOAD VS. CAPACITY



Wide assortment of mounting options, including through hole, surface mount and wire terminals.
Contact Jauch for more information.

©JQG 2025

09042026

Jauch Quartz GmbH • e-mail: batterytechnology@jauch.com
www.jauch.com

This information is generally descriptive only and is not intended to make or imply any representation, guarantee or warranty with respect to any cells and batteries. Cell and battery designs/specifications are subject to modification without notice. Contact JAUCH for the latest informatoion.