



HBL61CM65 -- Straight Blade Products, Weatherproof Flanged Receptacle



2-Pole 3-Wire Grounding, 20A 125V, 5-20R, with Lift Cover and Boot, Multiple Drive Screws, Gray

Product Specifications

Product Type	 <p>Flanged Receptacles</p>
Standard	NEMA
Amperage	20A
Voltage	125V
Poles and Wires	2 Pole, 3-Wire Grounding
Wiring Method	Side Wire Only
Hospital Grade ?	No
Receptacle Grade	Heavy Duty Spec Grade
Flange Style	Weatherproof
Enhancement	Corrosion Resistance
Color	 <p>Gray</p>
NEMA No.	5-20R
Horsepower	1
Type	2 Pole, 3 Wire, Grounding
Rating	20A, 125V
Certification	UL Listed, File E2186, Meets NEMA WD-6 requirements Listed to UL Standard 498, Certified to CSA, C22.2, No. 42
Terminal Screw Material	#8-32 Brass, Multiple Drive
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Base Material	Nylon
Power Contacts Material	.040" (1.0) Brass
Mounting Screw Material	Stainless Steel
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).

Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 V2.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A28
Catalog Section	Click here for Section-A
UPC Number	783585808673
Weight in LBs	0.250

