

A


Accessories for 19" subracks

B

Rack handles

- very stable version made of solid aluminium, 1 set comprises 2 handles incl. mounting material
- further sizes **G** → N ?

C



D

art. no.	suitable for subracks	art. no.	suitable for subracks
BGT 0384 7ME	3 U	BGT 0684 7ME	6 U

E

Threaded rails

- threaded rails with M 2.5 threads for mounting of fixing rails and front panels
- 1 set contains 4 threaded rails

F

art. no.
BGT 384 2

G

insulating strip (A)

- for rear module rail
- is used for isolation of the BUS-backplane
- with the isolating strips the standard insert depth for the plug-in module in the subrack will be established

H

art. no.
IST 84

I

technical data

class of flammability: UL 94 V-O
 material: PBT, self-extinguishing

K

Clips (B)

- for simple fastening of insulation strips into the threaded rails

L

art. no.	packing unit
FC	100 pieces

M

technical data

class of flammability: UL 94 V-O
 material: noryl, red

N

N 3

19" front panels
 Variable guide rails
 Reinforced guide rails
 Guide rail


→ N ?
 → N 6
 → N 6
 → N 5

Fixing material
 PCB holder
 19" handles
 Accessory for part front panels

→ N ?
 → N ? - ?
 → N ? - ?
 → N ?


Accessories for 19" subracks

Z-rails for connectors



art. no.	packing unit
GB 5 L	1 set contains 2 Z-rails for connectors with 32/48/64/96 contacts to DIN 41612
GB 20 L	1 set contains 2 Z-rails for connectors with 31 contacts according to DIN 41617



Cover panels



art. no.	handle perforation	suitable for subracks
BGTG 384 6	with	3 U
BGTG 684 6	with	6 U
BGTG 2 x 384 6	with	BGTO 2 x 384/ BGTG 2 x 384
BGTO 384 6	without	3 U
BGTO 684 6	without	6 U
BGTO 2 x 384 6	without	BGTO 2 x 384/ BGTG 2 x 384

Rear terminal profile

- 2 pieces cover the 2.54 mm gap between the part front panel and side panel
- **surface:** clear anodised



GB 37

art. no.	suitable for subracks
RA 3	3 U
RA 6	6 U

19" front panels
Variable guide rails
Reinforced guide rails
Guide rail

→ N ?
→ N 6
→ N 6
→ N 5

Fixing material
PCB holder
19" handles
Accessory for part front panels

→ N ?
→ N ? - ?
→ N ? - ?
→ N ?

N 4

A

B

C

D

E

F

G

H

I

K

L

M


N

A

Accessories for 19" subracks

B

Perforated cover panel




art. no.	depth of PCB [mm]	art. no.	depth of PCB [mm]
AB 211	160	AB 271	220

C

D

Backpanel protective cover

- with side panel depth of 240 and 300 mm gives mechanical and antistatic protection
- delivery incl. mounting material



art. no.	suitable for subracks	art. no.	suitable for subracks
RV 3 240	3 U	RV 6 240	6 U


E

F

G

Guide-rails

- with advanced mounting pins and locking neeps for easy mounting



art. no.	for Eurocards [mm]
FSC 100	100 x 100/ 233,5 x 100
FSC 160	100 x 160/ 233,5 x 160
FSC 220	100 x 220/ 233,5 x 220

H

I

K

L

M

N

N 5

19" front panels
 Variable guide rails
 Reinforced guide rails
 Guide rail

→ N ?
 → N 6
 → N 6
 → N 5


Fixing material
 PCB holder
 19" handles
 Accessory for part front panels

→ N ?
 → N ? - ?
 → N ? - ?
 → N ?

Accessories for 19" subracks

Variable guide-rails


- contains 1 pair of heads and 1 profile
- head pieces (1 pair): art. no. **FSC V**; profile (in running meters) art. no. **FSC P**
- further profile lengths upon request



art. no.	art. no.
FSC P	FSC V

Reinforced guide rails

- easy and fast to install by the use of clips
- can also be screwed into the module rails (M 2.5 x 12)
- high rigidity
- centred with spring-loaded strut
- good ventilation due to lattice work
- assembly option for one contact spring for advanced earthing to the module rails and front cover using conductor on the printed circuit board



art. no.	for Eurocards [mm]	art. no.	for Eurocards [mm]
FSCE 160	100 x 160/ 233,5 x 160	FSCE 220	100 x 220/ 233,5 x 220

contact spring please order separately:

art. no.
KFCE 1

19" front panels → N ?
 Variable guide rails → N 6
 Reinforced guide rails → N 6
 Guide rail → N 5

Fixing material → N ?
 PCB holder → N ? - ?
 19" handles → N ? - ?
 Accessory for part front panels → N ?

N 6

A

B

C

D

E

F

G

H

I

K

L

M

N