

CyMotion Master Plus9 wireless

M86-21700

CyMotion Line



Key benefits

- ADVANCED TECHNOLOGY KEYBOARD for even better key operation (ATK)
- High transmission and anti-tapping security thanks to data encryption with „Cherry Security Radio Technology“
- Precise working with the optical mouse due to the high resolution of 800 dpi
- Elegant, symmetric design
- Quick access to frequently-used functions with the unique, side-mounted XPress-keys (freely-programmable)
- Additional, free-programmable keys for controlling multimedia, Internet and your own applications
- Individual and easy key assignment due to our KeyM@n Software with new, comfort functions
- Palm rest with unique space saving storage feature
- F-key and double assignment for multimedia and Internet functions

Delivery volume

Keyboard
Wireless optical mouse
Palm rest
Receiver
4x batteries type AA
Adapter USB-PS/2
Printed manual

Approvals

FCC, cUR/cURus, GS, CE,
c-tick, GHOST-R
Microsoft Windows™ ME, 2000, XP

System requirements

USB or PS/2 interface

Technical data

Number of keys:

104 + 9 = US Layout with Windows™ and additional keys

105 + 9 = EU Layout with Windows™ and additional keys

Weight:

approx. 1170 g (keyboard)
approx. 2150 g (with packaging)

Dimensions:

approx. 495 x 195 x 37 mm (keyboard)
approx. 560 x 325 x 65 mm (packaging)

Range of coverage:

typ. 2 m

Storage temperature:

-20 °C until 60 °C

Working temperature:

0 °C until 50 °C

Operating life of standard individual key:

> 20 million operations

Interface:

USB (PS/2 via adapter)

Current input:

Keyboard: typ. 6 mA (at 2,0-3,3 V)

Mouse: typ. 20 mA (at 2,0-3,3 V)

Receiver: typ. 10 mA (at 4,0-5,25 V)

Packaging unit:

29 keyboards per master carton

2 master cartons per pallet

Guarantee period:

2 years

Order description

Order number	Housing	Number of keys
M86-21700xxAAAAA	black/ silver	113/114
M86-21700xxABAAB	white/ white	113/114
M86-21700xxACAAD	white/ silver	113/114
M86-21700xxADAAE	black/ black	113/114

The xx in the order description defines the country version.

BE	Belgium
CH	Switzerland
DE	Germany
ES	Spain
EU	US English/ international with €
FR	France
GB	English (UK)
IT	Italy
SF	Sweden/ Finland
SL	Slovenia
RG	Russia

Country version upon request.

Cherry GmbH
Cherrystraße
D-91275 Auerbach/Opf.
Phone: +49 (0) 9643 18-0
Hotline: +49 (0) 9643 18-206
Fax: +49 (0) 9643 18-1545
Internet: www.cherry.de

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.
Technical data relate to product specifications only.
Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2004 Cherry GmbH